

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519757

Luminaire Tested: **SQ4-125U-0D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519757
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6515.8 lumens
Efficiency: N/A
Efficacy: 137.2 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 47.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519757
CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519757

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5081	54623	19330
100°	5239	47957	41627
105°	5592	33428	46933
110°	5803	23239	44720
115°	6044	17047	37258
120°	6137	13428	29056
125°	6080	11279	22433
130°	6005	9892	17483
135°	5938	8892	14126
140°	5906	8156	11728
145°	5928	7579	9886
150°	6009	7123	8612
155°	6082	6789	7705
160°	6144	6556	7095
165°	6189	6395	6681
170°	6232	6280	6432
175°	6240	6208	6279



TEST NUMBER: P519757

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	472.2	7.2
100°-110°	1271.9	19.5
110°-120°	1334.8	20.5
120°-130°	1083.2	16.6
130°-140°	849.5	13.0
140°-150°	652.2	10.0
150°-160°	468.9	7.2
160°-170°	286.5	4.4
170°-180°	96.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3078.9	47.3
90°-150°	5663.8	86.9
90°-180°	6516.0	100.0
0°-180°	6515.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	8	15	17	17	
95°	72	257	774	396	274	80
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	



TEST NUMBER: P519757

CATALOG NUMBER: SQ4-125U-0D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)