

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518399

Luminaire Tested: **SQ4-BB-050U-050D-835-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518399
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9739.6 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 79.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518399
CATALOG NUMBER: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518399

CATALOG NUMBER: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	97	93	90	87	88	85	82	79	69	68	66	55	54	53	42	42	41	35				
2	89	83	77	73	81	76	71	67	63	59	57	50	48	47	39	38	37	32				
3	82	74	68	63	75	68	62	58	56	53	49	46	43	41	36	34	33	29				
4	76	66	60	54	69	61	55	51	51	47	43	42	39	37	33	31	30	26				
5	70	60	53	47	64	55	49	44	46	42	38	38	35	33	31	29	27	24				
6	65	54	47	42	59	50	44	39	42	38	34	35	32	29	28	26	25	22				
7	61	50	42	37	55	46	40	35	39	34	31	32	29	27	26	24	22	20				
8	56	45	38	33	52	42	36	32	36	31	28	30	27	24	25	22	21	18				
9	53	42	35	30	48	39	33	29	33	29	25	28	25	22	23	21	19	17				
10	49	38	32	27	45	36	30	26	31	26	23	26	23	20	22	19	18	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9694	9694	9694
5°	9538	9515	9585
10°	8925	9044	9296
15°	8114	8371	8837
20°	7202	7576	8240
25°	6272	6769	7571
30°	5372	5962	6937
35°	4455	5061	6172
40°	3422	4047	5259
45°	2474	3064	4232
50°	1686	2284	3356
55°	1096	1652	2609
60°	629	1163	1885
65°	167	710	955
70°	83	219	274
75°	37	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P518399

CATALOG NUMBER: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	287.7	3.0
10°-20°	735.7	7.6
20°-30°	921.0	9.5
30°-40°	850.7	8.7
40°-50°	571.6	5.9
50°-60°	295.2	3.0
60°-70°	92.5	0.9
70°-80°	5.8	0.1
80°-90°	3.6	0.0
90°-100°	439.4	4.5
100°-110°	1193.5	12.3
110°-120°	1227.1	12.6
120°-130°	981.1	10.1
130°-140°	770.9	7.9
140°-150°	591.1	6.1
150°-160°	425.1	4.4
160°-170°	260.0	2.7
170°-180°	87.6	0.9
0°-30°	1944.3	20.0
0°-40°	2795.0	28.7
0°-60°	3661.9	37.6
0°-90°	3763.8	38.6
90°-120°	2860.0	29.4
90°-150°	5203.1	53.4
90°-180°	5976.0	61.4
0°-180°	9739.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3152	3152	3152	3152	3152	
5°	3090	3058	3082	3093	3105	286
15°	2548	2539	2629	2717	2776	710
25°	1848	1863	1995	2131	2231	847
35°	1186	1216	1348	1507	1644	735
45°	569	603	705	842	973	447
55°	204	239	308	396	486	191
65°	23	44	98	118	131	39
75°	3	3	2	0	0	4
85°	0	0	0	0	0	0
90°	3	12	21	26	26	5
95°	65	240	765	333	224	69
105°	212	330	1312	1998	1880	225
115°	377	457	1051	2090	2381	372
125°	518	590	950	1602	1889	462
135°	624	693	924	1304	1471	482
145°	721	773	912	1108	1192	453
155°	815	844	906	995	1024	376
165°	883	894	909	948	950	249
175°	915	918	912	924	921	87
180°	915	915	915	915	915	

TEST NUMBER: P518399

CATALOG NUMBER: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3152.2	3152.2	3152.2	3152.2	3152.2
2.5°	3159.5	3129.7	3137.6	3137.4	3129.0
5°	3089.7	3058.4	3082.1	3093.0	3104.9
7.5°	2959.1	2934.7	2980.2	3014.3	3039.1
10°	2857.9	2837.0	2896.0	2942.5	2976.8
12.5°	2740.8	2724.7	2796.0	2859.8	2903.6
15°	2548.3	2539.4	2629.1	2717.4	2775.5
17.5°	2342.1	2341.8	2444.3	2553.9	2623.9
20°	2200.6	2205.1	2315.0	2435.8	2517.8
22.5°	2059.1	2069.5	2186.9	2312.8	2406.8
25°	1848.3	1863.2	1994.7	2131.2	2231.1
27.5°	1645.8	1667.6	1805.9	1947.8	2069.4
30°	1512.8	1538.2	1679.0	1828.3	1953.5
32.5°	1382.3	1412.4	1549.7	1707.6	1835.2
35°	1186.5	1216.3	1348.1	1506.8	1644.0
37.5°	984.2	1013.5	1142.2	1298.4	1446.6
40°	852.5	885.3	1008.0	1159.4	1310.0
42.5°	732.9	765.7	881.2	1029.9	1172.1
45°	568.8	603.1	704.6	841.7	973.0
47.5°	432.8	470.1	559.1	683.2	802.8
50°	352.3	389.6	477.3	586.7	701.5
52.5°	287.6	323.7	402.9	506.0	611.2
55°	204.4	238.6	308.1	395.5	486.5
57.5°	141.2	170.7	233.0	306.0	377.3
60°	102.2	130.5	189.1	248.4	306.5
62.5°	68.0	94.0	151.3	196.7	235.8
65°	22.9	43.8	97.6	117.7	131.2
67.5°	11.6	14.0	51.2	54.1	58.6
70°	9.2	9.2	24.4	26.0	30.5
72.5°	6.7	6.7	9.8	12.5	13.4
75°	3.1	3.1	1.5	0.0	0.0
77.5°	1.5	1.5	1.2	0.0	0.0
80°	1.5	1.5	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	2.3	4.1	5.3	5.3
90°	2.9	11.6	20.6	26.5	26.5
92.5°	26.5	120.3	208.9	89.7	75.9
95°	64.7	240.3	765.1	333.0	223.7
97.5°	107.1	265.4	1173.0	912.6	641.0
100°	135.4	282.1	1297.8	1315.6	1062.4
102.5°	163.6	298.9	1330.8	1627.0	1403.7
105°	211.9	329.9	1312.5	1998.4	1880.5
107.5°	261.9	366.1	1236.6	2190.2	2223.0
110°	297.2	392.2	1180.1	2228.0	2369.0



TEST NUMBER: P518399

CATALOG NUMBER: SQ4-BB-050U-050D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	327.8	418.2	1123.6	2196.7	2409.0
115°	376.7	457.3	1050.6	2090.1	2380.8
117.5°	422.6	499.7	1004.1	1939.1	2266.6
120°	453.2	528.0	982.9	1837.8	2163.0
122.5°	479.1	553.9	968.8	1736.3	2050.0
125°	517.9	589.9	950.5	1601.6	1889.3
127.5°	552.7	624.0	940.5	1499.4	1746.3
130°	573.9	642.9	935.8	1435.3	1656.8
132.5°	595.0	664.1	931.1	1380.5	1576.8
135°	623.9	692.9	924.1	1304.5	1471.4
137.5°	655.1	717.8	920.5	1237.4	1377.8
140°	673.9	734.3	918.2	1194.7	1321.3
142.5°	692.7	748.6	915.8	1161.3	1267.2
145°	721.0	772.8	912.3	1108.4	1191.8
147.5°	752.8	797.1	909.3	1066.8	1132.4
150°	774.0	811.4	909.3	1042.9	1094.7
152.5°	790.4	823.2	907.0	1021.5	1064.1
155°	815.2	843.9	906.4	995.3	1024.1
157.5°	839.3	861.7	906.4	977.5	999.4
160°	853.4	873.6	906.4	965.6	982.9
162.5°	867.5	883.1	908.7	956.1	968.8
165°	882.9	894.4	909.3	947.7	950.5
167.5°	898.7	904.5	912.3	937.6	939.9
170°	903.5	909.2	912.3	932.9	932.9
172.5°	908.2	911.6	912.3	928.2	928.2
175°	915.2	918.1	912.3	924.0	921.1
177.5°	917.6	917.6	910.5	919.8	915.2
180°	915.2	915.2	915.2	915.2	915.2

(END OF REPORT)