

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520405

Luminaire Tested: **SQ4-F-150U-075D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520405
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G3-1910-536-18)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-150U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11715.7 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 96.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520405
CATALOG NUMBER: SQ4-F-150U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P520405

CATALOG NUMBER: SQ4-F-150U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	85	78	72	67	77	71	66	61	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	26	46	36	29	24	29	24	20	23	19	16	17	14	13	10
9	48	36	28	23	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8702	8702	8702
5°	8735	8624	8687
10°	8699	8587	8652
15°	8632	8526	8600
20°	8554	8454	8521
25°	8460	8373	8434
30°	8353	8262	8308
35°	8244	8157	8195
40°	8105	8022	8012
45°	7966	7866	7888
50°	7744	7683	7683
55°	7564	7468	7399
60°	7322	7194	7131
65°	6925	6794	6701
70°	6503	6343	6181
75°	5851	5639	5516
80°	4679	4587	4541
85°	2809	3169	3260



TEST NUMBER: P520405

CATALOG NUMBER: SQ4-F-150U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	1.1
10°-20°	380.1	3.2
20°-30°	571.1	4.9
30°-40°	681.5	5.8
40°-50°	698.9	6.0
50°-60°	622.8	5.3
60°-70°	464.3	4.0
70°-80°	251.8	2.1
80°-90°	60.4	0.5
90°-100°	565.9	4.8
100°-110°	1530.2	13.1
110°-120°	1608.7	13.7
120°-130°	1306.7	11.2
130°-140°	1025.0	8.7
140°-150°	786.7	6.7
150°-160°	565.8	4.8
160°-170°	345.6	3.0
170°-180°	116.5	1.0
0°-30°	1084.8	9.3
0°-40°	1766.3	15.1
0°-60°	3087.9	26.4
0°-90°	3864.5	33.0
90°-120°	3704.8	31.6
90°-150°	6823.3	58.2
90°-180°	7851.0	67.0
0°-180°	11715.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1415	1415	1415	1415	1415	
5°	1415	1412	1397	1408	1407	134
15°	1356	1353	1339	1349	1350	382
25°	1247	1245	1234	1240	1243	574
35°	1098	1095	1086	1086	1091	686
45°	916	912	904	904	907	705
55°	705	704	696	690	690	630
65°	476	476	467	462	460	474
75°	246	241	237	233	232	259
85°	40	42	45	45	46	55
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2516	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	

TEST NUMBER: P520405

CATALOG NUMBER: SQ4-F-150U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1414.7	1414.7	1414.7	1414.7	1414.7
2.5°	1419.8	1416.8	1404.5	1414.7	1413.6
5°	1414.7	1412.1	1396.7	1408.2	1407.0
7.5°	1403.2	1400.4	1385.2	1396.7	1396.5
10°	1392.8	1389.1	1374.9	1386.4	1385.2
12.5°	1379.6	1375.7	1361.5	1373.1	1371.9
15°	1355.6	1353.2	1339.0	1349.2	1350.5
17.5°	1328.5	1323.8	1311.1	1321.1	1322.3
20°	1306.9	1303.2	1291.6	1300.5	1301.8
22.5°	1284.4	1280.6	1268.9	1278.0	1279.3
25°	1246.6	1245.4	1233.8	1240.3	1242.8
27.5°	1205.9	1202.3	1193.1	1198.0	1200.5
30°	1176.1	1173.6	1163.3	1167.2	1169.7
32.5°	1145.3	1143.9	1134.5	1136.4	1139.9
35°	1097.9	1095.4	1086.3	1086.4	1091.4
37.5°	1045.3	1042.5	1035.0	1033.8	1035.8
40°	1009.4	1005.6	999.1	997.8	997.8
42.5°	972.4	969.7	961.1	958.9	961.9
45°	915.8	912.0	904.3	904.3	906.8
47.5°	854.5	853.0	843.9	839.9	840.9
50°	809.3	811.9	802.9	797.9	802.9
52.5°	770.3	768.8	760.8	755.8	757.7
55°	705.4	704.2	696.4	690.0	690.0
57.5°	640.2	637.0	629.0	624.2	627.9
60°	595.2	593.9	584.8	576.0	579.7
62.5°	550.0	547.7	538.7	532.9	535.6
65°	475.8	475.8	466.8	461.7	460.4
67.5°	410.9	404.9	399.9	393.7	392.0
70°	361.6	356.6	352.7	347.5	343.7
72.5°	313.4	310.5	304.5	299.4	298.6
75°	246.2	241.2	237.3	233.4	232.1
77.5°	175.2	174.2	170.5	168.6	169.3
80°	132.1	132.1	129.5	129.5	128.2
82.5°	93.1	94.1	93.6	91.6	91.3
85°	39.8	42.3	44.9	44.9	46.2
87.5°	7.7	13.7	14.7	14.9	14.7
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.2	941.2	487.1	289.7
97.5°	141.0	353.5	1467.0	1214.1	891.6
100°	180.9	371.9	1630.6	1700.6	1375.1
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.5	439.5	1697.5	2503.9	2401.4
107.5°	346.4	487.8	1623.4	2775.0	2809.1
110°	394.5	522.7	1557.3	2847.7	2992.6



TEST NUMBER: P520405

CATALOG NUMBER: SQ4-F-150U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.3	3076.5
115°	500.8	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.3	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.3
122.5°	636.0	736.5	1293.8	2315.3	2724.6
125°	685.6	785.6	1268.9	2141.2	2515.5
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2105.9
135°	821.9	919.3	1234.7	1728.9	1957.0
137.5°	861.4	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.5	1687.2
145°	955.6	1027.3	1217.7	1479.8	1592.7
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.4	1461.6
152.5°	1045.0	1094.2	1208.8	1363.7	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.2
157.5°	1113.9	1143.4	1207.5	1302.2	1331.0
160°	1133.8	1158.2	1208.6	1286.4	1306.9
162.5°	1149.5	1169.9	1209.6	1273.7	1289.1
165°	1174.5	1186.1	1212.5	1259.8	1266.2
167.5°	1191.5	1199.4	1212.7	1247.9	1251.0
170°	1202.1	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.4	1235.4
175°	1219.1	1217.7	1213.8	1229.5	1226.9
177.5°	1222.0	1218.9	1213.5	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)