

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562643

Luminaire Tested: **SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562643
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6378.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562643
CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562643

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8488	8488
25°	8382	8443	8417
30°	8281	8381	8344
35°	8157	8282	8224
40°	8022	8135	8053
45°	7877	7932	7810
50°	7670	7670	7548
55°	7427	7331	7220
60°	7069	6926	6816
65°	6533	6402	6347
70°	5721	5766	5744
75°	4603	5090	5121
80°	3269	4314	4360
85°	1990	3620	3620



TEST NUMBER: P562643

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	2.1
10°-20°	376.2	5.9
20°-30°	569.7	8.9
30°-40°	683.0	10.7
40°-50°	696.4	10.9
50°-60°	607.9	9.5
60°-70°	435.2	6.8
70°-80°	224.2	3.5
80°-90°	58.2	0.9
90°-100°	190.9	3.0
100°-110°	518.5	8.1
110°-120°	533.1	8.4
120°-130°	426.2	6.7
130°-140°	334.9	5.3
140°-150°	256.8	4.0
150°-160°	184.7	2.9
160°-170°	112.9	1.8
170°-180°	38.1	0.6
0°-30°	1077.0	16.9
0°-40°	1760.0	27.6
0°-60°	3064.3	48.0
0°-90°	3781.9	59.3
90°-120°	1242.5	19.5
90°-150°	2260.4	35.4
90°-180°	2596.0	40.7
0°-180°	6378.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1385	1385	1385	1385	1385	
5°	1390	1376	1381	1377	1376	132
15°	1338	1326	1338	1338	1336	377
25°	1235	1226	1244	1240	1240	568
35°	1086	1084	1103	1095	1095	679
45°	906	903	912	900	898	697
55°	693	684	684	673	673	617
65°	449	439	440	436	436	444
75°	194	202	214	216	216	209
85°	28	43	51	53	51	38
90°	1	5	9	12	12	3
95°	28	104	332	145	97	30
105°	92	143	570	868	817	98
115°	164	199	456	908	1034	161
125°	225	256	413	696	821	201
135°	271	301	402	567	639	210
145°	313	336	396	482	518	197
155°	354	367	394	432	445	163
165°	384	389	395	412	413	108
175°	398	399	396	401	400	38
180°	398	398	398	398	398	

TEST NUMBER: P562643

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1385.2	1385.2	1385.2	1385.2	1385.2
2.5°	1393.4	1381.3	1385.2	1382.0	1377.0
5°	1390.3	1376.5	1381.3	1377.4	1376.2
7.5°	1380.3	1366.5	1372.9	1370.3	1369.0
10°	1371.1	1357.3	1364.7	1362.1	1360.8
12.5°	1358.8	1346.0	1354.4	1351.8	1351.6
15°	1337.7	1326.4	1337.7	1337.7	1336.4
17.5°	1311.3	1301.0	1313.1	1313.8	1313.1
20°	1292.8	1281.5	1296.7	1295.4	1296.7
22.5°	1270.3	1261.0	1277.2	1273.9	1275.1
25°	1235.1	1226.3	1244.1	1240.2	1240.2
27.5°	1193.6	1187.3	1206.6	1202.5	1202.5
30°	1165.9	1159.6	1180.0	1174.8	1174.8
32.5°	1135.1	1130.8	1150.2	1144.0	1144.0
35°	1086.3	1083.8	1103.0	1095.3	1095.3
37.5°	1036.1	1033.8	1051.2	1041.9	1038.9
40°	999.1	997.9	1013.2	1003.0	1003.0
42.5°	962.2	960.9	974.2	961.9	961.9
45°	905.5	903.0	911.9	900.3	897.8
47.5°	843.7	841.2	846.8	834.2	832.9
50°	801.6	799.1	801.6	790.0	788.8
52.5°	758.5	754.0	754.4	742.9	742.6
55°	692.6	683.8	683.6	673.3	673.3
57.5°	622.8	611.3	612.3	603.5	602.3
60°	574.6	562.0	563.0	555.3	554.1
62.5°	527.4	512.8	515.8	507.1	506.9
65°	448.9	438.9	439.9	436.1	436.1
67.5°	373.5	364.2	370.9	367.8	367.6
70°	318.1	311.8	320.6	320.6	319.4
72.5°	266.8	266.5	277.5	277.6	278.3
75°	193.7	202.4	214.2	215.5	215.5
77.5°	129.3	144.8	157.8	158.3	158.0
80°	92.3	109.9	121.8	124.4	123.1
82.5°	62.6	81.1	91.1	93.6	92.3
85°	28.2	43.3	51.3	52.6	51.3
87.5°	8.5	18.2	22.3	22.8	20.8
90°	1.3	5.0	8.9	11.5	11.5
92.5°	11.5	52.3	90.8	39.0	33.0
95°	28.1	104.4	332.4	144.7	97.2
97.5°	46.5	115.3	509.6	396.5	278.5
100°	58.8	122.6	563.8	571.5	461.5
102.5°	71.1	129.8	578.1	706.9	609.8
105°	92.1	143.3	570.2	868.2	817.0
107.5°	113.8	159.0	537.2	951.5	965.8
110°	129.1	170.4	512.7	967.9	1029.2

TEST NUMBER: P562643

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	142.4	181.7	488.1	954.3	1046.6
115°	163.6	198.7	456.4	908.1	1034.3
117.5°	183.6	217.1	436.2	842.4	984.7
120°	196.9	229.4	427.0	798.4	939.7
122.5°	208.1	240.6	420.9	754.3	890.6
125°	225.0	256.3	413.0	695.8	820.8
127.5°	240.1	271.1	408.6	651.4	758.7
130°	249.3	279.3	406.6	623.5	719.8
132.5°	258.5	288.5	404.5	599.8	685.0
135°	271.0	301.0	401.5	566.7	639.3
137.5°	284.6	311.8	399.9	537.6	598.6
140°	292.8	319.0	398.9	519.0	574.0
142.5°	301.0	325.2	397.9	504.5	550.5
145°	313.2	335.7	396.3	481.5	517.8
147.5°	327.0	346.3	395.1	463.5	492.0
150°	336.2	352.5	395.1	453.1	475.6
152.5°	343.4	357.7	394.0	443.8	462.3
155°	354.1	366.6	393.8	432.4	444.9
157.5°	364.6	374.4	393.8	424.7	434.2
160°	370.8	379.5	393.8	419.5	427.0
162.5°	376.9	383.7	394.8	415.4	420.9
165°	383.6	388.6	395.1	411.7	413.0
167.5°	390.5	393.0	396.3	407.4	408.4
170°	392.5	395.0	396.3	405.3	405.3
172.5°	394.5	396.0	396.3	403.2	403.2
175°	397.6	398.9	396.3	401.4	400.2
177.5°	398.6	398.6	395.6	399.6	397.6
180°	397.6	397.6	397.6	397.6	397.6

(END OF REPORT)