

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562955

Luminaire Tested: **SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562955  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10259.3 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 92.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562955  
CATALOG NUMBER: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562955

CATALOG NUMBER: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	81	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11321	11321	11321
5°	11406	11332	11290
10°	11378	11325	11293
15°	11318	11318	11307
20°	11244	11277	11277
25°	11138	11218	11184
30°	11002	11135	11087
35°	10838	11005	10927
40°	10659	10810	10700
45°	10465	10540	10376
50°	10192	10192	10029
55°	9868	9740	9594
60°	9392	9203	9056
65°	8681	8507	8433
70°	7600	7661	7631
75°	6115	6763	6804
80°	4346	5735	5795
85°	2646	4813	4813



TEST NUMBER: P562955

CATALOG NUMBER: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.2	1.7
10°-20°	499.9	4.9
20°-30°	757.0	7.4
30°-40°	907.5	8.8
40°-50°	925.3	9.0
50°-60°	807.8	7.9
60°-70°	578.3	5.6
70°-80°	297.9	2.9
80°-90°	77.0	0.8
90°-100°	377.3	3.7
100°-110°	1041.6	10.2
110°-120°	1074.2	10.5
120°-130°	863.2	8.4
130°-140°	678.4	6.6
140°-150°	520.3	5.1
150°-160°	373.9	3.6
160°-170°	228.7	2.2
170°-180°	77.1	0.8
0°-30°	1431.0	13.9
0°-40°	2338.5	22.8
0°-60°	4071.6	39.7
0°-90°	5024.7	49.0
90°-120°	2493.0	24.3
90°-150°	4554.9	44.4
90°-180°	5235.0	51.0
0°-180°	10259.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1840	1840	1840	1840	1840	
5°	1847	1829	1835	1830	1829	175
15°	1777	1762	1777	1777	1776	501
25°	1641	1629	1653	1648	1648	755
35°	1443	1440	1466	1455	1455	903
45°	1203	1200	1212	1196	1193	926
55°	920	909	908	895	895	820
65°	596	583	584	579	579	590
75°	257	269	285	286	286	278
85°	38	58	68	70	68	51
90°	3	5	10	12	13	5
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P562955

CATALOG NUMBER: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1840.5	1840.5	1840.5	1840.5	1840.5
2.5°	1851.4	1835.4	1840.5	1836.2	1829.6
5°	1847.3	1829.0	1835.4	1830.2	1828.6
7.5°	1834.0	1815.7	1824.1	1820.7	1819.0
10°	1821.7	1803.4	1813.2	1809.8	1808.1
12.5°	1805.4	1788.4	1799.6	1796.2	1795.8
15°	1777.4	1762.4	1777.4	1777.4	1775.7
17.5°	1742.3	1728.7	1744.7	1745.7	1744.7
20°	1717.8	1702.8	1722.9	1721.2	1722.9
22.5°	1687.8	1675.5	1697.0	1692.6	1694.3
25°	1641.1	1629.4	1653.0	1647.9	1647.9
27.5°	1585.9	1577.6	1603.3	1597.8	1597.8
30°	1549.1	1540.7	1567.8	1561.0	1561.0
32.5°	1508.2	1502.5	1528.3	1520.1	1520.1
35°	1443.4	1440.1	1465.6	1455.3	1455.3
37.5°	1376.6	1373.6	1396.7	1384.4	1380.4
40°	1327.5	1325.9	1346.3	1332.6	1332.6
42.5°	1278.5	1276.8	1294.5	1278.1	1278.1
45°	1203.1	1199.8	1211.7	1196.2	1192.9
47.5°	1121.0	1117.7	1125.1	1108.3	1106.7
50°	1065.1	1061.8	1065.1	1049.7	1048.1
52.5°	1007.8	1001.8	1002.4	987.0	986.7
55°	920.2	908.6	908.3	894.7	894.7
57.5°	827.5	812.2	813.6	801.9	800.3
60°	763.5	746.8	748.1	737.9	736.2
62.5°	700.7	681.4	685.4	673.8	673.5
65°	596.5	583.1	584.5	579.4	579.4
67.5°	496.2	483.9	492.8	488.7	488.4
70°	422.6	414.3	426.0	426.0	424.3
72.5°	354.5	354.1	368.8	368.8	369.8
75°	257.3	269.0	284.6	286.3	286.3
77.5°	171.8	192.4	209.6	210.3	210.0
80°	122.7	146.0	161.9	165.3	163.6
82.5°	83.2	107.8	121.0	124.4	122.7
85°	37.5	57.5	68.2	69.8	68.2
87.5°	11.4	23.9	29.3	29.5	27.1
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6



TEST NUMBER: P562955

CATALOG NUMBER: SQ4-PC3-100U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)