

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937113

Luminaire Tested: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937113
REPORT IS A COMBINATION OF REPORTS P933494 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16206.0 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 127.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937113
CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45													
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37													
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30													
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25													
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21													
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17													
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15													
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13													
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11													
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10													
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2886	2886	2886
5°	2820	3336	3879
10°	2559	4865	6431
15°	2176	6357	7765
20°	1772	7369	7914
25°	1479	7713	7753
30°	1248	7764	7739
35°	1104	7637	7939
40°	962	7471	8146
45°	872	7351	8178
50°	800	7243	8042
55°	767	7084	7686
60°	787	6776	7123
65°	820	6306	6350
70°	875	5503	5364
75°	974	4491	4186
80°	1072	3118	2820
85°	972	1657	1444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8178 cd/sqm



TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.7	0.7
10°-20°	534.9	3.3
20°-30°	935.6	5.8
30°-40°	1204.5	7.4
40°-50°	1345.3	8.3
50°-60°	1288.5	8.0
60°-70°	1021.2	6.3
70°-80°	600.4	3.7
80°-90°	172.1	1.1
90°-100°	675.4	4.2
100°-110°	1775.8	11.0
110°-120°	1841.3	11.4
120°-130°	1476.9	9.1
130°-140°	1158.9	7.2
140°-150°	889.5	5.5
150°-160°	640.6	4.0
160°-170°	391.9	2.4
170°-180°	132.4	0.8
0°-30°	1591.3	9.8
0°-40°	2795.7	17.3
0°-60°	5429.6	33.5
0°-90°	7223.3	44.6
90°-120°	4292.5	26.5
90°-150°	7817.8	48.2
90°-180°	8983.0	55.4
0°-180°	16206.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	909	975	1098	1242	1287	84
15°	681	1257	2118	2568	2649	190
25°	435	1425	2523	2634	2637	200
35°	294	1362	2376	2511	2610	184
45°	201	1086	2100	2406	2514	155
55°	144	690	1782	2070	2127	131
65°	114	366	1323	1488	1509	113
75°	84	225	726	798	801	88
85°	30	69	180	198	201	32
90°	9	26	71	35	35	10
95°	89	350	1163	600	408	99
105°	320	484	1963	2981	2781	339
115°	568	690	1573	3137	3580	561
125°	790	886	1430	2417	2851	702
135°	942	1037	1386	1951	2212	729
145°	1093	1162	1368	1665	1795	685
155°	1235	1269	1368	1502	1546	567
165°	1333	1350	1368	1422	1440	376
175°	1386	1386	1377	1395	1395	132
180°	1386	1386	1386	1386	1386	



TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	933.0	933.0	933.0	933.0	933.0	933.0	933.0	933.0	933.0	933.0	933.0
2.5°	933.0	933.0	939.0	942.0	948.0	951.0	957.0	963.0	981.0	984.0	990.0
5°	909.0	921.0	960.0	975.0	1017.0	1074.0	1098.0	1137.1	1218.1	1242.1	1257.1
7.5°	873.0	900.0	996.0	1020.0	1125.0	1275.1	1338.1	1422.1	1551.1	1614.1	1665.1
10°	816.0	873.0	1044.0	1101.0	1272.1	1500.1	1617.1	1734.1	1929.1	2016.1	2049.1
12.5°	753.0	846.0	1095.0	1173.1	1419.1	1752.1	1893.1	2022.1	2244.1	2361.1	2379.1
15°	681.0	807.0	1143.1	1257.1	1575.1	1962.1	2118.1	2277.1	2484.1	2568.1	2589.1
17.5°	618.0	777.0	1188.1	1308.1	1695.1	2151.1	2310.1	2442.1	2610.1	2667.1	2682.1
20°	540.0	729.0	1218.1	1374.1	1821.1	2289.1	2442.1	2544.1	2658.1	2694.1	2700.1
22.5°	483.0	678.0	1236.1	1398.1	1905.1	2373.1	2502.1	2583.1	2661.1	2673.1	2676.1
25°	435.0	621.0	1233.1	1425.1	1977.1	2424.1	2523.1	2583.1	2628.1	2634.1	2634.1
27.5°	390.0	558.0	1221.1	1431.1	2031.1	2436.1	2514.1	2556.1	2577.1	2589.1	2589.1
30°	351.0	498.0	1191.1	1419.1	2055.1	2424.1	2487.1	2508.1	2529.1	2547.1	2556.1
32.5°	321.0	441.0	1146.1	1395.1	2058.1	2394.1	2439.1	2451.1	2481.1	2523.1	2538.1
35°	294.0	384.0	1095.0	1362.1	2040.1	2346.1	2376.1	2388.1	2448.1	2511.1	2532.1
37.5°	267.0	342.0	1029.0	1305.1	2013.1	2289.1	2310.1	2331.1	2424.1	2499.1	2523.1
40°	240.0	306.0	951.0	1242.1	1971.1	2220.1	2238.1	2271.1	2394.1	2481.1	2505.1
42.5°	219.0	276.0	867.0	1176.1	1917.1	2142.1	2169.1	2217.1	2358.1	2451.1	2478.1
45°	201.0	246.0	777.0	1086.0	1848.1	2061.1	2100.1	2166.1	2316.1	2406.1	2430.1
47.5°	183.0	225.0	684.0	993.0	1773.1	1980.1	2031.1	2106.1	2259.1	2346.1	2367.1
50°	168.0	204.0	591.0	894.0	1692.1	1893.1	1953.1	2031.1	2187.1	2268.1	2295.1
52.5°	156.0	186.0	504.0	795.0	1599.1	1803.1	1872.1	1953.1	2100.1	2178.1	2196.1
55°	144.0	171.0	429.0	690.0	1503.1	1707.1	1782.1	1860.1	2004.1	2070.1	2082.1
57.5°	138.0	159.0	366.0	591.0	1401.1	1599.1	1683.1	1755.1	1890.1	1941.1	1953.1
60°	129.0	150.0	318.0	507.0	1290.1	1497.1	1569.1	1641.1	1755.1	1797.1	1806.1
62.5°	120.0	144.0	282.0	426.0	1176.1	1377.1	1449.1	1515.1	1611.1	1641.1	1653.1
65°	114.0	138.0	255.0	366.0	1059.0	1251.1	1323.1	1380.1	1458.1	1488.1	1494.1
67.5°	108.0	132.0	234.0	315.0	942.0	1125.0	1179.1	1233.1	1293.1	1323.1	1326.1
70°	99.0	126.0	216.0	279.0	822.0	981.0	1026.0	1083.0	1131.0	1146.1	1155.1
72.5°	93.0	117.0	204.0	252.0	699.0	843.0	885.0	918.0	960.0	975.0	975.0
75°	84.0	105.0	192.0	225.0	573.0	690.0	726.0	759.0	792.0	798.0	789.0
77.5°	75.0	93.0	165.0	189.0	447.0	546.0	576.0	594.0	621.0	627.0	630.0
80°	63.0	81.0	129.0	147.0	324.0	402.0	423.0	438.0	462.0	462.0	468.0
82.5°	48.0	63.0	93.0	105.0	219.0	276.0	294.0	303.0	318.0	318.0	318.0
85°	30.0	39.0	60.0	69.0	132.0	168.0	180.0	183.0	195.0	198.0	198.0
87.5°	15.0	21.0	39.0	42.0	69.0	87.0	87.0	93.0	93.0	90.0	87.0
90°	9.3	16.7	24.1	26.0	40.9	60.8	70.7	62.8	47.1	35.3	35.3
92.5°	37.2	100.4	163.7	179.5	252.3	349.4	398.0	348.8	250.5	176.7	169.7
95°	89.3	205.0	320.8	349.7	620.9	982.6	1163.4	1038.2	787.7	599.8	578.5
97.5°	154.4	256.5	358.6	384.1	836.4	1439.4	1740.9	1661.7	1503.4	1384.7	1344.2
100°	204.6	297.2	389.8	412.9	914.8	1583.9	1918.5	1924.3	1935.9	1944.6	1896.3
102.5°	247.4	333.8	420.1	441.7	950.7	1629.4	1968.8	2069.6	2271.3	2422.6	2381.3
105°	319.9	393.1	466.2	484.5	977.4	1634.6	1963.2	2189.3	2641.5	2980.6	2958.4
107.5°	394.3	462.5	530.7	547.8	982.4	1561.9	1851.6	2167.0	2797.7	3270.7	3276.1
110°	444.5	506.1	567.7	583.1	974.9	1497.4	1758.6	2111.2	2816.3	3345.1	3368.2



TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	493.8	552.5	611.2	625.9	975.3	1441.1	1674.0	2034.8	2756.5	3297.7	3333.2
115°	568.2	622.3	676.5	690.0	984.2	1376.5	1572.6	1920.2	2615.4	3136.8	3186.1
117.5°	641.7	690.9	740.0	752.3	1002.5	1336.0	1502.8	1816.5	2443.9	2914.5	2969.2
120°	684.5	730.8	777.0	788.6	1017.4	1322.4	1474.9	1761.5	2334.8	2764.8	2817.9
122.5°	726.3	773.0	819.7	831.4	1038.8	1315.3	1453.5	1711.6	2227.9	2615.1	2667.5
125°	790.5	833.1	875.7	886.3	1067.6	1309.4	1430.3	1649.6	2088.1	2417.0	2465.3
127.5°	842.6	885.6	928.6	939.3	1096.5	1306.0	1410.8	1599.1	1975.6	2258.0	2298.7
130°	870.5	916.8	963.0	974.6	1117.5	1308.0	1403.3	1570.9	1906.1	2157.5	2195.1
132.5°	899.3	945.6	991.8	1003.4	1134.5	1309.4	1396.8	1546.8	1846.9	2072.0	2105.7
135°	942.1	984.2	1026.4	1036.9	1153.2	1308.2	1385.7	1511.3	1762.6	1951.1	1980.1
137.5°	985.8	1027.5	1069.3	1079.7	1181.1	1316.2	1383.8	1490.0	1702.5	1861.8	1885.6
140°	1022.0	1060.4	1098.9	1108.5	1198.1	1317.6	1377.3	1469.1	1652.6	1790.2	1812.4
142.5°	1049.9	1085.5	1121.0	1129.9	1212.4	1322.3	1377.3	1457.9	1619.1	1740.0	1759.1
145°	1092.7	1123.7	1154.7	1162.5	1231.0	1322.3	1368.0	1433.9	1565.8	1664.7	1679.2
147.5°	1135.5	1165.7	1195.9	1203.4	1258.3	1331.4	1368.0	1419.9	1523.6	1601.4	1613.4
150°	1163.4	1190.7	1218.0	1224.8	1272.5	1336.2	1368.0	1411.8	1499.4	1565.1	1574.8
152.5°	1192.2	1212.9	1233.5	1238.7	1281.8	1339.3	1368.0	1405.4	1480.2	1536.3	1543.6
155°	1235.0	1250.3	1265.6	1269.4	1302.3	1346.1	1368.0	1397.8	1457.3	1501.9	1506.8
157.5°	1266.6	1281.5	1296.4	1300.1	1322.7	1352.9	1368.0	1391.1	1437.4	1472.1	1475.5
160°	1288.0	1299.6	1311.2	1314.1	1332.1	1356.0	1368.0	1387.8	1427.5	1457.3	1459.3
162.5°	1309.4	1318.1	1326.7	1328.9	1341.9	1359.3	1368.0	1384.7	1418.2	1443.3	1445.2
165°	1332.7	1340.5	1348.3	1350.3	1356.2	1364.1	1368.0	1380.0	1403.9	1421.9	1423.9
167.5°	1354.0	1357.7	1361.5	1362.4	1367.4	1374.0	1377.3	1385.1	1400.8	1412.6	1413.4
170°	1368.0	1371.7	1375.5	1376.4	1376.7	1377.1	1377.3	1385.1	1400.8	1412.6	1412.6
172.5°	1375.4	1376.2	1377.1	1377.3	1377.3	1377.3	1377.3	1383.5	1395.9	1405.2	1404.5
175°	1385.7	1385.7	1385.7	1385.7	1382.9	1379.2	1377.3	1381.2	1389.1	1395.0	1395.0
177.5°	1385.7	1385.7	1385.7	1385.7	1383.5	1380.6	1379.2	1382.3	1388.5	1393.1	1392.3
180°	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7	1385.7



TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	933.0	933.0
2.5°	996.0	990.0
5°	1281.1	1287.1
7.5°	1725.1	1722.1
10°	2145.1	2172.1
12.5°	2451.1	2457.1
15°	2637.1	2649.1
17.5°	2709.1	2712.1
20°	2712.1	2706.1
22.5°	2679.1	2673.1
25°	2640.1	2637.1
27.5°	2604.1	2607.1
30°	2589.1	2598.1
32.5°	2589.1	2604.1
35°	2595.1	2610.1
37.5°	2592.1	2610.1
40°	2580.1	2601.1
42.5°	2547.1	2562.1
45°	2496.1	2514.1
47.5°	2430.1	2442.1
50°	2346.1	2358.1
52.5°	2241.1	2244.1
55°	2115.1	2127.1
57.5°	1980.1	1983.1
60°	1830.1	1839.1
62.5°	1671.1	1671.1
65°	1503.1	1509.1
67.5°	1329.1	1344.1
70°	1152.1	1155.1
72.5°	978.0	978.0
75°	798.0	801.0
77.5°	627.0	627.0
80°	465.0	468.0
82.5°	321.0	327.0
85°	201.0	201.0
87.5°	93.0	84.0
90°	35.3	35.3
92.5°	141.6	113.5
95°	493.4	408.3
97.5°	1182.2	1020.2
100°	1703.3	1510.3
102.5°	2215.9	2050.6
105°	2869.5	2780.6
107.5°	3297.6	3319.1
110°	3460.8	3553.4



TEST NUMBER: P937113

CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3475.4	3617.6
115°	3383.2	3580.4
117.5°	3187.8	3406.5
120°	3030.4	3242.8
122.5°	2877.0	3086.6
125°	2658.3	2851.3
127.5°	2461.6	2624.4
130°	2345.6	2496.1
132.5°	2240.4	2375.2
135°	2096.3	2212.4
137.5°	1980.6	2075.7
140°	1901.3	1990.1
142.5°	1835.6	1912.0
145°	1737.0	1794.8
147.5°	1661.3	1709.3
150°	1613.7	1652.6
152.5°	1573.0	1602.3
155°	1526.2	1545.6
157.5°	1489.2	1502.8
160°	1467.1	1474.9
162.5°	1452.6	1460.1
165°	1431.7	1439.6
167.5°	1416.8	1420.1
170°	1412.6	1412.6
172.5°	1401.6	1398.7
175°	1395.0	1395.0
177.5°	1389.0	1385.7
180°	1385.7	1385.7



TEST NUMBER: P937113
 CATALOG NUMBER: SQ4-FB-075U-075D-835-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.18	5.02	5.17	6.03	7.38	17.37	18.22	18.36	19.23	20.57
	3H	4.88	5.64	5.88	6.66	8.03	19.21	19.97	20.22	20.99	22.36
	4H	5.18	5.90	6.20	6.92	8.29	19.86	20.58	20.88	21.61	22.98
	6H	5.43	6.09	6.46	7.12	8.50	20.29	20.96	21.32	21.99	23.37
	8H	5.49	6.13	6.53	7.17	8.55	20.42	21.05	21.45	22.10	23.48
	12H	5.51	6.11	6.55	7.15	8.56	20.49	21.09	21.53	22.13	23.53
4H	2H	11.40	12.12	12.42	13.14	14.51	17.64	18.36	18.66	19.39	20.76
	3H	12.96	13.57	14.00	14.62	16.00	19.69	20.29	20.72	21.35	22.73
	4H	13.06	13.61	14.10	14.65	16.06	20.46	21.01	21.50	22.06	23.46
	6H	13.07	13.54	14.12	14.61	16.01	21.00	21.48	22.05	22.55	23.95
	8H	13.04	13.49	14.10	14.55	15.97	21.17	21.61	22.22	22.67	24.09
	12H	13.00	13.40	14.07	14.48	15.90	21.26	21.67	22.33	22.74	24.16
8H	4H	14.50	14.95	15.56	16.01	17.43	20.52	20.96	21.57	22.02	23.44
	6H	14.75	15.12	15.82	16.22	17.63	21.15	21.52	22.23	22.62	24.04
	8H	14.76	15.09	15.85	16.17	17.61	21.37	21.70	22.46	22.78	24.22
	12H	14.73	15.02	15.82	16.10	17.57	21.52	21.81	22.61	22.89	24.36
12H	4H	14.65	15.05	15.72	16.13	17.55	20.47	20.87	21.54	21.95	23.37
	6H	15.01	15.33	16.09	16.42	17.85	21.13	21.46	22.22	22.54	23.98
	8H	15.07	15.36	16.16	16.44	17.92	21.37	21.65	22.45	22.73	24.21