

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563099

Luminaire Tested: **SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563099
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10418.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563099
CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563099

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5781	5781	5781
5°	5824	5787	5765
10°	5810	5783	5767
15°	5779	5779	5774
20°	5742	5759	5759
25°	5687	5729	5711
30°	5618	5686	5661
35°	5535	5620	5580
40°	5443	5520	5464
45°	5344	5382	5298
50°	5205	5205	5121
55°	5039	4974	4900
60°	4795	4699	4624
65°	4433	4344	4307
70°	3881	3911	3897
75°	3123	3453	3474
80°	2221	2929	2958
85°	1348	2456	2456



TEST NUMBER: P563099

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	0.9
10°-20°	255.2	2.4
20°-30°	386.5	3.7
30°-40°	463.4	4.4
40°-50°	472.5	4.5
50°-60°	412.5	4.0
60°-70°	295.3	2.8
70°-80°	152.1	1.5
80°-90°	41.0	0.4
90°-100°	565.9	5.4
100°-110°	1530.2	14.7
110°-120°	1608.7	15.4
120°-130°	1306.7	12.5
130°-140°	1025.0	9.8
140°-150°	786.7	7.6
150°-160°	565.8	5.4
160°-170°	345.6	3.3
170°-180°	116.5	1.1
0°-30°	730.7	7.0
0°-40°	1194.1	11.5
0°-60°	2079.1	20.0
0°-90°	2567.5	24.6
90°-120°	3704.8	35.6
90°-150°	6823.3	65.5
90°-180°	7851.0	75.4
0°-180°	10418.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	940	940	940	940	940	
5°	943	934	937	935	934	90
15°	908	900	908	908	907	256
25°	838	832	844	842	842	386
35°	737	735	748	743	743	461
45°	614	613	619	611	609	473
55°	470	464	464	457	457	419
65°	305	298	298	296	296	301
75°	131	137	145	146	146	142
85°	19	29	35	36	35	26
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	

TEST NUMBER: P563099

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	939.8	939.8	939.8	939.8	939.8
2.5°	945.4	937.2	939.8	937.6	934.2
5°	943.3	933.9	937.2	934.6	933.7
7.5°	936.5	927.1	931.5	929.7	928.8
10°	930.2	920.9	925.9	924.1	923.3
12.5°	921.9	913.2	918.9	917.2	917.0
15°	907.6	900.0	907.6	907.6	906.7
17.5°	889.7	882.7	890.9	891.4	890.9
20°	877.2	869.5	879.8	878.9	879.8
22.5°	861.8	855.5	866.5	864.3	865.1
25°	838.0	832.0	844.1	841.5	841.5
27.5°	809.8	805.5	818.7	815.9	815.9
30°	791.0	786.8	800.6	797.1	797.1
32.5°	770.1	767.2	780.4	776.2	776.2
35°	737.1	735.4	748.4	743.1	743.1
37.5°	702.9	701.4	713.2	706.9	704.9
40°	677.9	677.0	687.5	680.5	680.5
42.5°	652.8	652.0	661.0	652.6	652.6
45°	614.4	612.7	618.7	610.8	609.1
47.5°	572.4	570.7	574.5	566.0	565.1
50°	543.9	542.2	543.9	536.0	535.2
52.5°	514.6	511.6	511.8	504.0	503.8
55°	469.9	463.9	463.8	456.9	456.9
57.5°	422.6	414.7	415.4	409.5	408.6
60°	389.8	381.3	382.0	376.8	375.9
62.5°	357.8	348.0	350.0	344.1	343.9
65°	304.6	297.8	298.5	295.9	295.9
67.5°	253.4	247.1	251.7	249.6	249.4
70°	215.8	211.6	217.5	217.5	216.7
72.5°	181.0	180.8	188.3	188.3	188.8
75°	131.4	137.4	145.3	146.2	146.2
77.5°	87.7	98.3	107.0	107.4	107.2
80°	62.7	74.6	82.7	84.4	83.5
82.5°	42.5	55.1	61.8	63.5	62.7
85°	19.1	29.4	34.8	35.7	34.8
87.5°	6.1	13.2	17.3	17.6	15.9
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6



TEST NUMBER: P563099

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)