

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937813

Luminaire Tested: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P937813  
REPORT IS A COMBINATION OF REPORTS P933589 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19853.0 lumens  
Efficiency: N/A  
Efficacy: 139.0 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 142.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937813  
CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P937813

CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20				20
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16				16
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	22	20	19	13				13
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11				11
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10				10
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8				8
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7				7
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6				6
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6				6
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5				5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1936	1936	1936
5°	1892	2238	2602
10°	1716	3263	4313
15°	1460	4264	5208
20°	1189	4942	5308
25°	992	5173	5200
30°	837	5207	5190
35°	740	5122	5325
40°	646	5011	5463
45°	585	4930	5485
50°	537	4858	5394
55°	515	4751	5155
60°	527	4545	4777
65°	550	4230	4258
70°	587	3691	3598
75°	653	3012	2807
80°	719	2091	1892
85°	651	1111	968

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 90°  
 Luminance: 5753 cd/sqm



TEST NUMBER: P937813

CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.9	0.4
10°-20°	358.8	1.8
20°-30°	627.5	3.2
30°-40°	807.8	4.1
40°-50°	902.3	4.5
50°-60°	864.2	4.4
60°-70°	684.9	3.4
70°-80°	402.7	2.0
80°-90°	120.7	0.6
90°-100°	1128.1	5.7
100°-110°	2966.0	14.9
110°-120°	3075.4	15.5
120°-130°	2466.8	12.4
130°-140°	1935.6	9.7
140°-150°	1485.6	7.5
150°-160°	1069.9	5.4
160°-170°	654.6	3.3
170°-180°	221.2	1.1
0°-30°	1067.2	5.4
0°-40°	1875.0	9.4
0°-60°	3641.5	18.3
0°-90°	4849.8	24.4
90°-120°	7169.4	36.1
90°-150°	13057.5	65.8
90°-180°	15003.0	75.6
0°-180°	19853.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	626	626	626	626	626	
5°	610	654	736	833	863	56
15°	457	843	1421	1722	1777	127
25°	292	956	1692	1767	1769	134
35°	197	914	1594	1684	1751	123
45°	135	728	1408	1614	1686	104
55°	97	463	1195	1388	1427	88
65°	76	246	887	998	1012	76
75°	56	151	487	535	537	59
85°	20	46	121	133	135	21
90°	16	44	118	59	59	14
95°	149	584	1943	1002	682	166
105°	534	809	3279	4978	4644	566
115°	949	1152	2627	5239	5980	937
125°	1320	1480	2389	4037	4762	1172
135°	1574	1732	2314	3259	3695	1217
145°	1825	1942	2285	2780	2998	1143
155°	2063	2120	2285	2508	2582	948
165°	2226	2255	2285	2375	2404	628
175°	2314	2314	2300	2330	2330	220
180°	2314	2314	2314	2314	2314	



TEST NUMBER: P937813  
 CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8
2.5°	625.8	625.8	629.8	631.8	635.8	637.8	641.9	645.9	658.0	660.0	664.0
5°	609.7	617.7	643.9	653.9	682.1	720.3	736.4	762.6	816.9	833.0	843.1
7.5°	585.5	603.6	668.0	684.1	754.6	855.2	897.4	953.8	1040.3	1082.5	1116.7
10°	547.3	585.5	700.2	738.5	853.1	1006.1	1084.5	1163.0	1293.8	1352.2	1374.3
12.5°	505.0	567.4	734.4	786.7	951.7	1175.1	1269.7	1356.2	1505.1	1583.6	1595.6
15°	456.8	541.3	766.6	843.1	1056.4	1315.9	1420.6	1527.2	1666.1	1722.4	1736.5
17.5°	414.5	521.1	796.8	877.3	1136.9	1442.7	1549.3	1637.9	1750.6	1788.8	1798.9
20°	362.2	489.0	816.9	921.6	1221.4	1535.3	1637.9	1706.3	1782.8	1806.9	1810.9
22.5°	324.0	454.7	829.0	937.7	1277.7	1591.6	1678.1	1732.5	1784.8	1792.8	1794.8
25°	291.8	416.5	827.0	955.8	1326.0	1625.8	1692.2	1732.5	1762.6	1766.7	1766.7
27.5°	261.6	374.3	818.9	959.8	1362.2	1633.9	1686.2	1714.3	1728.4	1736.5	1736.5
30°	235.4	334.0	798.8	951.7	1378.3	1625.8	1668.1	1682.2	1696.2	1708.3	1714.3
32.5°	215.3	295.8	768.6	935.6	1380.3	1605.7	1635.9	1643.9	1664.0	1692.2	1702.3
35°	197.2	257.6	734.4	913.5	1368.3	1573.5	1593.6	1601.7	1641.9	1684.2	1698.2
37.5°	179.1	229.4	690.2	875.3	1350.1	1535.3	1549.3	1563.4	1625.8	1676.1	1692.2
40°	161.0	205.2	637.8	833.0	1322.0	1489.0	1501.1	1523.2	1605.7	1664.0	1680.1
42.5°	146.9	185.1	581.5	788.8	1285.8	1436.7	1454.8	1487.0	1581.5	1643.9	1662.0
45°	134.8	165.0	521.1	728.4	1239.5	1382.3	1408.5	1452.8	1553.4	1613.7	1629.8
47.5°	122.7	150.9	458.8	666.0	1189.2	1328.0	1362.2	1412.5	1515.1	1573.5	1587.6
50°	112.7	136.8	396.4	599.6	1134.8	1269.7	1309.9	1362.2	1466.9	1521.2	1539.3
52.5°	104.6	124.8	338.0	533.2	1072.5	1209.3	1255.6	1309.9	1408.5	1460.8	1472.9
55°	96.6	114.7	287.7	462.8	1008.1	1144.9	1195.2	1247.5	1344.1	1388.4	1396.4
57.5°	92.6	106.6	245.5	396.4	939.7	1072.5	1128.8	1177.1	1267.6	1301.9	1309.9
60°	86.5	100.6	213.3	340.1	865.2	1004.1	1052.4	1100.6	1177.1	1205.3	1211.3
62.5°	80.5	96.6	189.1	285.7	788.8	923.6	971.9	1016.1	1080.5	1100.6	1108.7
65°	76.5	92.6	171.0	245.5	710.3	839.1	887.4	925.6	977.9	998.0	1002.0
67.5°	72.4	88.5	156.9	211.3	631.8	754.6	790.8	827.0	867.2	887.4	889.4
70°	66.4	84.5	144.9	187.1	551.3	658.0	688.2	726.4	758.6	768.6	774.7
72.5°	62.4	78.5	136.8	169.0	468.8	565.4	593.6	615.7	643.9	653.9	653.9
75°	56.3	70.4	128.8	150.9	384.3	462.8	486.9	509.1	531.2	535.2	529.2
77.5°	50.3	62.4	110.7	126.8	299.8	366.2	386.3	398.4	416.5	420.5	422.5
80°	42.3	54.3	86.5	98.6	217.3	269.6	283.7	293.8	309.9	309.9	313.9
82.5°	32.2	42.3	62.4	70.4	146.9	185.1	197.2	203.2	213.3	213.3	213.3
85°	20.1	26.2	40.2	46.3	88.5	112.7	120.7	122.7	130.8	132.8	132.8
87.5°	10.1	14.1	26.2	28.2	46.3	58.4	58.4	62.4	62.4	60.4	58.4
90°	15.5	27.9	40.4	43.5	68.3	101.4	118.0	104.9	78.7	59.0	59.0
92.5°	62.1	167.7	273.4	299.8	421.5	583.7	664.8	582.6	418.3	295.1	283.4
95°	149.1	342.4	535.7	584.0	1037.0	1641.1	1943.1	1733.9	1315.6	1001.9	966.3
97.5°	257.8	428.3	598.9	641.5	1396.9	2404.1	2907.7	2775.5	2511.1	2312.8	2245.1
100°	341.7	496.4	651.0	689.7	1527.9	2645.6	3204.4	3214.1	3233.4	3247.9	3167.3
102.5°	413.2	557.5	701.7	737.8	1588.0	2721.5	3288.3	3456.7	3793.6	4046.3	3977.3
105°	534.3	656.5	778.7	809.3	1632.5	2730.1	3278.9	3656.5	4411.8	4978.2	4941.1
107.5°	658.6	772.5	886.4	914.9	1640.8	2608.7	3092.6	3619.3	4672.7	5462.8	5471.8
110°	742.5	845.3	948.2	973.9	1628.3	2500.9	2937.2	3526.1	4703.8	5587.1	5625.8



TEST NUMBER: P937813

CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	824.8	922.8	1020.8	1045.3	1628.8	2406.9	2795.9	3398.6	4603.9	5507.9	5567.3
115°	949.0	1039.4	1129.9	1152.5	1643.9	2299.0	2626.6	3207.2	4368.3	5239.2	5321.5
117.5°	1071.8	1153.9	1236.1	1256.6	1674.4	2231.5	2510.1	3034.1	4082.0	4867.9	4959.2
120°	1143.2	1220.5	1297.9	1317.2	1699.3	2208.8	2463.5	2942.3	3899.8	4617.9	4706.6
122.5°	1213.1	1291.1	1369.1	1388.6	1735.0	2196.9	2427.8	2858.9	3721.1	4367.8	4455.3
125°	1320.3	1391.4	1462.5	1480.3	1783.2	2187.0	2388.9	2755.1	3487.6	4036.9	4117.5
127.5°	1407.3	1479.1	1550.9	1568.8	1831.3	2181.3	2356.3	2670.7	3299.6	3771.3	3839.3
130°	1453.9	1531.2	1608.5	1627.8	1866.5	2184.8	2343.9	2623.8	3183.7	3603.6	3666.4
132.5°	1502.0	1579.3	1656.7	1676.0	1895.0	2187.0	2333.0	2583.6	3084.8	3460.7	3517.0
135°	1573.5	1643.9	1714.3	1731.9	1926.1	2185.0	2314.4	2524.3	2944.0	3258.8	3307.3
137.5°	1646.5	1716.2	1785.9	1803.3	1972.6	2198.4	2311.3	2488.7	2843.5	3109.6	3149.3
140°	1707.0	1771.2	1835.4	1851.5	2001.1	2200.6	2300.4	2453.6	2760.1	2990.0	3027.1
142.5°	1753.6	1813.0	1872.4	1887.2	2024.9	2208.6	2300.4	2435.0	2704.3	2906.2	2938.1
145°	1825.1	1876.9	1928.7	1941.6	2056.0	2208.6	2284.9	2395.0	2615.2	2780.3	2804.5
147.5°	1896.5	1946.9	1997.3	2009.9	2101.6	2223.8	2284.9	2371.5	2544.8	2674.7	2694.7
150°	1943.1	1988.7	2034.3	2045.7	2125.4	2231.7	2284.9	2358.1	2504.4	2614.1	2630.3
152.5°	1991.3	2025.8	2060.4	2069.0	2141.0	2236.9	2284.9	2347.4	2472.3	2566.0	2578.3
155°	2062.7	2088.3	2113.8	2120.2	2175.1	2248.3	2284.9	2334.6	2434.0	2508.5	2516.6
157.5°	2115.6	2140.4	2165.3	2171.5	2209.3	2259.7	2284.9	2323.5	2400.8	2458.8	2464.5
160°	2151.3	2170.6	2190.0	2194.8	2224.8	2264.9	2284.9	2318.0	2384.3	2434.0	2437.3
162.5°	2187.0	2201.5	2216.0	2219.6	2241.4	2270.4	2284.9	2312.9	2368.8	2410.7	2413.8
165°	2225.8	2238.9	2252.0	2255.3	2265.2	2278.3	2284.9	2304.9	2344.9	2374.9	2378.2
167.5°	2261.6	2267.8	2274.0	2275.5	2283.8	2294.9	2300.4	2313.5	2339.7	2359.4	2360.8
170°	2284.9	2291.1	2297.3	2298.8	2299.3	2300.0	2300.4	2313.5	2339.7	2359.4	2359.4
172.5°	2297.3	2298.7	2300.1	2300.4	2300.4	2300.4	2300.4	2310.8	2331.5	2347.0	2345.8
175°	2314.4	2314.4	2314.4	2314.4	2309.7	2303.5	2300.4	2307.0	2320.1	2329.9	2329.9
177.5°	2314.4	2314.4	2314.4	2314.4	2310.8	2305.9	2303.5	2308.7	2319.0	2326.8	2325.4
180°	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4	2314.4



TEST NUMBER: P937813

CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	625.8	625.8
2.5°	668.0	664.0
5°	859.2	863.2
7.5°	1157.0	1155.0
10°	1438.7	1456.8
12.5°	1643.9	1647.9
15°	1768.7	1776.7
17.5°	1817.0	1819.0
20°	1819.0	1815.0
22.5°	1796.8	1792.8
25°	1770.7	1768.7
27.5°	1746.5	1748.6
30°	1736.5	1742.5
32.5°	1736.5	1746.5
35°	1740.5	1750.6
37.5°	1738.5	1750.6
40°	1730.4	1744.5
42.5°	1708.3	1718.4
45°	1674.1	1686.2
47.5°	1629.8	1637.9
50°	1573.5	1581.5
52.5°	1503.1	1505.1
55°	1418.6	1426.6
57.5°	1328.0	1330.0
60°	1227.4	1233.4
62.5°	1120.8	1120.8
65°	1008.1	1012.1
67.5°	891.4	901.4
70°	772.7	774.7
72.5°	656.0	656.0
75°	535.2	537.2
77.5°	420.5	420.5
80°	311.9	313.9
82.5°	215.3	219.3
85°	134.8	134.8
87.5°	62.4	56.3
90°	59.0	59.0
92.5°	236.4	189.5
95°	824.1	681.9
97.5°	1974.5	1703.9
100°	2844.9	2522.5
102.5°	3701.1	3425.0
105°	4792.7	4644.3
107.5°	5507.7	5543.6
110°	5780.4	5935.0





TEST NUMBER: P937813

CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	5804.7	6042.2
115°	5650.8	5980.1
117.5°	5324.4	5689.6
120°	5061.4	5416.2
122.5°	4805.3	5155.3
125°	4439.9	4762.3
127.5°	4111.3	4383.3
130°	3917.7	4169.0
132.5°	3742.0	3967.0
135°	3501.2	3695.2
137.5°	3308.1	3466.9
140°	3175.6	3324.0
142.5°	3065.8	3193.5
145°	2901.1	2997.8
147.5°	2774.8	2854.9
150°	2695.3	2760.2
152.5°	2627.3	2676.3
155°	2549.1	2581.5
157.5°	2487.3	2510.1
160°	2450.4	2463.5
162.5°	2426.2	2438.6
165°	2391.3	2404.5
167.5°	2366.3	2371.8
170°	2359.4	2359.4
172.5°	2340.9	2336.1
175°	2329.9	2329.9
177.5°	2319.9	2314.4
180°	2314.4	2314.4



TEST NUMBER: P937813  
 CATALOG NUMBER: SQ4-FB-125U-050D-835-1D-UNV-STD-W-12

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.29	0.98	1.44	2.11	3.71	13.48	14.17	14.63	15.31	16.90
	3H	0.98	1.60	2.13	2.74	4.35	15.31	15.93	16.47	17.07	18.68
	4H	1.27	1.86	2.43	3.00	4.62	15.95	16.54	17.12	17.69	19.30
	6H	1.51	2.05	2.68	3.20	4.82	16.38	16.92	17.55	18.07	19.69
	8H	1.58	2.09	2.75	3.25	4.87	16.50	17.01	17.67	18.17	19.79
	12H	1.59	2.07	2.76	3.23	4.87	16.56	17.05	17.74	18.21	19.84
4H	2H	7.49	8.08	8.66	9.22	10.84	13.73	14.32	14.90	15.47	17.08
	3H	9.04	9.53	10.22	10.70	12.33	15.77	16.26	16.94	17.43	19.05
	4H	9.13	9.58	10.31	10.74	12.38	16.53	16.98	17.71	18.14	19.78
	6H	9.13	9.52	10.31	10.70	12.33	17.06	17.45	18.25	18.63	20.27
	8H	9.10	9.46	10.28	10.64	12.29	17.22	17.59	18.40	18.76	20.41
	12H	9.05	9.38	10.25	10.56	12.22	17.31	17.64	18.51	18.82	20.48
8H	4H	10.56	10.92	11.74	12.10	13.75	16.58	16.94	17.76	18.11	19.76
	6H	10.80	11.09	12.00	12.31	13.96	17.20	17.50	18.40	18.71	20.36
	8H	10.81	11.07	12.02	12.26	13.93	17.42	17.68	18.63	18.87	20.54
	12H	10.77	11.00	11.98	12.19	13.89	17.56	17.79	18.77	18.98	20.68
12H	4H	10.70	11.03	11.89	12.21	13.86	16.52	16.85	17.72	18.03	19.69
	6H	11.05	11.31	12.26	12.51	14.17	17.18	17.44	18.39	18.63	20.30
	8H	11.11	11.34	12.32	12.53	14.23	17.41	17.63	18.62	18.82	20.52