

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563219

Luminaire Tested: **SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563219
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5004.6 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563219
CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563219

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54				
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46				
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39				
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34				
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30				
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27				
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24				
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22				
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8435	8377	8271
40°	8164	8113	8020
45°	7942	7886	7808
50°	7656	7607	7534
55°	7260	7164	7109
60°	6610	6420	6388
65°	5823	5580	5561
70°	5026	4820	4820
75°	4328	4266	4206
80°	3815	3861	3769
85°	2985	3260	3260



TEST NUMBER: P563219

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	2.8
10°-20°	395.0	7.9
20°-30°	591.7	11.8
30°-40°	694.0	13.9
40°-50°	696.2	13.9
50°-60°	593.9	11.9
60°-70°	387.3	7.7
70°-80°	194.3	3.9
80°-90°	54.8	1.1
90°-100°	94.7	1.9
100°-110°	248.9	5.0
110°-120°	258.1	5.2
120°-130°	207.0	4.1
130°-140°	162.4	3.2
140°-150°	124.6	2.5
150°-160°	89.8	1.8
160°-170°	54.9	1.1
170°-180°	18.6	0.4
0°-30°	1125.1	22.5
0°-40°	1819.1	36.3
0°-60°	3109.2	62.1
0°-90°	3745.7	74.8
90°-120°	601.6	12.0
90°-150°	1095.7	21.9
90°-180°	1259.0	25.2
0°-180°	5004.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1463	1463	1463	1463	1463	
5°	1468	1454	1459	1454	1454	139
15°	1412	1398	1404	1399	1396	398
25°	1300	1285	1291	1280	1278	598
35°	1123	1112	1116	1103	1102	702
45°	913	907	907	898	898	703
55°	677	674	668	664	663	602
65°	400	392	383	381	382	399
75°	182	182	180	178	177	198
85°	42	46	46	46	46	50
90°	1	4	10	5	5	3
95°	12	49	163	84	57	14
105°	45	68	275	418	390	48
115°	80	97	220	440	502	79
125°	111	124	200	339	400	98
135°	132	145	194	274	310	102
145°	153	163	192	233	252	96
155°	173	178	192	211	217	80
165°	187	189	192	199	202	53
175°	194	194	193	196	196	18
180°	194	194	194	194	194	

TEST NUMBER: P563219

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.1	1463.1	1463.1	1463.1	1463.1
2.5°	1472.3	1460.3	1463.1	1460.9	1454.9
5°	1468.2	1454.4	1459.2	1454.1	1454.1
7.5°	1458.2	1443.1	1447.9	1442.8	1442.5
10°	1449.0	1433.9	1438.7	1433.5	1432.3
12.5°	1435.6	1420.6	1426.4	1420.2	1420.0
15°	1411.8	1398.0	1404.1	1398.9	1396.4
17.5°	1384.8	1369.8	1377.2	1369.9	1368.9
20°	1364.3	1349.3	1356.6	1346.4	1346.4
22.5°	1339.7	1324.7	1333.0	1319.7	1319.7
25°	1300.2	1285.2	1291.2	1279.7	1278.4
27.5°	1253.3	1238.5	1244.8	1231.7	1231.5
30°	1219.4	1205.6	1213.0	1198.9	1197.6
32.5°	1182.5	1169.7	1175.1	1160.9	1159.7
35°	1123.3	1112.0	1115.6	1102.7	1101.5
37.5°	1060.9	1049.4	1053.5	1042.5	1042.0
40°	1016.8	1009.3	1010.4	1001.4	998.9
42.5°	975.8	967.3	968.4	959.4	958.9
45°	913.0	906.7	906.6	897.6	897.6
47.5°	846.3	841.5	840.1	832.7	832.4
50°	800.1	796.4	795.0	788.6	787.3
52.5°	751.9	750.2	745.8	740.4	740.1
55°	677.0	674.5	668.1	664.2	662.9
57.5°	595.7	590.7	583.4	577.8	578.8
60°	537.3	532.3	521.9	519.3	519.3
62.5°	480.8	474.8	464.4	460.9	462.9
65°	400.1	392.5	383.4	380.9	382.1
67.5°	326.7	320.0	310.1	310.0	309.0
70°	279.5	275.8	268.0	268.0	268.0
72.5°	237.5	235.7	230.0	230.0	229.0
75°	182.1	182.1	179.5	178.2	177.0
77.5°	136.4	136.9	135.7	134.3	132.1
80°	107.7	110.2	109.0	107.7	106.4
82.5°	81.0	83.5	83.3	81.0	80.8
85°	42.3	46.1	46.2	46.2	46.2
87.5°	11.5	16.0	18.4	17.4	18.4
90°	1.2	3.7	10.0	5.0	5.0
92.5°	5.2	25.2	55.8	24.7	15.9
95°	12.5	49.0	163.1	84.1	57.3
97.5°	21.7	53.8	244.0	194.1	142.9
100°	28.6	57.9	268.9	272.5	211.7
102.5°	34.6	61.9	275.9	339.5	287.4
105°	44.8	68.0	275.2	417.7	389.7
107.5°	55.3	76.7	259.5	458.3	465.2
110°	62.3	81.7	246.5	468.8	498.0



TEST NUMBER: P563219

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.2	87.7	234.6	462.2	507.0
115°	79.7	96.7	220.4	439.7	501.8
117.5°	89.9	105.5	210.7	408.5	477.4
120°	95.9	110.5	206.7	387.5	454.4
122.5°	101.8	116.5	203.7	366.6	432.5
125°	110.8	124.2	200.5	338.8	399.7
127.5°	118.0	131.7	197.7	316.4	367.8
130°	122.0	136.6	196.7	302.4	349.9
132.5°	126.0	140.6	195.7	290.3	332.9
135°	132.0	145.4	194.2	273.5	310.0
137.5°	138.2	151.3	194.0	260.9	290.8
140°	143.2	155.4	193.0	250.9	278.9
142.5°	147.2	158.4	193.0	243.8	267.9
145°	153.1	162.9	191.7	233.2	251.5
147.5°	159.1	168.6	191.7	224.5	239.6
150°	163.1	171.6	191.7	219.4	231.6
152.5°	167.1	173.7	191.7	215.4	224.6
155°	173.1	177.9	191.7	210.6	216.6
157.5°	177.5	182.2	191.7	206.3	210.7
160°	180.5	184.2	191.7	204.2	206.7
162.5°	183.5	186.2	191.7	202.3	204.7
165°	186.8	189.2	191.7	199.3	201.7
167.5°	189.7	191.0	193.0	198.0	199.0
170°	191.7	193.0	193.0	198.0	198.0
172.5°	192.7	193.0	193.0	196.9	196.0
175°	194.2	194.2	193.0	195.5	195.5
177.5°	194.2	194.2	193.2	195.2	194.2
180°	194.2	194.2	194.2	194.2	194.2

(END OF REPORT)