

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562773

Luminaire Tested: **SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562773
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23739.4 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 194.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562773
CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562773

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16626	16626	16626
5°	16751	16643	16582
10°	16711	16633	16586
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16477	16425
30°	16159	16354	16283
35°	15918	16162	16050
40°	15655	15876	15715
45°	15370	15479	15240
50°	14969	14969	14729
55°	14493	14306	14091
60°	13794	13516	13301
65°	12749	12495	12385
70°	11163	11252	11207
75°	8982	9934	9993
80°	6383	8421	8512
85°	3885	7064	7064



TEST NUMBER: P562773

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	511.6	2.2
10°-20°	1468.3	6.2
20°-30°	2223.5	9.4
30°-40°	2665.7	11.2
40°-50°	2718.1	11.4
50°-60°	2372.7	10.0
60°-70°	1698.6	7.2
70°-80°	874.9	3.7
80°-90°	224.7	0.9
90°-100°	650.2	2.7
100°-110°	1789.0	7.5
110°-120°	1846.5	7.8
120°-130°	1479.4	6.2
130°-140°	1162.0	4.9
140°-150°	890.5	3.8
150°-160°	640.2	2.7
160°-170°	391.5	1.6
170°-180°	132.0	0.6
0°-30°	4203.4	17.7
0°-40°	6869.0	28.9
0°-60°	11959.8	50.4
0°-90°	14758.0	62.2
90°-120°	4285.7	18.1
90°-150°	7817.7	32.9
90°-180°	8981.0	37.8
0°-180°	23739.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5406	5406	5406	5406	5406	
5°	5426	5372	5391	5376	5371	515
15°	5221	5177	5221	5221	5216	1472
25°	4820	4786	4856	4840	4840	2218
35°	4240	4230	4305	4275	4275	2652
45°	3534	3524	3559	3514	3504	2720
55°	2703	2669	2668	2628	2628	2410
65°	1752	1713	1717	1702	1702	1733
75°	756	790	836	841	841	817
85°	110	169	200	205	200	150
90°	3	12	20	26	26	11
95°	97	355	1150	492	314	102
105°	320	492	1971	3002	2801	337
115°	566	690	1581	3148	3573	559
125°	780	889	1434	2426	2842	696
135°	942	1045	1393	1962	2220	727
145°	1088	1163	1373	1672	1801	682
155°	1232	1272	1364	1503	1546	566
165°	1332	1349	1370	1426	1434	375
175°	1379	1382	1373	1390	1387	131
180°	1379	1379	1379	1379	1379	

TEST NUMBER: P562773

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5406.2	5406.2	5406.2	5406.2	5406.2
2.5°	5438.2	5391.2	5406.2	5393.7	5374.2
5°	5426.2	5372.4	5391.2	5376.0	5371.2
7.5°	5387.2	5333.3	5358.1	5348.0	5343.1
10°	5351.1	5297.3	5326.1	5316.0	5311.1
12.5°	5303.1	5253.2	5286.1	5276.0	5275.0
15°	5221.0	5176.9	5221.0	5220.9	5216.0
17.5°	5117.9	5077.7	5124.9	5127.8	5124.9
20°	5045.8	5001.7	5060.8	5055.9	5060.8
22.5°	4957.7	4921.5	4984.7	4971.8	4976.7
25°	4820.5	4786.3	4855.6	4840.5	4840.5
27.5°	4658.3	4633.9	4709.4	4693.4	4693.4
30°	4550.2	4525.7	4605.3	4585.3	4585.3
32.5°	4430.1	4413.4	4489.1	4465.1	4465.1
35°	4239.9	4230.1	4304.9	4274.9	4274.9
37.5°	4043.6	4034.8	4102.7	4066.4	4054.6
40°	3899.5	3894.6	3954.5	3914.5	3914.5
42.5°	3755.3	3750.4	3802.4	3754.3	3754.3
45°	3534.0	3524.3	3559.1	3513.8	3504.0
47.5°	3292.8	3283.0	3304.8	3255.6	3250.7
50°	3128.6	3118.8	3128.6	3083.4	3078.5
52.5°	2960.4	2942.8	2944.4	2899.3	2898.3
55°	2703.1	2668.8	2668.1	2628.0	2628.0
57.5°	2430.8	2385.8	2389.7	2355.6	2350.7
60°	2242.6	2193.6	2197.5	2167.4	2162.5
62.5°	2058.4	2001.6	2013.3	1979.2	1978.3
65°	1752.0	1712.9	1717.0	1701.9	1701.9
67.5°	1457.7	1421.5	1447.7	1435.6	1434.6
70°	1241.4	1216.9	1251.4	1251.3	1246.4
72.5°	1041.2	1040.2	1083.2	1083.3	1086.2
75°	755.9	790.1	836.0	841.0	841.0
77.5°	504.6	565.3	615.7	617.7	616.7
80°	360.4	428.9	475.5	485.4	480.6
82.5°	244.3	316.7	355.4	365.3	360.4
85°	110.1	168.9	200.2	205.1	200.2
87.5°	32.6	69.6	84.2	85.2	77.4
90°	2.9	11.5	20.5	26.4	26.4
92.5°	40.5	173.0	299.8	115.1	94.5
95°	96.8	354.9	1149.9	491.7	313.9
97.5°	157.8	393.6	1754.7	1352.0	953.9
100°	202.4	417.5	1944.8	1963.0	1601.6
102.5°	244.6	446.0	1994.1	2435.3	2103.8
105°	319.7	491.8	1971.2	3002.1	2801.3
107.5°	391.3	548.5	1859.1	3279.6	3339.3
110°	442.9	586.3	1774.6	3348.7	3555.2



TEST NUMBER: P562773

CATALOG NUMBER: SQ4-PC3-075U-125D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	489.9	628.7	1690.2	3304.2	3618.5
115°	566.1	689.5	1581.0	3148.3	3572.8
117.5°	638.9	752.4	1511.8	2929.5	3409.7
120°	683.5	792.4	1481.3	2765.6	3261.8
122.5°	723.4	832.3	1460.2	2621.9	3092.9
125°	780.3	889.2	1434.4	2426.5	2842.4
127.5°	834.2	938.1	1417.4	2263.4	2628.2
130°	862.4	968.5	1408.0	2166.5	2499.2
132.5°	895.2	1001.4	1400.9	2081.3	2381.8
135°	941.6	1044.8	1393.3	1962.4	2220.5
137.5°	985.0	1080.8	1386.9	1866.3	2079.1
140°	1017.9	1106.8	1384.5	1802.5	1994.6
142.5°	1046.0	1128.0	1379.8	1745.5	1910.2
145°	1088.3	1162.8	1372.8	1672.0	1801.0
147.5°	1133.4	1197.7	1369.3	1606.9	1710.1
150°	1161.6	1218.9	1366.9	1571.1	1651.4
152.5°	1187.4	1240.2	1364.6	1540.3	1606.9
155°	1232.0	1272.1	1364.0	1502.8	1545.8
157.5°	1264.3	1296.9	1364.0	1472.0	1501.8
160°	1287.7	1313.5	1364.0	1455.4	1478.4
162.5°	1306.5	1327.7	1366.3	1441.3	1459.6
165°	1331.7	1348.9	1369.8	1425.8	1434.4
167.5°	1349.3	1362.5	1372.8	1412.7	1415.0
170°	1361.0	1369.7	1372.8	1408.0	1408.0
172.5°	1370.4	1374.5	1372.8	1400.9	1398.6
175°	1378.6	1381.5	1372.8	1390.3	1387.4
177.5°	1381.0	1381.0	1371.6	1385.6	1381.0
180°	1378.6	1378.6	1378.6	1378.6	1378.6

(END OF REPORT)