

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563421

Luminaire Tested: **SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563421  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20437.3 lumens  
Efficiency: N/A  
Efficacy: 126.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 162.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563421  
CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563421

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13680
15°	13747	13672	13597
20°	13656	13579	13476
25°	13494	13401	13268
30°	13244	13174	13007
35°	12898	12809	12647
40°	12485	12406	12265
45°	12144	12059	11940
50°	11708	11633	11521
55°	11102	10955	10871
60°	10107	9817	9769
65°	8904	8533	8505
70°	7687	7370	7370
75°	6617	6523	6431
80°	5834	5903	5765
85°	4566	4982	4982



TEST NUMBER: P563421

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	423.1	2.1
10°-20°	1208.1	5.9
20°-30°	1809.6	8.9
30°-40°	2122.6	10.4
40°-50°	2129.2	10.4
50°-60°	1816.4	8.9
60°-70°	1184.6	5.8
70°-80°	594.3	2.9
80°-90°	168.0	0.8
90°-100°	650.2	3.2
100°-110°	1789.0	8.8
110°-120°	1846.5	9.0
120°-130°	1479.4	7.2
130°-140°	1162.0	5.7
140°-150°	890.5	4.4
150°-160°	640.2	3.1
160°-170°	391.5	1.9
170°-180°	132.0	0.6
0°-30°	3440.9	16.8
0°-40°	5563.5	27.2
0°-60°	9509.1	46.5
0°-90°	11456.0	56.1
90°-120°	4285.7	21.0
90°-150°	7817.7	38.3
90°-180°	8981.0	43.9
0°-180°	20437.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4475	4475	4475	4475	4475	
5°	4490	4448	4463	4447	4447	426
15°	4318	4276	4294	4278	4271	1218
25°	3977	3930	3949	3914	3910	1829
35°	3435	3401	3412	3372	3369	2146
45°	2792	2773	2773	2745	2745	2150
55°	2071	2063	2043	2031	2028	1840
65°	1224	1200	1173	1165	1169	1221
75°	557	557	549	545	541	604
85°	129	141	141	141	141	152
90°	3	12	20	26	26	11
95°	97	355	1150	492	314	102
105°	320	492	1971	3002	2801	337
115°	566	690	1581	3148	3573	559
125°	780	889	1434	2426	2842	696
135°	942	1045	1393	1962	2220	727
145°	1088	1163	1373	1672	1801	682
155°	1232	1272	1364	1503	1546	566
165°	1332	1349	1370	1426	1434	375
175°	1379	1382	1373	1390	1387	131
180°	1379	1379	1379	1379	1379	

TEST NUMBER: P563421

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4474.6	4474.6	4474.6	4474.6	4474.6
2.5°	4502.8	4466.0	4474.6	4467.9	4449.5
5°	4490.3	4448.1	4462.8	4447.2	4447.2
7.5°	4459.7	4413.7	4428.3	4412.6	4411.9
10°	4431.5	4385.4	4400.1	4384.3	4380.5
12.5°	4390.7	4344.7	4362.4	4343.6	4342.8
15°	4317.7	4275.6	4294.2	4278.3	4270.7
17.5°	4235.4	4189.4	4211.9	4189.8	4186.8
20°	4172.6	4126.6	4149.1	4117.7	4117.7
22.5°	4097.3	4051.3	4076.9	4036.2	4036.2
25°	3976.6	3930.5	3949.1	3913.7	3909.9
27.5°	3833.0	3787.8	3807.1	3767.1	3766.4
30°	3729.5	3687.3	3709.9	3666.7	3662.8
32.5°	3616.5	3577.4	3593.8	3550.6	3546.7
35°	3435.4	3400.9	3411.8	3372.5	3368.7
37.5°	3244.8	3209.5	3222.0	3188.3	3186.7
40°	3109.9	3086.9	3090.3	3062.6	3055.0
42.5°	2984.4	2958.3	2961.6	2934.1	2932.6
45°	2792.2	2773.0	2772.6	2745.2	2745.2
47.5°	2588.3	2573.7	2569.5	2546.7	2545.9
50°	2447.1	2435.6	2431.4	2411.7	2407.9
52.5°	2299.7	2294.3	2280.8	2264.3	2263.6
55°	2070.6	2063.0	2043.2	2031.3	2027.5
57.5°	1822.0	1806.7	1784.4	1767.2	1770.2
60°	1643.2	1627.8	1596.1	1588.3	1588.3
62.5°	1470.6	1452.2	1420.4	1409.6	1415.7
65°	1223.6	1200.5	1172.6	1164.8	1168.7
67.5°	999.2	978.5	948.3	948.2	945.1
70°	854.9	843.4	819.6	819.6	819.6
72.5°	726.3	720.9	703.5	703.5	700.4
75°	556.9	556.9	549.0	545.0	541.2
77.5°	417.3	418.8	414.9	410.8	403.9
80°	329.4	337.1	333.3	329.3	325.5
82.5°	247.8	255.5	254.9	247.8	247.1
85°	129.4	140.9	141.2	141.2	141.2
87.5°	35.1	49.1	54.3	55.5	58.6
90°	2.9	11.5	20.5	26.4	26.4
92.5°	40.5	173.0	299.8	115.1	94.5
95°	96.8	354.9	1149.9	491.7	313.9
97.5°	157.8	393.6	1754.7	1352.0	953.9
100°	202.4	417.5	1944.8	1963.0	1601.6
102.5°	244.6	446.0	1994.1	2435.3	2103.8
105°	319.7	491.8	1971.2	3002.1	2801.3
107.5°	391.3	548.5	1859.1	3279.6	3339.3
110°	442.9	586.3	1774.6	3348.7	3555.2



TEST NUMBER: P563421

CATALOG NUMBER: SQ4-PP3-075U-100D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	489.9	628.7	1690.2	3304.2	3618.5
115°	566.1	689.5	1581.0	3148.3	3572.8
117.5°	638.9	752.4	1511.8	2929.5	3409.7
120°	683.5	792.4	1481.3	2765.6	3261.8
122.5°	723.4	832.3	1460.2	2621.9	3092.9
125°	780.3	889.2	1434.4	2426.5	2842.4
127.5°	834.2	938.1	1417.4	2263.4	2628.2
130°	862.4	968.5	1408.0	2166.5	2499.2
132.5°	895.2	1001.4	1400.9	2081.3	2381.8
135°	941.6	1044.8	1393.3	1962.4	2220.5
137.5°	985.0	1080.8	1386.9	1866.3	2079.1
140°	1017.9	1106.8	1384.5	1802.5	1994.6
142.5°	1046.0	1128.0	1379.8	1745.5	1910.2
145°	1088.3	1162.8	1372.8	1672.0	1801.0
147.5°	1133.4	1197.7	1369.3	1606.9	1710.1
150°	1161.6	1218.9	1366.9	1571.1	1651.4
152.5°	1187.4	1240.2	1364.6	1540.3	1606.9
155°	1232.0	1272.1	1364.0	1502.8	1545.8
157.5°	1264.3	1296.9	1364.0	1472.0	1501.8
160°	1287.7	1313.5	1364.0	1455.4	1478.4
162.5°	1306.5	1327.7	1366.3	1441.3	1459.6
165°	1331.7	1348.9	1369.8	1425.8	1434.4
167.5°	1349.3	1362.5	1372.8	1412.7	1415.0
170°	1361.0	1369.7	1372.8	1408.0	1408.0
172.5°	1370.4	1374.5	1372.8	1400.9	1398.6
175°	1378.6	1381.5	1372.8	1390.3	1387.4
177.5°	1381.0	1381.0	1371.6	1385.6	1381.0
180°	1378.6	1378.6	1378.6	1378.6	1378.6

(END OF REPORT)