

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563555

Luminaire Tested: **SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563555  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6349.4 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct


Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563555

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563555

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15276	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14204	14023
40°	13843	13757	13599
45°	13465	13371	13238
50°	12982	12899	12775
55°	12311	12148	12054
60°	11207	10886	10833
65°	9873	9462	9430
70°	8524	8172	8172
75°	7336	7234	7129
80°	6468	6546	6394
85°	5060	5526	5526



TEST NUMBER: P563555

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.6	3.7
10°-20°	669.8	10.5
20°-30°	1003.3	15.8
30°-40°	1176.8	18.5
40°-50°	1180.5	18.6
50°-60°	1007.0	15.9
60°-70°	656.8	10.3
70°-80°	329.5	5.2
80°-90°	91.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1907.7	30.0
0°-40°	3084.5	48.6
0°-60°	5272.0	83.0
0°-90°	6349.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6349.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2481	2481	2481	2481	2481	
5°	2490	2466	2474	2466	2466	236
15°	2394	2370	2381	2372	2368	675
25°	2205	2179	2189	2170	2168	1014
35°	1905	1886	1892	1870	1868	1190
45°	1548	1537	1537	1522	1522	1192
55°	1148	1144	1133	1126	1124	1020
65°	678	666	650	646	648	677
75°	309	309	304	302	300	335
85°	72	78	78	78	78	87
90°	0	0	0	0	0	



TEST NUMBER: P563555

CATALOG NUMBER: SQ4-PP3-0U-125D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2480.8	2480.8	2480.8	2480.8	2480.8
2.5°	2496.4	2476.0	2480.8	2477.1	2466.9
5°	2489.5	2466.1	2474.2	2465.6	2465.6
7.5°	2472.5	2447.0	2455.1	2446.4	2446.0
10°	2456.9	2431.3	2439.5	2430.7	2428.6
12.5°	2434.2	2408.7	2418.6	2408.1	2407.7
15°	2393.8	2370.4	2380.8	2372.0	2367.7
17.5°	2348.1	2322.6	2335.1	2322.9	2321.2
20°	2313.4	2287.8	2300.3	2282.9	2282.9
22.5°	2271.6	2246.1	2260.3	2237.7	2237.7
25°	2204.6	2179.1	2189.4	2169.8	2167.7
27.5°	2125.1	2100.0	2110.7	2088.5	2088.1
30°	2067.7	2044.3	2056.8	2032.8	2030.7
32.5°	2005.1	1983.4	1992.4	1968.5	1966.4
35°	1904.6	1885.5	1891.6	1869.8	1867.6
37.5°	1798.9	1779.4	1786.3	1767.6	1766.8
40°	1724.1	1711.4	1713.3	1698.0	1693.7
42.5°	1654.6	1640.1	1642.0	1626.7	1625.9
45°	1548.0	1537.4	1537.2	1521.9	1521.9
47.5°	1435.0	1426.9	1424.5	1411.9	1411.5
50°	1356.7	1350.3	1348.0	1337.1	1335.0
52.5°	1275.0	1272.0	1264.5	1255.4	1255.0
55°	1148.0	1143.7	1132.8	1126.2	1124.1
57.5°	1010.1	1001.6	989.3	979.7	981.4
60°	911.0	902.5	884.9	880.6	880.6
62.5°	815.3	805.1	787.5	781.5	784.9
65°	678.4	665.6	650.1	645.8	647.9
67.5°	554.0	542.5	525.7	525.7	524.0
70°	474.0	467.6	454.4	454.4	454.4
72.5°	402.7	399.7	390.1	390.0	388.3
75°	308.7	308.7	304.4	302.2	300.0
77.5°	231.3	232.2	230.0	227.8	223.9
80°	182.6	186.9	184.8	182.6	180.5
82.5°	137.4	141.7	141.3	137.4	137.0
85°	71.7	78.1	78.3	78.3	78.3
87.5°	19.1	25.9	27.8	27.9	29.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)