

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563699

Luminaire Tested: **SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563699
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10262.8 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563699
CATALOG NUMBER: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563699

CATALOG NUMBER: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	87	79	73	68	78	72	67	63	59	55	52	46	44	41	34	33	32	26
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	31	29	27	22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13
8	52	40	33	27	47	37	30	26	30	25	22	24	21	18	19	16	14	12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8435	8377	8271
40°	8164	8113	8020
45°	7942	7886	7808
50°	7656	7607	7534
55°	7260	7164	7109
60°	6610	6420	6388
65°	5823	5580	5561
70°	5026	4820	4820
75°	4328	4266	4206
80°	3815	3861	3769
85°	2985	3260	3260



TEST NUMBER: P563699

CATALOG NUMBER: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	1.3
10°-20°	395.0	3.8
20°-30°	591.7	5.8
30°-40°	694.0	6.8
40°-50°	696.2	6.8
50°-60°	593.9	5.8
60°-70°	387.3	3.8
70°-80°	194.3	1.9
80°-90°	56.1	0.5
90°-100°	472.2	4.6
100°-110°	1271.9	12.4
110°-120°	1334.8	13.0
120°-130°	1083.2	10.6
130°-140°	849.5	8.3
140°-150°	652.2	6.4
150°-160°	468.9	4.6
160°-170°	286.5	2.8
170°-180°	96.6	0.9
0°-30°	1125.1	11.0
0°-40°	1819.1	17.7
0°-60°	3109.2	30.3
0°-90°	3747.0	36.5
90°-120°	3078.9	30.0
90°-150°	5663.8	55.2
90°-180°	6516.0	63.5
0°-180°	10262.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1463	1463	1463	1463	1463	
5°	1468	1454	1459	1454	1454	139
15°	1412	1398	1404	1399	1396	398
25°	1300	1285	1291	1280	1278	598
35°	1123	1112	1116	1103	1102	702
45°	913	907	907	898	898	703
55°	677	674	668	664	663	602
65°	400	392	383	381	382	399
75°	182	182	180	178	177	198
85°	42	46	46	46	46	50
90°	3	8	15	17	17	7
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P563699

CATALOG NUMBER: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1463.1	1463.1	1463.1	1463.1	1463.1
2.5°	1472.3	1460.3	1463.1	1460.9	1454.9
5°	1468.2	1454.4	1459.2	1454.1	1454.1
7.5°	1458.2	1443.1	1447.9	1442.8	1442.5
10°	1449.0	1433.9	1438.7	1433.5	1432.3
12.5°	1435.6	1420.6	1426.4	1420.2	1420.0
15°	1411.8	1398.0	1404.1	1398.9	1396.4
17.5°	1384.8	1369.8	1377.2	1369.9	1368.9
20°	1364.3	1349.3	1356.6	1346.4	1346.4
22.5°	1339.7	1324.7	1333.0	1319.7	1319.7
25°	1300.2	1285.2	1291.2	1279.7	1278.4
27.5°	1253.3	1238.5	1244.8	1231.7	1231.5
30°	1219.4	1205.6	1213.0	1198.9	1197.6
32.5°	1182.5	1169.7	1175.1	1160.9	1159.7
35°	1123.3	1112.0	1115.6	1102.7	1101.5
37.5°	1060.9	1049.4	1053.5	1042.5	1042.0
40°	1016.8	1009.3	1010.4	1001.4	998.9
42.5°	975.8	967.3	968.4	959.4	958.9
45°	913.0	906.7	906.6	897.6	897.6
47.5°	846.3	841.5	840.1	832.7	832.4
50°	800.1	796.4	795.0	788.6	787.3
52.5°	751.9	750.2	745.8	740.4	740.1
55°	677.0	674.5	668.1	664.2	662.9
57.5°	595.7	590.7	583.4	577.8	578.8
60°	537.3	532.3	521.9	519.3	519.3
62.5°	480.8	474.8	464.4	460.9	462.9
65°	400.1	392.5	383.4	380.9	382.1
67.5°	326.7	320.0	310.1	310.0	309.0
70°	279.5	275.8	268.0	268.0	268.0
72.5°	237.5	235.7	230.0	230.0	229.0
75°	182.1	182.1	179.5	178.2	177.0
77.5°	136.4	136.9	135.7	134.3	132.1
80°	107.7	110.2	109.0	107.7	106.4
82.5°	81.0	83.5	83.3	81.0	80.8
85°	42.3	46.1	46.2	46.2	46.2
87.5°	11.8	16.8	19.5	19.8	20.8
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7



TEST NUMBER: P563699

CATALOG NUMBER: SQ4-PP3-125U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)