

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563747

Luminaire Tested: **SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563747
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12867.6 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563747
CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563747

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15259	15259	15259
5°	15371	15276	15223
10°	15345	15236	15168
15°	15243	15160	15077
20°	15142	15057	14943
25°	14962	14859	14711
30°	14685	14608	14423
35°	14301	14204	14023
40°	13843	13757	13599
45°	13465	13371	13238
50°	12982	12899	12775
55°	12311	12148	12054
60°	11207	10886	10833
65°	9873	9462	9430
70°	8524	8172	8172
75°	7336	7234	7129
80°	6468	6546	6394
85°	5060	5526	5526



TEST NUMBER: P563747

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.6	1.8
10°-20°	669.8	5.2
20°-30°	1003.3	7.8
30°-40°	1176.8	9.1
40°-50°	1180.5	9.2
50°-60°	1007.0	7.8
60°-70°	656.8	5.1
70°-80°	329.5	2.6
80°-90°	93.6	0.7
90°-100°	472.2	3.7
100°-110°	1271.9	9.9
110°-120°	1334.8	10.4
120°-130°	1083.2	8.4
130°-140°	849.5	6.6
140°-150°	652.2	5.1
150°-160°	468.9	3.6
160°-170°	286.5	2.2
170°-180°	96.6	0.8
0°-30°	1907.7	14.8
0°-40°	3084.5	24.0
0°-60°	5272.0	41.0
0°-90°	6351.8	49.4
90°-120°	3078.9	23.9
90°-150°	5663.8	44.0
90°-180°	6516.0	50.6
0°-180°	12867.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2481	2481	2481	2481	2481	
5°	2490	2466	2474	2466	2466	236
15°	2394	2370	2381	2372	2368	675
25°	2205	2179	2189	2170	2168	1014
35°	1905	1886	1892	1870	1868	1190
45°	1548	1537	1537	1522	1522	1192
55°	1148	1144	1133	1126	1124	1020
65°	678	666	650	646	648	677
75°	309	309	304	302	300	335
85°	72	78	78	78	78	84
90°	3	8	15	17	17	8
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P563747

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2480.8	2480.8	2480.8	2480.8	2480.8
2.5°	2496.4	2476.0	2480.8	2477.1	2466.9
5°	2489.5	2466.1	2474.2	2465.6	2465.6
7.5°	2472.5	2447.0	2455.1	2446.4	2446.0
10°	2456.9	2431.3	2439.5	2430.7	2428.6
12.5°	2434.2	2408.7	2418.6	2408.1	2407.7
15°	2393.8	2370.4	2380.8	2372.0	2367.7
17.5°	2348.1	2322.6	2335.1	2322.9	2321.2
20°	2313.4	2287.8	2300.3	2282.9	2282.9
22.5°	2271.6	2246.1	2260.3	2237.7	2237.7
25°	2204.6	2179.1	2189.4	2169.8	2167.7
27.5°	2125.1	2100.0	2110.7	2088.5	2088.1
30°	2067.7	2044.3	2056.8	2032.8	2030.7
32.5°	2005.1	1983.4	1992.4	1968.5	1966.4
35°	1904.6	1885.5	1891.6	1869.8	1867.6
37.5°	1798.9	1779.4	1786.3	1767.6	1766.8
40°	1724.1	1711.4	1713.3	1698.0	1693.7
42.5°	1654.6	1640.1	1642.0	1626.7	1625.9
45°	1548.0	1537.4	1537.2	1521.9	1521.9
47.5°	1435.0	1426.9	1424.5	1411.9	1411.5
50°	1356.7	1350.3	1348.0	1337.1	1335.0
52.5°	1275.0	1272.0	1264.5	1255.4	1255.0
55°	1148.0	1143.7	1132.8	1126.2	1124.1
57.5°	1010.1	1001.6	989.3	979.7	981.4
60°	911.0	902.5	884.9	880.6	880.6
62.5°	815.3	805.1	787.5	781.5	784.9
65°	678.4	665.6	650.1	645.8	647.9
67.5°	554.0	542.5	525.7	525.7	524.0
70°	474.0	467.6	454.4	454.4	454.4
72.5°	402.7	399.7	390.1	390.0	388.3
75°	308.7	308.7	304.4	302.2	300.0
77.5°	231.3	232.2	230.0	227.8	223.9
80°	182.6	186.9	184.8	182.6	180.5
82.5°	137.4	141.7	141.3	137.4	137.0
85°	71.7	78.1	78.3	78.3	78.3
87.5°	19.6	27.5	30.9	31.2	32.9
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7



TEST NUMBER: P563747

CATALOG NUMBER: SQ4-PP3-125U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)