

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563493

Luminaire Tested: **SQ4-PP3-0U-075D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563493
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-075D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8619.3 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct


Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563493

CATALOG NUMBER: SQ4-PP3-0U-075D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563493

CATALOG NUMBER: SQ4-PP3-0U-075D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10357	10357	10357
5°	10433	10369	10333
10°	10415	10342	10295
15°	10346	10290	10234
20°	10278	10220	10143
25°	10156	10085	9985
30°	9968	9915	9790
35°	9707	9640	9518
40°	9396	9337	9230
45°	9140	9076	8986
50°	8812	8755	8670
55°	8356	8245	8182
60°	7607	7389	7353
65°	6701	6422	6400
70°	5785	5547	5547
75°	4980	4910	4840
80°	4390	4444	4339
85°	3437	3751	3751



TEST NUMBER: P563493

CATALOG NUMBER: SQ4-PP3-0U-075D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.4	3.7
10°-20°	909.3	10.5
20°-30°	1361.9	15.8
30°-40°	1597.5	18.5
40°-50°	1602.5	18.6
50°-60°	1367.1	15.9
60°-70°	891.6	10.3
70°-80°	447.3	5.2
80°-90°	123.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2589.7	30.0
0°-40°	4187.1	48.6
0°-60°	7156.7	83.0
0°-90°	8619.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8619.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3368	3368	3368	3368	3368	
5°	3380	3348	3359	3347	3347	321
15°	3250	3218	3232	3220	3214	917
25°	2993	2958	2972	2946	2943	1376
35°	2586	2560	2568	2538	2535	1615
45°	2102	2087	2087	2066	2066	1618
55°	1558	1553	1538	1529	1526	1385
65°	921	904	882	877	880	919
75°	419	419	413	410	407	455
85°	97	106	106	106	106	118
90°	0	0	0	0	0	



TEST NUMBER: P563493

CATALOG NUMBER: SQ4-PP3-OU-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3367.6	3367.6	3367.6	3367.6	3367.6
2.5°	3388.9	3361.2	3367.6	3362.6	3348.8
5°	3379.5	3347.7	3358.8	3347.0	3347.0
7.5°	3356.4	3321.8	3332.8	3321.0	3320.4
10°	3335.2	3300.5	3311.6	3299.7	3296.8
12.5°	3304.5	3269.9	3283.2	3269.1	3268.5
15°	3249.6	3217.8	3231.9	3219.9	3214.2
17.5°	3187.6	3153.0	3169.9	3153.3	3151.0
20°	3140.4	3105.8	3122.7	3099.1	3099.1
22.5°	3083.7	3049.1	3068.4	3037.7	3037.7
25°	2992.8	2958.2	2972.1	2945.5	2942.6
27.5°	2884.8	2850.7	2865.3	2835.2	2834.6
30°	2806.9	2775.1	2792.1	2759.6	2756.7
32.5°	2721.9	2692.4	2704.7	2672.2	2669.3
35°	2585.5	2559.5	2567.8	2538.2	2535.3
37.5°	2442.1	2415.5	2424.9	2399.5	2398.4
40°	2340.5	2323.2	2325.8	2305.0	2299.2
42.5°	2246.1	2226.5	2229.0	2208.3	2207.1
45°	2101.5	2087.0	2086.7	2066.0	2066.0
47.5°	1948.0	1937.0	1933.8	1916.7	1916.1
50°	1841.7	1833.1	1829.9	1815.1	1812.2
52.5°	1730.8	1726.7	1716.6	1704.2	1703.6
55°	1558.4	1552.6	1537.7	1528.8	1525.9
57.5°	1371.3	1359.7	1342.9	1330.0	1332.3
60°	1236.7	1225.1	1201.3	1195.4	1195.4
62.5°	1106.8	1093.0	1069.0	1060.9	1065.5
65°	920.9	903.5	882.5	876.7	879.5
67.5°	752.0	736.5	713.7	713.6	711.3
70°	643.4	634.8	616.9	616.9	616.9
72.5°	546.6	542.6	529.5	529.4	527.1
75°	419.1	419.1	413.2	410.2	407.3
77.5°	314.0	315.2	312.3	309.2	304.0
80°	247.9	253.7	250.9	247.9	245.0
82.5°	186.5	192.3	191.8	186.5	185.9
85°	97.4	106.1	106.3	106.3	106.3
87.5°	26.0	35.2	37.8	37.8	40.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)