

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563661

Luminaire Tested: **SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563661  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20851.5 lumens  
Efficiency: N/A  
Efficacy: 142.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 146.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563661  
CATALOG NUMBER: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563661

CATALOG NUMBER: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20
3	77	68	61	56	69	61	55	51	48	44	41	36	34	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7027	7027	7027
5°	7079	7035	7011
10°	7067	7016	6985
15°	7020	6982	6943
20°	6973	6934	6881
25°	6890	6843	6775
30°	6763	6727	6642
35°	6586	6541	6458
40°	6375	6335	6263
45°	6201	6158	6097
50°	5979	5940	5883
55°	5669	5594	5551
60°	5161	5013	4988
65°	4547	4357	4343
70°	3926	3763	3763
75°	3379	3332	3283
80°	2979	3014	2943
85°	2332	2544	2544



TEST NUMBER: P563661

CATALOG NUMBER: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	216.1	1.0
10°-20°	616.9	3.0
20°-30°	924.1	4.4
30°-40°	1083.9	5.2
40°-50°	1087.3	5.2
50°-60°	927.5	4.4
60°-70°	604.9	2.9
70°-80°	303.5	1.5
80°-90°	89.5	0.4
90°-100°	1086.8	5.2
100°-110°	2927.6	14.0
110°-120°	3072.5	14.7
120°-130°	2493.2	12.0
130°-140°	1955.4	9.4
140°-150°	1501.2	7.2
150°-160°	1079.4	5.2
160°-170°	659.4	3.2
170°-180°	222.4	1.1
0°-30°	1757.0	8.4
0°-40°	2840.9	13.6
0°-60°	4855.7	23.3
0°-90°	5853.5	28.1
90°-120°	7086.9	34.0
90°-150°	13036.8	62.5
90°-180°	14998.0	71.9
0°-180°	20851.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2285	2285	2285	2285	2285	
5°	2293	2271	2279	2271	2271	218
15°	2205	2183	2193	2185	2181	622
25°	2031	2007	2016	1998	1996	934
35°	1754	1737	1742	1722	1720	1096
45°	1426	1416	1416	1402	1402	1098
55°	1057	1053	1043	1037	1035	940
65°	625	613	599	595	597	624
75°	284	284	280	278	276	309
85°	66	72	72	72	72	78
90°	6	18	36	38	38	14
95°	166	591	1782	911	630	173
105°	542	843	3238	4844	4546	569
115°	956	1170	2696	5210	5892	941
125°	1305	1499	2421	4092	4815	1165
135°	1572	1754	2353	3301	3738	1213
145°	1817	1959	2323	2822	3031	1140
155°	2063	2138	2302	2532	2613	950
165°	2237	2264	2311	2403	2415	631
175°	2326	2323	2314	2347	2341	221
180°	2323	2323	2323	2323	2323	

TEST NUMBER: P563661

CATALOG NUMBER: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2284.9	2284.9	2284.9	2284.9	2284.9
2.5°	2299.3	2280.5	2284.9	2281.5	2272.1
5°	2292.9	2271.4	2278.9	2270.9	2270.9
7.5°	2277.3	2253.8	2261.2	2253.2	2252.8
10°	2262.9	2239.4	2246.8	2238.8	2236.8
12.5°	2242.0	2218.5	2227.6	2218.0	2217.6
15°	2204.8	2183.2	2192.8	2184.7	2180.7
17.5°	2162.7	2139.2	2150.7	2139.5	2137.9
20°	2130.7	2107.2	2118.7	2102.6	2102.6
22.5°	2092.2	2068.7	2081.8	2061.0	2061.0
25°	2030.6	2007.1	2016.5	1998.5	1996.5
27.5°	1957.3	1934.2	1944.0	1923.6	1923.2
30°	1904.4	1882.9	1894.4	1872.3	1870.4
32.5°	1846.7	1826.8	1835.1	1813.0	1811.1
35°	1754.2	1736.6	1742.2	1722.1	1720.2
37.5°	1656.9	1638.9	1645.3	1628.0	1627.3
40°	1588.0	1576.3	1578.0	1563.9	1560.0
42.5°	1523.9	1510.6	1512.3	1498.3	1497.5
45°	1425.8	1416.0	1415.8	1401.8	1401.8
47.5°	1321.7	1314.2	1312.1	1300.4	1300.0
50°	1249.6	1243.7	1241.6	1231.5	1229.5
52.5°	1174.3	1171.5	1164.7	1156.2	1155.9
55°	1057.3	1053.4	1043.3	1037.3	1035.3
57.5°	930.4	922.5	911.1	902.4	903.9
60°	839.1	831.2	815.0	811.0	811.0
62.5°	750.9	741.5	725.3	719.8	722.9
65°	624.8	613.0	598.8	594.8	596.8
67.5°	510.2	499.7	484.2	484.2	482.6
70°	436.6	430.7	418.5	418.5	418.5
72.5°	370.9	368.1	359.3	359.2	357.7
75°	284.4	284.4	280.4	278.3	276.3
77.5°	213.1	213.9	211.9	209.8	206.3
80°	168.2	172.1	170.2	168.2	166.2
82.5°	126.6	130.5	130.2	126.6	126.2
85°	66.1	72.0	72.1	72.1	72.1
87.5°	18.8	27.4	32.7	33.4	34.9
90°	5.9	17.5	35.5	38.5	38.5
92.5°	72.2	255.1	504.3	242.8	168.7
95°	165.7	591.1	1781.7	911.1	630.4
97.5°	264.6	676.7	2794.4	2334.5	1760.3
100°	340.3	710.8	3116.4	3260.6	2705.0
102.5°	413.7	758.7	3223.0	3954.3	3498.2
105°	541.6	842.6	3237.8	4843.9	4545.9
107.5°	662.3	930.9	3099.8	5301.1	5378.1
110°	742.8	997.5	2974.4	5443.1	5723.8

TEST NUMBER: P563661

CATALOG NUMBER: SQ4-PP3-125U-050D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	828.1	1064.2	2853.6	5411.7	5873.0
115°	955.9	1170.1	2696.2	5209.5	5892.5
117.5°	1072.5	1273.4	2574.2	4886.9	5647.4
120°	1148.3	1342.2	2512.7	4655.4	5436.7
122.5°	1214.6	1406.2	2467.7	4418.6	5197.6
125°	1305.2	1499.1	2420.9	4091.8	4815.2
127.5°	1392.2	1583.2	2391.3	3803.5	4449.4
130°	1444.3	1635.3	2379.5	3638.4	4205.5
132.5°	1496.4	1685.0	2367.6	3492.9	4013.8
135°	1571.5	1753.8	2352.9	3301.0	3737.9
137.5°	1643.1	1817.9	2345.2	3138.2	3497.0
140°	1692.9	1860.7	2338.1	3038.0	3362.1
142.5°	1745.0	1901.2	2333.3	2944.5	3217.6
145°	1817.2	1959.0	2323.3	2822.2	3030.6
147.5°	1895.3	2018.6	2313.2	2719.4	2883.2
150°	1947.4	2054.5	2308.5	2654.9	2790.9
152.5°	1994.7	2087.9	2306.1	2602.2	2712.7
155°	2062.8	2138.1	2302.5	2532.3	2613.3
157.5°	2122.6	2181.1	2303.1	2483.1	2537.5
160°	2160.5	2209.7	2305.5	2454.4	2494.9
162.5°	2193.6	2233.6	2307.9	2430.5	2459.4
165°	2237.4	2263.5	2311.4	2403.4	2415.0
167.5°	2272.9	2288.0	2314.4	2382.6	2387.2
170°	2296.6	2302.4	2314.4	2370.6	2370.6
172.5°	2310.8	2312.0	2316.7	2358.8	2358.8
175°	2326.2	2323.3	2314.4	2346.8	2341.0
177.5°	2332.7	2328.1	2316.2	2335.0	2330.4
180°	2323.3	2323.3	2323.3	2323.3	2323.3

(END OF REPORT)