

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563709

Luminaire Tested: **SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563709
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26455.9 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 201.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563709
CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563709

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13761	13761	13761
5°	13862	13777	13729
10°	13839	13741	13680
15°	13747	13672	13597
20°	13656	13579	13476
25°	13494	13401	13268
30°	13244	13174	13007
35°	12898	12809	12647
40°	12485	12406	12265
45°	12144	12059	11940
50°	11708	11633	11521
55°	11102	10955	10871
60°	10107	9817	9769
65°	8904	8533	8505
70°	7687	7370	7370
75°	6617	6523	6431
80°	5834	5903	5765
85°	4566	4982	4982



TEST NUMBER: P563709

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.1	1.6
10°-20°	1208.1	4.6
20°-30°	1809.6	6.8
30°-40°	2122.6	8.0
40°-50°	2129.2	8.0
50°-60°	1816.4	6.9
60°-70°	1184.6	4.5
70°-80°	594.3	2.2
80°-90°	169.9	0.6
90°-100°	1086.8	4.1
100°-110°	2927.6	11.1
110°-120°	3072.5	11.6
120°-130°	2493.2	9.4
130°-140°	1955.4	7.4
140°-150°	1501.2	5.7
150°-160°	1079.4	4.1
160°-170°	659.4	2.5
170°-180°	222.4	0.8
0°-30°	3440.9	13.0
0°-40°	5563.5	21.0
0°-60°	9509.1	35.9
0°-90°	11458.0	43.3
90°-120°	7086.9	26.8
90°-150°	13036.8	49.3
90°-180°	14998.0	56.7
0°-180°	26455.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4475	4475	4475	4475	4475	
5°	4490	4448	4463	4447	4447	426
15°	4318	4276	4294	4278	4271	1218
25°	3977	3930	3949	3914	3910	1829
35°	3435	3401	3412	3372	3369	2146
45°	2792	2773	2773	2745	2745	2150
55°	2071	2063	2043	2031	2028	1840
65°	1224	1200	1173	1165	1169	1221
75°	557	557	549	545	541	604
85°	129	141	141	141	141	152
90°	6	18	36	38	38	16
95°	166	591	1782	911	630	173
105°	542	843	3238	4844	4546	569
115°	956	1170	2696	5210	5892	941
125°	1305	1499	2421	4092	4815	1165
135°	1572	1754	2353	3301	3738	1213
145°	1817	1959	2323	2822	3031	1140
155°	2063	2138	2302	2532	2613	950
165°	2237	2264	2311	2403	2415	631
175°	2326	2323	2314	2347	2341	221
180°	2323	2323	2323	2323	2323	

TEST NUMBER: P563709

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4474.6	4474.6	4474.6	4474.6	4474.6
2.5°	4502.8	4466.0	4474.6	4467.9	4449.5
5°	4490.3	4448.1	4462.8	4447.2	4447.2
7.5°	4459.7	4413.7	4428.3	4412.6	4411.9
10°	4431.5	4385.4	4400.1	4384.3	4380.5
12.5°	4390.7	4344.7	4362.4	4343.6	4342.8
15°	4317.7	4275.6	4294.2	4278.3	4270.7
17.5°	4235.4	4189.4	4211.9	4189.8	4186.8
20°	4172.6	4126.6	4149.1	4117.7	4117.7
22.5°	4097.3	4051.3	4076.9	4036.2	4036.2
25°	3976.6	3930.5	3949.1	3913.7	3909.9
27.5°	3833.0	3787.8	3807.1	3767.1	3766.4
30°	3729.5	3687.3	3709.9	3666.7	3662.8
32.5°	3616.5	3577.4	3593.8	3550.6	3546.7
35°	3435.4	3400.9	3411.8	3372.5	3368.7
37.5°	3244.8	3209.5	3222.0	3188.3	3186.7
40°	3109.9	3086.9	3090.3	3062.6	3055.0
42.5°	2984.4	2958.3	2961.6	2934.1	2932.6
45°	2792.2	2773.0	2772.6	2745.2	2745.2
47.5°	2588.3	2573.7	2569.5	2546.7	2545.9
50°	2447.1	2435.6	2431.4	2411.7	2407.9
52.5°	2299.7	2294.3	2280.8	2264.3	2263.6
55°	2070.6	2063.0	2043.2	2031.3	2027.5
57.5°	1822.0	1806.7	1784.4	1767.2	1770.2
60°	1643.2	1627.8	1596.1	1588.3	1588.3
62.5°	1470.6	1452.2	1420.4	1409.6	1415.7
65°	1223.6	1200.5	1172.6	1164.8	1168.7
67.5°	999.2	978.5	948.3	948.2	945.1
70°	854.9	843.4	819.6	819.6	819.6
72.5°	726.3	720.9	703.5	703.5	700.4
75°	556.9	556.9	549.0	545.0	541.2
77.5°	417.3	418.8	414.9	410.8	403.9
80°	329.4	337.1	333.3	329.3	325.5
82.5°	247.8	255.5	254.9	247.8	247.1
85°	129.4	140.9	141.2	141.2	141.2
87.5°	35.7	50.3	57.3	58.0	61.0
90°	5.9	17.5	35.5	38.5	38.5
92.5°	72.2	255.1	504.3	242.8	168.7
95°	165.7	591.1	1781.7	911.1	630.4
97.5°	264.6	676.7	2794.4	2334.5	1760.3
100°	340.3	710.8	3116.4	3260.6	2705.0
102.5°	413.7	758.7	3223.0	3954.3	3498.2
105°	541.6	842.6	3237.8	4843.9	4545.9
107.5°	662.3	930.9	3099.8	5301.1	5378.1
110°	742.8	997.5	2974.4	5443.1	5723.8



TEST NUMBER: P563709

CATALOG NUMBER: SQ4-PP3-125U-100D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	828.1	1064.2	2853.6	5411.7	5873.0
115°	955.9	1170.1	2696.2	5209.5	5892.5
117.5°	1072.5	1273.4	2574.2	4886.9	5647.4
120°	1148.3	1342.2	2512.7	4655.4	5436.7
122.5°	1214.6	1406.2	2467.7	4418.6	5197.6
125°	1305.2	1499.1	2420.9	4091.8	4815.2
127.5°	1392.2	1583.2	2391.3	3803.5	4449.4
130°	1444.3	1635.3	2379.5	3638.4	4205.5
132.5°	1496.4	1685.0	2367.6	3492.9	4013.8
135°	1571.5	1753.8	2352.9	3301.0	3737.9
137.5°	1643.1	1817.9	2345.2	3138.2	3497.0
140°	1692.9	1860.7	2338.1	3038.0	3362.1
142.5°	1745.0	1901.2	2333.3	2944.5	3217.6
145°	1817.2	1959.0	2323.3	2822.2	3030.6
147.5°	1895.3	2018.6	2313.2	2719.4	2883.2
150°	1947.4	2054.5	2308.5	2654.9	2790.9
152.5°	1994.7	2087.9	2306.1	2602.2	2712.7
155°	2062.8	2138.1	2302.5	2532.3	2613.3
157.5°	2122.6	2181.1	2303.1	2483.1	2537.5
160°	2160.5	2209.7	2305.5	2454.4	2494.9
162.5°	2193.6	2233.6	2307.9	2430.5	2459.4
165°	2237.4	2263.5	2311.4	2403.4	2415.0
167.5°	2272.9	2288.0	2314.4	2382.6	2387.2
170°	2296.6	2302.4	2314.4	2370.6	2370.6
172.5°	2310.8	2312.0	2316.7	2358.8	2358.8
175°	2326.2	2323.3	2314.4	2346.8	2341.0
177.5°	2332.7	2328.1	2316.2	2335.0	2330.4
180°	2323.3	2323.3	2323.3	2323.3	2323.3

(END OF REPORT)