

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564107

Luminaire Tested: **SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564107
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8849.5 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564107
CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564107

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	67	63	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	43	41	38	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	37	33	29	32	29	26	23
7	60	47	40	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12169	12169	12169
5°	12279	12184	12121
10°	12240	12155	12091
15°	12187	12110	12045
20°	12125	12047	11957
25°	12040	11959	11820
30°	11910	11825	11656
35°	11734	11632	11465
40°	11467	11343	11138
45°	10999	10806	10584
50°	10176	9931	9735
55°	8881	8681	8497
60°	7484	7422	7274
65°	6474	6498	6449
70°	5945	5976	5976
75°	5711	5711	5751
80°	5373	5434	5373
85°	4326	4813	4813



TEST NUMBER: P564107

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.1	2.1
10°-20°	535.3	6.0
20°-30°	807.4	9.1
30°-40°	962.0	10.9
40°-50°	948.5	10.7
50°-60°	724.9	8.2
60°-70°	448.6	5.1
70°-80°	254.8	2.9
80°-90°	79.0	0.9
90°-100°	282.5	3.2
100°-110°	777.2	8.8
110°-120°	802.2	9.1
120°-130°	642.7	7.3
130°-140°	504.8	5.7
140°-150°	386.9	4.4
150°-160°	278.2	3.1
160°-170°	170.1	1.9
170°-180°	57.3	0.6
0°-30°	1529.8	17.3
0°-40°	2491.9	28.2
0°-60°	4165.2	47.1
0°-90°	4947.6	55.9
90°-120°	1861.9	21.0
90°-150°	3396.4	38.4
90°-180°	3902.0	44.1
0°-180°	8849.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1978	1978	1978	1978	1978	
5°	1989	1967	1973	1966	1963	189
15°	1914	1894	1902	1895	1892	540
25°	1774	1752	1762	1743	1742	816
35°	1563	1544	1549	1529	1527	975
45°	1264	1248	1242	1220	1217	969
55°	828	815	810	796	792	742
65°	445	441	446	443	443	451
75°	240	240	240	242	242	254
85°	61	65	68	68	68	71
90°	1	5	9	12	12	5
95°	42	154	500	214	136	44
105°	139	214	856	1304	1217	146
115°	246	300	687	1368	1552	243
125°	339	386	623	1054	1235	302
135°	409	454	605	852	965	316
145°	473	505	596	726	782	296
155°	535	553	593	653	672	246
165°	579	586	595	619	623	163
175°	599	600	596	604	603	57
180°	599	599	599	599	599	



TEST NUMBER: P564107

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1978.5	1978.5	1978.5	1978.5	1978.5
2.5°	1990.8	1973.5	1978.5	1974.2	1964.9
5°	1988.7	1967.1	1973.4	1966.5	1963.2
7.5°	1973.4	1952.1	1958.4	1951.5	1949.5
10°	1959.8	1939.8	1946.1	1939.2	1935.9
12.5°	1944.8	1923.4	1931.1	1922.9	1919.6
15°	1913.8	1893.8	1901.8	1894.9	1891.6
17.5°	1879.7	1858.3	1866.4	1858.4	1854.1
20°	1852.4	1832.4	1840.5	1828.5	1826.8
22.5°	1822.4	1802.4	1810.5	1794.5	1794.1
25°	1774.0	1752.4	1762.1	1743.3	1741.6
27.5°	1716.4	1696.4	1704.5	1685.4	1683.4
30°	1676.9	1656.9	1665.0	1644.4	1641.1
32.5°	1631.9	1613.2	1620.0	1599.5	1597.5
35°	1562.7	1544.4	1549.1	1528.6	1526.9
37.5°	1484.0	1467.3	1470.0	1447.5	1445.8
40°	1428.1	1411.4	1412.7	1388.8	1387.2
42.5°	1366.7	1350.1	1348.7	1324.8	1323.1
45°	1264.5	1247.8	1242.3	1220.1	1216.8
47.5°	1147.9	1131.3	1121.0	1102.9	1100.5
50°	1063.4	1046.7	1037.8	1022.4	1017.4
52.5°	972.0	955.4	947.8	933.8	928.8
55°	828.2	814.9	809.5	795.8	792.4
57.5°	691.5	682.5	681.0	667.7	666.3
60°	608.4	603.4	603.3	591.3	591.3
62.5°	537.5	533.8	536.5	528.6	527.3
65°	444.8	441.4	446.5	443.1	443.1
67.5°	371.5	371.5	374.6	373.2	373.2
70°	330.6	330.6	332.3	332.3	332.3
72.5°	293.8	292.5	296.9	296.8	295.5
75°	240.3	240.3	240.3	242.0	242.0
77.5°	187.1	187.4	188.8	188.4	187.1
80°	151.7	153.3	153.4	151.7	151.7
82.5°	116.2	117.9	117.9	117.6	116.2
85°	61.3	64.7	68.2	68.2	68.2
87.5°	18.0	24.1	29.1	29.5	28.2
90°	1.3	5.0	8.9	11.5	11.5
92.5°	17.6	75.2	130.2	50.0	41.0
95°	42.1	154.2	499.5	213.6	136.4
97.5°	68.6	171.0	762.3	587.4	414.4
100°	87.9	181.4	844.9	852.8	695.8
102.5°	106.3	193.8	866.3	1058.0	914.0
105°	138.9	213.7	856.4	1304.2	1217.0
107.5°	170.0	238.3	807.7	1424.8	1450.7
110°	192.4	254.7	771.0	1454.8	1544.5



TEST NUMBER: P564107

CATALOG NUMBER: SQ4-PR1-075U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.8	273.1	734.3	1435.5	1572.1
115°	246.0	299.5	686.9	1367.8	1552.2
117.5°	277.6	326.9	656.8	1272.7	1481.3
120°	296.9	344.3	643.6	1201.5	1417.1
122.5°	314.3	361.6	634.4	1139.1	1343.7
125°	339.0	386.3	623.2	1054.2	1234.9
127.5°	362.4	407.5	615.8	983.3	1141.8
130°	374.7	420.8	611.7	941.2	1085.8
132.5°	388.9	435.0	608.6	904.2	1034.8
135°	409.1	453.9	605.3	852.5	964.7
137.5°	427.9	469.5	602.5	810.8	903.3
140°	442.2	480.8	601.5	783.1	866.6
142.5°	454.4	490.1	599.5	758.3	829.9
145°	472.8	505.2	596.4	726.4	782.5
147.5°	492.4	520.3	594.9	698.1	743.0
150°	504.6	529.6	593.9	682.6	717.5
152.5°	515.9	538.8	592.8	669.2	698.1
155°	535.2	552.7	592.6	652.9	671.6
157.5°	549.2	563.5	592.6	639.5	652.5
160°	559.4	570.7	592.6	632.3	642.3
162.5°	567.6	576.8	593.6	626.1	634.1
165°	578.6	586.0	595.1	619.4	623.2
167.5°	586.2	591.9	596.4	613.8	614.8
170°	591.3	595.0	596.4	611.7	611.7
172.5°	595.4	597.1	596.4	608.6	607.6
175°	598.9	600.2	596.4	604.0	602.8
177.5°	600.0	600.0	595.9	602.0	600.0
180°	598.9	598.9	598.9	598.9	598.9

(END OF REPORT)