

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563733

Luminaire Tested: **SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563733
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29618.4 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563733
CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563733

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16812	16599
35°	16459	16347	16140
40°	15933	15832	15651
45°	15497	15389	15236
50°	14941	14845	14702
55°	14168	13980	13873
60°	12898	12529	12466
65°	11362	10889	10853
70°	9810	9405	9405
75°	8444	8325	8206
80°	7446	7534	7357
85°	5829	6359	6359



TEST NUMBER: P563733

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	540.0	1.8
10°-20°	1541.7	5.2
20°-30°	2309.3	7.8
30°-40°	2708.7	9.1
40°-50°	2717.2	9.2
50°-60°	2318.0	7.8
60°-70°	1511.7	5.1
70°-80°	758.4	2.6
80°-90°	215.4	0.7
90°-100°	1086.8	3.7
100°-110°	2927.6	9.9
110°-120°	3072.5	10.4
120°-130°	2493.2	8.4
130°-140°	1955.4	6.6
140°-150°	1501.2	5.1
150°-160°	1079.4	3.6
160°-170°	659.4	2.2
170°-180°	222.4	0.8
0°-30°	4391.0	14.8
0°-40°	7099.7	24.0
0°-60°	12134.9	41.0
0°-90°	14620.4	49.4
90°-120°	7086.9	23.9
90°-150°	13036.8	44.0
90°-180°	14998.0	50.6
0°-180°	29618.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5710	5710	5710	5710	5710	
5°	5730	5676	5695	5675	5675	544
15°	5510	5456	5480	5460	5450	1554
25°	5075	5016	5040	4994	4990	2333
35°	4384	4340	4354	4304	4299	2739
45°	3563	3539	3538	3503	3503	2744
55°	2642	2633	2607	2592	2587	2348
65°	1561	1532	1496	1486	1491	1558
75°	711	711	701	696	691	771
85°	165	180	180	180	180	194
90°	6	18	36	38	38	18
95°	166	591	1782	911	630	173
105°	542	843	3238	4844	4546	569
115°	956	1170	2696	5210	5892	941
125°	1305	1499	2421	4092	4815	1165
135°	1572	1754	2353	3301	3738	1213
145°	1817	1959	2323	2822	3031	1140
155°	2063	2138	2302	2532	2613	950
165°	2237	2264	2311	2403	2415	631
175°	2326	2323	2314	2347	2341	221
180°	2323	2323	2323	2323	2323	

TEST NUMBER: P563733

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5710.2	5710.2	5710.2	5710.2	5710.2
2.5°	5746.2	5699.2	5710.2	5701.6	5678.2
5°	5730.2	5676.4	5695.2	5675.2	5675.2
7.5°	5691.2	5632.5	5651.1	5631.1	5630.1
10°	5655.1	5596.4	5615.1	5595.0	5590.1
12.5°	5603.1	5544.4	5567.1	5543.0	5542.0
15°	5510.0	5456.2	5480.0	5459.7	5450.0
17.5°	5404.9	5346.2	5374.9	5346.8	5342.9
20°	5324.8	5266.1	5294.8	5254.8	5254.8
22.5°	5228.8	5170.0	5202.7	5150.7	5150.7
25°	5074.6	5015.9	5039.6	4994.4	4989.5
27.5°	4891.4	4833.7	4858.4	4807.3	4806.4
30°	4759.3	4705.5	4734.3	4679.1	4674.2
32.5°	4615.2	4565.3	4586.2	4531.0	4526.1
35°	4384.0	4339.9	4354.0	4303.8	4298.9
37.5°	4140.8	4095.7	4111.7	4068.7	4066.7
40°	3968.6	3939.2	3943.6	3908.3	3898.5
42.5°	3808.5	3775.2	3779.4	3744.4	3742.4
45°	3563.2	3538.8	3538.2	3503.2	3503.2
47.5°	3303.0	3284.4	3279.0	3249.9	3249.0
50°	3122.8	3108.2	3102.8	3077.7	3072.8
52.5°	2934.7	2927.8	2910.6	2889.6	2888.6
55°	2642.4	2632.6	2607.4	2592.2	2587.4
57.5°	2325.1	2305.5	2277.1	2255.1	2259.1
60°	2096.9	2077.3	2036.9	2026.8	2026.8
62.5°	1876.7	1853.2	1812.6	1798.8	1806.6
65°	1561.4	1532.1	1496.4	1486.5	1491.4
67.5°	1275.2	1248.7	1210.1	1210.0	1206.1
70°	1091.0	1076.3	1046.0	1046.0	1046.0
72.5°	926.8	920.0	897.8	897.7	893.8
75°	710.6	710.6	700.6	695.5	690.6
77.5°	532.5	534.4	529.5	524.3	515.5
80°	420.4	430.2	425.4	420.3	415.4
82.5°	316.3	326.1	325.3	316.3	315.3
85°	165.2	179.8	180.2	180.2	180.2
87.5°	45.2	63.2	71.2	71.8	75.8
90°	5.9	17.5	35.5	38.5	38.5
92.5°	72.2	255.1	504.3	242.8	168.7
95°	165.7	591.1	1781.7	911.1	630.4
97.5°	264.6	676.7	2794.4	2334.5	1760.3
100°	340.3	710.8	3116.4	3260.6	2705.0
102.5°	413.7	758.7	3223.0	3954.3	3498.2
105°	541.6	842.6	3237.8	4843.9	4545.9
107.5°	662.3	930.9	3099.8	5301.1	5378.1
110°	742.8	997.5	2974.4	5443.1	5723.8



TEST NUMBER: P563733

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	828.1	1064.2	2853.6	5411.7	5873.0
115°	955.9	1170.1	2696.2	5209.5	5892.5
117.5°	1072.5	1273.4	2574.2	4886.9	5647.4
120°	1148.3	1342.2	2512.7	4655.4	5436.7
122.5°	1214.6	1406.2	2467.7	4418.6	5197.6
125°	1305.2	1499.1	2420.9	4091.8	4815.2
127.5°	1392.2	1583.2	2391.3	3803.5	4449.4
130°	1444.3	1635.3	2379.5	3638.4	4205.5
132.5°	1496.4	1685.0	2367.6	3492.9	4013.8
135°	1571.5	1753.8	2352.9	3301.0	3737.9
137.5°	1643.1	1817.9	2345.2	3138.2	3497.0
140°	1692.9	1860.7	2338.1	3038.0	3362.1
142.5°	1745.0	1901.2	2333.3	2944.5	3217.6
145°	1817.2	1959.0	2323.3	2822.2	3030.6
147.5°	1895.3	2018.6	2313.2	2719.4	2883.2
150°	1947.4	2054.5	2308.5	2654.9	2790.9
152.5°	1994.7	2087.9	2306.1	2602.2	2712.7
155°	2062.8	2138.1	2302.5	2532.3	2613.3
157.5°	2122.6	2181.1	2303.1	2483.1	2537.5
160°	2160.5	2209.7	2305.5	2454.4	2494.9
162.5°	2193.6	2233.6	2307.9	2430.5	2459.4
165°	2237.4	2263.5	2311.4	2403.4	2415.0
167.5°	2272.9	2288.0	2314.4	2382.6	2387.2
170°	2296.6	2302.4	2314.4	2370.6	2370.6
172.5°	2310.8	2312.0	2316.7	2358.8	2358.8
175°	2326.2	2323.3	2314.4	2346.8	2341.0
177.5°	2332.7	2328.1	2316.2	2335.0	2330.4
180°	2323.3	2323.3	2323.3	2323.3	2323.3

(END OF REPORT)