

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564323

Luminaire Tested: **SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564323
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11548.1 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564323
CATALOG NUMBER: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564323

CATALOG NUMBER: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15530	15530	15530
5°	15670	15549	15468
10°	15620	15511	15430
15°	15551	15455	15371
20°	15473	15374	15260
25°	15364	15261	15084
30°	15198	15090	14874
35°	14974	14843	14631
40°	14633	14475	14213
45°	14036	13791	13506
50°	12985	12673	12423
55°	11334	11077	10844
60°	9551	9471	9283
65°	8261	8293	8229
70°	7587	7627	7627
75°	7286	7286	7339
80°	6854	6932	6854
85°	5526	6140	6140



TEST NUMBER: P564323

CATALOG NUMBER: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.8	2.1
10°-20°	683.1	5.9
20°-30°	1030.4	8.9
30°-40°	1227.7	10.6
40°-50°	1210.4	10.5
50°-60°	925.0	8.0
60°-70°	572.5	5.0
70°-80°	325.1	2.8
80°-90°	100.6	0.9
90°-100°	377.3	3.3
100°-110°	1041.6	9.0
110°-120°	1074.2	9.3
120°-130°	863.2	7.5
130°-140°	678.4	5.9
140°-150°	520.3	4.5
150°-160°	373.9	3.2
160°-170°	228.7	2.0
170°-180°	77.1	0.7
0°-30°	1952.3	16.9
0°-40°	3179.9	27.5
0°-60°	5315.4	46.0
0°-90°	6313.5	54.7
90°-120°	2493.0	21.6
90°-150°	4554.9	39.4
90°-180°	5235.0	45.3
0°-180°	11548.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2525	2525	2525	2525	2525	
5°	2538	2510	2518	2510	2505	241
15°	2442	2417	2427	2418	2414	689
25°	2264	2236	2249	2225	2223	1042
35°	1994	1971	1977	1951	1948	1245
45°	1614	1592	1585	1557	1553	1236
55°	1057	1040	1033	1016	1011	947
65°	568	563	570	565	565	575
75°	307	307	307	309	309	324
85°	78	82	87	87	87	91
90°	3	5	10	12	13	7
95°	55	204	684	281	183	59
105°	186	286	1146	1750	1647	197
115°	333	402	923	1827	2078	327
125°	456	519	837	1416	1662	406
135°	549	608	813	1147	1293	425
145°	637	681	803	976	1051	399
155°	718	742	797	876	904	331
165°	777	787	800	832	838	219
175°	806	807	802	813	811	77
180°	806	806	806	806	806	

TEST NUMBER: P564323

CATALOG NUMBER: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2524.8	2524.8	2524.8	2524.8	2524.8
2.5°	2540.5	2518.4	2524.8	2519.4	2507.5
5°	2537.9	2510.3	2518.3	2509.5	2505.3
7.5°	2518.3	2491.1	2499.2	2490.4	2487.9
10°	2500.9	2475.4	2483.5	2474.7	2470.5
12.5°	2481.8	2454.6	2464.4	2453.9	2449.6
15°	2442.2	2416.7	2427.0	2418.2	2413.9
17.5°	2398.7	2371.5	2381.8	2371.6	2366.1
20°	2363.9	2338.4	2348.7	2333.4	2331.3
22.5°	2325.6	2300.1	2310.4	2290.0	2289.5
25°	2263.9	2236.2	2248.7	2224.7	2222.6
27.5°	2190.4	2164.9	2175.2	2150.7	2148.2
30°	2139.9	2114.4	2124.7	2098.5	2094.3
32.5°	2082.5	2058.7	2067.3	2041.1	2038.6
35°	1994.2	1970.8	1976.8	1950.7	1948.5
37.5°	1893.7	1872.5	1875.9	1847.2	1845.0
40°	1822.4	1801.2	1802.8	1772.3	1770.2
42.5°	1744.1	1722.9	1721.1	1690.6	1688.5
45°	1613.6	1592.4	1585.4	1557.0	1552.7
47.5°	1464.9	1443.6	1430.5	1407.4	1404.4
50°	1357.0	1335.8	1324.4	1304.7	1298.3
52.5°	1240.5	1219.2	1209.6	1191.6	1185.2
55°	1056.9	1039.9	1033.0	1015.5	1011.2
57.5°	882.5	871.0	869.0	852.0	850.3
60°	776.4	770.0	769.9	754.6	754.6
62.5°	685.9	681.2	684.6	674.6	672.9
65°	567.6	563.3	569.8	565.4	565.4
67.5°	474.1	474.1	478.0	476.3	476.3
70°	421.9	421.9	424.1	424.1	424.1
72.5°	374.9	373.2	378.8	378.8	377.1
75°	306.6	306.6	306.6	308.8	308.8
77.5°	238.8	239.2	241.0	240.5	238.8
80°	193.5	195.7	195.7	193.5	193.5
82.5°	148.3	150.4	150.5	150.0	148.3
85°	78.3	82.5	87.0	87.0	87.0
87.5°	23.1	30.4	36.9	37.1	35.6
90°	2.6	5.1	10.3	11.6	12.9
92.5°	23.2	96.3	172.2	62.8	49.0
95°	55.4	204.2	684.5	281.4	183.0
97.5°	91.8	228.7	1013.9	780.6	565.4
100°	118.6	243.4	1135.6	1143.7	929.4
102.5°	144.4	260.1	1159.3	1413.1	1209.9
105°	185.6	286.4	1145.9	1749.5	1647.4
107.5°	229.4	319.2	1082.0	1911.7	1949.0
110°	260.4	341.0	1032.5	1946.6	2067.6



TEST NUMBER: P564323

CATALOG NUMBER: SQ4-PR1-100U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.2	365.9	986.1	1919.0	2097.5
115°	332.6	401.9	922.9	1827.1	2077.9
117.5°	371.2	440.3	881.4	1697.7	1983.0
120°	397.0	465.1	864.9	1610.1	1897.4
122.5°	421.8	486.8	851.5	1528.3	1800.5
125°	456.3	519.3	836.6	1415.8	1661.6
127.5°	485.7	548.7	827.8	1320.7	1532.6
130°	505.3	568.3	823.7	1262.5	1455.3
132.5°	523.9	583.9	819.6	1213.6	1388.3
135°	549.1	608.4	813.4	1146.7	1292.9
137.5°	577.5	631.4	810.3	1090.5	1215.3
140°	593.0	645.9	808.2	1053.0	1162.7
142.5°	610.5	659.4	806.2	1019.7	1116.3
145°	636.8	680.9	803.1	976.2	1050.6
147.5°	662.0	700.6	800.2	939.5	997.2
150°	680.6	712.1	799.2	917.6	964.2
152.5°	695.0	724.5	798.2	898.8	937.4
155°	718.0	741.9	796.6	875.9	903.6
157.5°	739.1	757.5	796.9	859.2	878.1
160°	751.5	767.9	797.9	849.8	863.6
162.5°	761.8	776.2	798.9	841.5	852.3
165°	777.3	787.4	800.5	831.6	837.9
167.5°	789.1	795.2	801.8	825.5	827.6
170°	795.3	800.4	801.8	822.4	822.4
172.5°	800.5	803.5	801.8	818.2	817.2
175°	805.6	806.9	801.8	813.3	810.8
177.5°	807.7	806.7	801.5	808.7	806.7
180°	805.6	805.6	805.6	805.6	805.6

(END OF REPORT)