

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564443

Luminaire Tested: **SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564443
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10379.4 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564443
CATALOG NUMBER: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564443

CATALOG NUMBER: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	28	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6214	6214	6214
5°	6270	6222	6190
10°	6250	6207	6174
15°	6223	6184	6151
20°	6191	6152	6106
25°	6148	6107	6035
30°	6082	6038	5952
35°	5992	5939	5855
40°	5855	5792	5687
45°	5617	5518	5404
50°	5196	5071	4971
55°	4535	4432	4339
60°	3822	3789	3715
65°	3305	3318	3294
70°	3036	3052	3052
75°	2916	2916	2937
80°	2742	2773	2742
85°	2209	2456	2456



TEST NUMBER: P564443

CATALOG NUMBER: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	0.9
10°-20°	273.3	2.6
20°-30°	412.3	4.0
30°-40°	491.2	4.7
40°-50°	484.3	4.7
50°-60°	370.1	3.6
60°-70°	229.1	2.2
70°-80°	130.1	1.3
80°-90°	42.1	0.4
90°-100°	565.9	5.5
100°-110°	1530.2	14.7
110°-120°	1608.7	15.5
120°-130°	1306.7	12.6
130°-140°	1025.0	9.9
140°-150°	786.7	7.6
150°-160°	565.8	5.5
160°-170°	345.6	3.3
170°-180°	116.5	1.1
0°-30°	781.2	7.5
0°-40°	1272.4	12.3
0°-60°	2126.9	20.5
0°-90°	2528.1	24.4
90°-120°	3704.8	35.7
90°-150°	6823.3	65.7
90°-180°	7851.0	75.6
0°-180°	10379.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1010	1010	1010	1010	1010	
5°	1016	1004	1008	1004	1002	96
15°	977	967	971	968	966	276
25°	906	895	900	890	889	417
35°	798	789	791	780	780	498
45°	646	637	634	623	621	495
55°	423	416	413	406	405	379
65°	227	225	228	226	226	230
75°	123	123	123	124	124	130
85°	31	33	35	35	35	36
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	



TEST NUMBER: P564443

CATALOG NUMBER: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.3	1010.3	1010.3	1010.3	1010.3
2.5°	1016.6	1007.7	1010.3	1008.1	1003.3
5°	1015.5	1004.5	1007.7	1004.2	1002.5
7.5°	1007.7	996.8	1000.0	996.5	995.5
10°	1000.7	990.5	993.8	990.2	988.5
12.5°	993.1	982.2	986.1	981.9	980.2
15°	977.2	967.0	971.1	967.6	965.9
17.5°	959.8	948.9	953.0	949.0	946.8
20°	945.9	935.7	939.8	933.7	932.8
22.5°	930.6	920.4	924.5	916.3	916.1
25°	905.9	894.8	899.8	890.2	889.3
27.5°	876.5	866.2	870.4	860.6	859.6
30°	856.3	846.1	850.2	839.7	838.0
32.5°	833.3	823.8	827.2	816.7	815.7
35°	798.0	788.6	791.0	780.5	779.7
37.5°	757.8	749.3	750.6	739.1	738.3
40°	729.2	720.7	721.4	709.2	708.3
42.5°	697.9	689.4	688.7	676.5	675.6
45°	645.7	637.2	634.4	623.0	621.3
47.5°	586.2	577.7	572.4	563.2	562.0
50°	543.0	534.5	529.9	522.1	519.5
52.5°	496.4	487.8	484.0	476.8	474.3
55°	422.9	416.1	413.3	406.3	404.6
57.5°	353.1	348.5	347.7	340.9	340.2
60°	310.7	308.1	308.0	302.0	302.0
62.5°	274.5	272.6	273.9	269.9	269.2
65°	227.1	225.4	228.0	226.3	226.3
67.5°	189.7	189.7	191.3	190.6	190.6
70°	168.8	168.8	169.7	169.7	169.7
72.5°	150.0	149.3	151.6	151.6	150.9
75°	122.7	122.7	122.7	123.6	123.6
77.5°	95.5	95.7	96.4	96.2	95.5
80°	77.4	78.3	78.3	77.4	77.4
82.5°	59.3	60.2	60.2	60.0	59.3
85°	31.3	33.0	34.8	34.8	34.8
87.5°	9.6	13.3	17.3	17.6	16.6
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6



TEST NUMBER: P564443

CATALOG NUMBER: SQ4-PR1-150U-050D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)