

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565029

Luminaire Tested: **SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565029
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23528.6 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 172.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565029

CATALOG NUMBER: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P565029

CATALOG NUMBER: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31				
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	32	31	26				
3	79	70	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22				
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16				
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	19	18	14				
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13				
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	13	10				
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10305	10305	10305
5°	10372	10289	10244
10°	10289	10206	10150
15°	10180	10067	10029
20°	10058	9903	9884
25°	9918	9737	9707
30°	9708	9561	9498
35°	9432	9299	9244
40°	9138	8996	8960
45°	8782	8667	8629
50°	8418	8347	8291
55°	8026	8026	7898
60°	7536	7681	7409
65°	6896	7240	6724
70°	6079	6663	5919
75°	5191	5964	5051
80°	4026	5019	4079
85°	2604	3853	3437



TEST NUMBER: P565029

CATALOG NUMBER: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.5	1.3
10°-20°	890.8	3.8
20°-30°	1321.4	5.6
30°-40°	1546.1	6.6
40°-50°	1539.2	6.5
50°-60°	1329.2	5.6
60°-70°	956.8	4.1
70°-80°	501.7	2.1
80°-90°	129.9	0.6
90°-100°	1086.8	4.6
100°-110°	2927.6	12.4
110°-120°	3072.5	13.1
120°-130°	2493.2	10.6
130°-140°	1955.4	8.3
140°-150°	1501.2	6.4
150°-160°	1079.4	4.6
160°-170°	659.4	2.8
170°-180°	222.4	0.9
0°-30°	2527.7	10.7
0°-40°	4073.8	17.3
0°-60°	6942.3	29.5
0°-90°	8530.6	36.3
90°-120°	7086.9	30.1
90°-150°	13036.8	55.4
90°-180°	14998.0	63.7
0°-180°	23528.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3351	3351	3351	3351	3351	
5°	3360	3322	3333	3324	3318	318
15°	3197	3157	3162	3156	3150	901
25°	2923	2874	2870	2852	2861	1344
35°	2512	2478	2477	2454	2462	1571
45°	2019	2002	1993	1987	1984	1558
55°	1497	1494	1497	1476	1473	1335
65°	948	976	995	956	924	939
75°	437	477	502	468	425	468
85°	74	97	109	103	97	97
90°	6	18	36	38	38	14
95°	166	591	1782	911	630	173
105°	542	843	3238	4844	4546	569
115°	956	1170	2696	5210	5892	941
125°	1305	1499	2421	4092	4815	1165
135°	1572	1754	2353	3301	3738	1213
145°	1817	1959	2323	2822	3031	1140
155°	2063	2138	2302	2532	2613	950
165°	2237	2264	2311	2403	2415	631
175°	2326	2323	2314	2347	2341	221
180°	2323	2323	2323	2323	2323	

TEST NUMBER: P565029

CATALOG NUMBER: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3350.7	3350.7	3350.7	3350.7	3350.7
2.5°	3369.6	3341.9	3350.7	3343.3	3327.1
5°	3359.6	3322.1	3333.0	3324.0	3318.3
7.5°	3325.3	3290.7	3298.8	3289.2	3285.8
10°	3294.6	3260.0	3268.1	3256.1	3250.4
12.5°	3259.2	3222.3	3230.3	3218.4	3214.9
15°	3197.2	3156.8	3161.8	3155.8	3150.0
17.5°	3125.2	3084.2	3085.0	3075.6	3074.4
20°	3073.2	3029.9	3026.0	3014.3	3020.1
22.5°	3016.5	2970.9	2966.9	2950.6	2958.7
25°	2922.7	2873.6	2869.5	2852.0	2860.7
27.5°	2814.0	2765.5	2765.6	2741.0	2750.3
30°	2733.7	2687.5	2692.4	2663.1	2674.7
32.5°	2648.7	2607.1	2609.7	2580.5	2592.0
35°	2512.3	2477.7	2476.9	2453.5	2462.1
37.5°	2373.0	2342.4	2337.5	2324.0	2326.3
40°	2276.1	2250.2	2240.7	2231.9	2231.9
42.5°	2174.6	2150.9	2141.5	2135.0	2132.7
45°	2019.3	2002.0	1992.7	1986.8	1983.9
47.5°	1865.8	1849.6	1841.6	1837.4	1834.5
50°	1759.5	1748.0	1744.7	1735.8	1732.9
52.5°	1653.2	1646.3	1643.2	1631.9	1629.0
55°	1496.8	1493.9	1496.8	1476.0	1473.1
57.5°	1333.8	1338.4	1348.0	1320.1	1313.1
60°	1225.2	1236.7	1248.8	1216.0	1204.5
62.5°	1114.2	1132.6	1149.6	1112.0	1095.9
65°	947.7	976.5	994.9	955.8	924.0
67.5°	787.1	822.8	844.9	802.8	767.0
70°	676.1	716.5	741.0	698.8	658.3
72.5°	579.2	624.3	644.2	604.3	563.9
75°	436.9	477.3	501.9	468.4	425.1
77.5°	310.0	348.1	368.4	339.3	303.5
80°	227.3	267.7	283.4	259.1	230.3
82.5°	161.2	194.7	205.5	190.9	171.2
85°	73.8	96.9	109.2	103.2	97.4
87.5°	20.1	38.6	52.0	52.6	54.9
90°	5.9	17.5	35.5	38.5	38.5
92.5°	72.2	255.1	504.3	242.8	168.7
95°	165.7	591.1	1781.7	911.1	630.4
97.5°	264.6	676.7	2794.4	2334.5	1760.3
100°	340.3	710.8	3116.4	3260.6	2705.0
102.5°	413.7	758.7	3223.0	3954.3	3498.2
105°	541.6	842.6	3237.8	4843.9	4545.9
107.5°	662.3	930.9	3099.8	5301.1	5378.1
110°	742.8	997.5	2974.4	5443.1	5723.8

TEST NUMBER: P565029

CATALOG NUMBER: SQ4-PW1-125U-075D-835-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	828.1	1064.2	2853.6	5411.7	5873.0
115°	955.9	1170.1	2696.2	5209.5	5892.5
117.5°	1072.5	1273.4	2574.2	4886.9	5647.4
120°	1148.3	1342.2	2512.7	4655.4	5436.7
122.5°	1214.6	1406.2	2467.7	4418.6	5197.6
125°	1305.2	1499.1	2420.9	4091.8	4815.2
127.5°	1392.2	1583.2	2391.3	3803.5	4449.4
130°	1444.3	1635.3	2379.5	3638.4	4205.5
132.5°	1496.4	1685.0	2367.6	3492.9	4013.8
135°	1571.5	1753.8	2352.9	3301.0	3737.9
137.5°	1643.1	1817.9	2345.2	3138.2	3497.0
140°	1692.9	1860.7	2338.1	3038.0	3362.1
142.5°	1745.0	1901.2	2333.3	2944.5	3217.6
145°	1817.2	1959.0	2323.3	2822.2	3030.6
147.5°	1895.3	2018.6	2313.2	2719.4	2883.2
150°	1947.4	2054.5	2308.5	2654.9	2790.9
152.5°	1994.7	2087.9	2306.1	2602.2	2712.7
155°	2062.8	2138.1	2302.5	2532.3	2613.3
157.5°	2122.6	2181.1	2303.1	2483.1	2537.5
160°	2160.5	2209.7	2305.5	2454.4	2494.9
162.5°	2193.6	2233.6	2307.9	2430.5	2459.4
165°	2237.4	2263.5	2311.4	2403.4	2415.0
167.5°	2272.9	2288.0	2314.4	2382.6	2387.2
170°	2296.6	2302.4	2314.4	2370.6	2370.6
172.5°	2310.8	2312.0	2316.7	2358.8	2358.8
175°	2326.2	2323.3	2314.4	2346.8	2341.0
177.5°	2332.7	2328.1	2316.2	2335.0	2330.4
180°	2323.3	2323.3	2323.3	2323.3	2323.3

(END OF REPORT)