

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P565043

Luminaire Tested: **SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565043
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10221.9 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565043
CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565043

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	32	31	26
3	79	70	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	19	18	14
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8954	8954	8954
5°	9012	8940	8901
10°	8939	8868	8820
15°	8845	8747	8714
20°	8740	8605	8588
25°	8617	8461	8434
30°	8435	8308	8253
35°	8196	8080	8032
40°	7940	7817	7785
45°	7631	7530	7497
50°	7315	7253	7204
55°	6974	6974	6863
60°	6548	6674	6437
65°	5992	6290	5842
70°	5282	5789	5143
75°	4511	5181	4389
80°	3500	4360	3542
85°	2265	3352	2985



TEST NUMBER: P565043

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.1	1.3
10°-20°	387.0	3.8
20°-30°	574.1	5.6
30°-40°	671.7	6.6
40°-50°	668.7	6.5
50°-60°	577.5	5.6
60°-70°	415.7	4.1
70°-80°	218.0	2.1
80°-90°	56.4	0.6
90°-100°	472.2	4.6
100°-110°	1271.9	12.4
110°-120°	1334.8	13.1
120°-130°	1083.2	10.6
130°-140°	849.5	8.3
140°-150°	652.2	6.4
150°-160°	468.9	4.6
160°-170°	286.5	2.8
170°-180°	96.6	0.9
0°-30°	1098.1	10.7
0°-40°	1769.9	17.3
0°-60°	3016.0	29.5
0°-90°	3706.1	36.3
90°-120°	3078.9	30.1
90°-150°	5663.8	55.4
90°-180°	6516.0	63.7
0°-180°	10221.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1456	1456	1456	1456	1456	
5°	1460	1443	1448	1444	1442	138
15°	1389	1372	1374	1371	1368	392
25°	1270	1248	1247	1239	1243	584
35°	1092	1076	1076	1066	1070	682
45°	877	870	866	863	862	677
55°	650	649	650	641	640	580
65°	412	424	432	415	401	408
75°	190	207	218	204	185	203
85°	32	42	48	45	42	42
90°	3	8	15	17	17	6
95°	72	257	774	396	274	75
105°	235	366	1407	2104	1975	247
115°	415	508	1171	2263	2560	409
125°	567	651	1052	1778	2092	506
135°	683	762	1022	1434	1624	527
145°	790	851	1009	1226	1317	495
155°	896	929	1000	1100	1135	413
165°	972	983	1004	1044	1049	274
175°	1011	1009	1006	1020	1017	96
180°	1009	1009	1009	1009	1009	

TEST NUMBER: P565043

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1455.7	1455.7	1455.7	1455.7	1455.7
2.5°	1463.9	1451.9	1455.7	1452.5	1445.5
5°	1459.6	1443.3	1448.0	1444.1	1441.6
7.5°	1444.7	1429.6	1433.1	1429.0	1427.5
10°	1431.3	1416.3	1419.8	1414.6	1412.1
12.5°	1416.0	1399.9	1403.4	1398.2	1396.7
15°	1389.0	1371.5	1373.6	1371.0	1368.5
17.5°	1357.7	1339.9	1340.3	1336.2	1335.7
20°	1335.2	1316.3	1314.6	1309.6	1312.1
22.5°	1310.5	1290.7	1289.0	1281.9	1285.4
25°	1269.7	1248.4	1246.7	1239.0	1242.8
27.5°	1222.5	1201.5	1201.5	1190.8	1194.8
30°	1187.7	1167.6	1169.7	1157.0	1162.0
32.5°	1150.7	1132.7	1133.8	1121.1	1126.1
35°	1091.5	1076.4	1076.1	1065.9	1069.7
37.5°	1030.9	1017.6	1015.5	1009.7	1010.7
40°	988.9	977.6	973.5	969.6	969.6
42.5°	944.7	934.5	930.4	927.5	926.5
45°	877.3	869.8	865.7	863.1	861.9
47.5°	810.6	803.6	800.1	798.2	797.0
50°	764.4	759.4	758.0	754.1	752.9
52.5°	718.2	715.2	713.9	709.0	707.7
55°	650.3	649.0	650.3	641.3	640.0
57.5°	579.5	581.5	585.6	573.5	570.5
60°	532.3	537.3	542.5	528.3	523.3
62.5°	484.0	492.1	499.4	483.1	476.1
65°	411.7	424.2	432.2	415.2	401.4
67.5°	341.9	357.5	367.1	348.8	333.2
70°	293.7	311.3	321.9	303.6	286.0
72.5°	251.6	271.2	279.9	262.5	245.0
75°	189.8	207.4	218.0	203.5	184.7
77.5°	134.7	151.2	160.1	147.4	131.8
80°	98.8	116.3	123.1	112.6	100.0
82.5°	70.0	84.6	89.3	82.9	74.4
85°	32.1	42.1	47.5	44.8	42.3
87.5°	8.7	16.8	22.6	22.9	23.9
90°	2.6	7.6	15.4	16.7	16.7
92.5°	31.4	110.8	219.1	105.5	73.3
95°	72.0	256.8	774.0	395.8	273.9
97.5°	114.9	294.0	1214.0	1014.2	764.8
100°	147.9	308.8	1353.9	1416.6	1175.2
102.5°	179.8	329.6	1400.2	1717.9	1519.8
105°	235.3	366.0	1406.6	2104.4	1974.9
107.5°	287.8	404.4	1346.7	2303.1	2336.5
110°	322.7	433.4	1292.2	2364.7	2486.7



TEST NUMBER: P565043

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.8	462.3	1239.7	2351.1	2551.5
115°	415.3	508.3	1171.3	2263.3	2560.0
117.5°	466.0	553.2	1118.4	2123.1	2453.5
120°	498.9	583.1	1091.6	2022.5	2362.0
122.5°	527.7	610.9	1072.1	1919.6	2258.1
125°	567.0	651.3	1051.8	1777.6	2091.9
127.5°	604.8	687.8	1038.9	1652.4	1933.0
130°	627.5	710.4	1033.8	1580.7	1827.1
132.5°	650.1	732.1	1028.6	1517.5	1743.8
135°	682.7	761.9	1022.2	1434.1	1623.9
137.5°	713.9	789.8	1018.8	1363.4	1519.3
140°	735.5	808.4	1015.8	1319.8	1460.6
142.5°	758.1	826.0	1013.7	1279.2	1397.9
145°	789.5	851.1	1009.3	1226.1	1316.6
147.5°	823.4	877.0	1005.0	1181.4	1252.6
150°	846.0	892.6	1002.9	1153.4	1212.5
152.5°	866.6	907.1	1001.9	1130.5	1178.5
155°	896.2	928.9	1000.3	1100.1	1135.3
157.5°	922.2	947.5	1000.6	1078.8	1102.4
160°	938.6	960.0	1001.6	1066.3	1083.9
162.5°	953.0	970.4	1002.6	1055.9	1068.5
165°	972.0	983.4	1004.2	1044.2	1049.2
167.5°	987.5	994.0	1005.5	1035.1	1037.1
170°	997.8	1000.3	1005.5	1029.9	1029.9
172.5°	1003.9	1004.4	1006.5	1024.8	1024.8
175°	1010.6	1009.4	1005.5	1019.6	1017.0
177.5°	1013.4	1011.4	1006.2	1014.4	1012.4
180°	1009.3	1009.3	1009.3	1009.3	1009.3

(END OF REPORT)