

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565115

Luminaire Tested: **SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P565115  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10366.7 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 84.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P565115  
CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P565115

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	68	64	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	22	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6075	6075	6075
5°	6114	6066	6039
10°	6065	6016	5984
15°	6001	5935	5912
20°	5930	5839	5827
25°	5847	5740	5723
30°	5723	5636	5599
35°	5560	5482	5449
40°	5387	5303	5282
45°	5177	5110	5087
50°	4962	4921	4888
55°	4731	4731	4656
60°	4442	4528	4367
65°	4065	4269	3965
70°	3584	3928	3491
75°	3061	3515	2978
80°	2373	2958	2405
85°	1538	2272	2025



TEST NUMBER: P565115

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.0	0.9
10°-20°	262.6	2.5
20°-30°	389.5	3.8
30°-40°	455.7	4.4
40°-50°	453.7	4.4
50°-60°	391.8	3.8
60°-70°	282.0	2.7
70°-80°	147.9	1.4
80°-90°	39.2	0.4
90°-100°	565.9	5.5
100°-110°	1530.2	14.8
110°-120°	1608.7	15.5
120°-130°	1306.7	12.6
130°-140°	1025.0	9.9
140°-150°	786.7	7.6
150°-160°	565.8	5.5
160°-170°	345.6	3.3
170°-180°	116.5	1.1
0°-30°	745.1	7.2
0°-40°	1200.8	11.6
0°-60°	2046.3	19.7
0°-90°	2515.4	24.3
90°-120°	3704.8	35.7
90°-150°	6823.3	65.8
90°-180°	7851.0	75.7
0°-180°	10366.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	988	988	988	988	988	
5°	990	979	982	980	978	94
15°	942	930	932	930	928	266
25°	862	847	846	841	843	396
35°	740	730	730	723	726	463
45°	595	590	587	586	585	459
55°	441	440	441	435	434	394
65°	279	288	293	282	272	277
75°	129	141	148	138	125	138
85°	22	29	32	30	29	29
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	

TEST NUMBER: P565115

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	987.7	987.7	987.7	987.7	987.7
2.5°	993.2	985.1	987.7	985.5	980.7
5°	990.3	979.2	982.5	979.8	978.1
7.5°	980.2	970.0	972.4	969.5	968.5
10°	971.1	960.9	963.3	959.8	958.1
12.5°	960.7	949.8	952.2	948.7	947.6
15°	942.4	930.5	932.0	930.2	928.5
17.5°	921.2	909.1	909.4	906.6	906.2
20°	905.9	893.1	892.0	888.5	890.2
22.5°	889.2	875.7	874.5	869.7	872.1
25°	861.5	847.0	845.8	840.7	843.2
27.5°	829.5	815.2	815.2	808.0	810.7
30°	805.8	792.2	793.6	785.0	788.4
32.5°	780.7	768.5	769.3	760.6	764.0
35°	740.5	730.3	730.1	723.2	725.7
37.5°	699.5	690.4	689.0	685.0	685.7
40°	670.9	663.3	660.5	657.9	657.9
42.5°	641.0	634.0	631.2	629.3	628.6
45°	595.2	590.1	587.4	585.6	584.8
47.5°	550.0	545.2	542.8	541.6	540.7
50°	518.6	515.2	514.3	511.7	510.8
52.5°	487.3	485.3	484.4	481.0	480.2
55°	441.2	440.3	441.2	435.1	434.2
57.5°	393.2	394.5	397.3	389.1	387.1
60°	361.1	364.5	368.1	358.4	355.0
62.5°	328.4	333.9	338.9	327.8	323.0
65°	279.3	287.8	293.3	281.7	272.4
67.5°	232.0	242.5	249.1	236.6	226.1
70°	199.3	211.2	218.4	206.0	194.1
72.5°	170.7	184.0	189.9	178.1	166.2
75°	128.8	140.7	147.9	138.1	125.3
77.5°	91.4	102.6	108.6	100.0	89.5
80°	67.0	78.9	83.5	76.4	67.9
82.5°	47.5	57.4	60.6	56.3	50.5
85°	21.8	28.6	32.2	30.4	28.7
87.5°	6.1	11.9	16.6	16.9	17.3
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6



TEST NUMBER: P565115

CATALOG NUMBER: SQ4-PW1-150U-050D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)