

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P565163

Luminaire Tested: **SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565163
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12774.9 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 112.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565163
CATALOG NUMBER: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565163

CATALOG NUMBER: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	57	50	45	46	41	38	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	27	25	23	21	17
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11897	11897	11897
5°	11974	11879	11827
10°	11878	11782	11719
15°	11752	11622	11579
20°	11612	11434	11411
25°	11450	11241	11207
30°	11207	11038	10966
35°	10889	10736	10672
40°	10550	10386	10344
45°	10139	10006	9962
50°	9719	9638	9572
55°	9265	9265	9119
60°	8700	8868	8553
65°	7961	8358	7763
70°	7019	7692	6834
75°	5994	6885	5832
80°	4647	5795	4707
85°	3006	4453	3966



TEST NUMBER: P565163

CATALOG NUMBER: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.1	1.4
10°-20°	514.2	4.0
20°-30°	762.8	6.0
30°-40°	892.5	7.0
40°-50°	888.5	7.0
50°-60°	767.3	6.0
60°-70°	552.3	4.3
70°-80°	289.6	2.3
80°-90°	74.3	0.6
90°-100°	565.9	4.4
100°-110°	1530.2	12.0
110°-120°	1608.7	12.6
120°-130°	1306.7	10.2
130°-140°	1025.0	8.0
140°-150°	786.7	6.2
150°-160°	565.8	4.4
160°-170°	345.6	2.7
170°-180°	116.5	0.9
0°-30°	1459.1	11.4
0°-40°	2351.6	18.4
0°-60°	4007.4	31.4
0°-90°	4923.7	38.5
90°-120°	3704.8	29.0
90°-150°	6823.3	53.4
90°-180°	7851.0	61.5
0°-180°	12774.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1934	1934	1934	1934	1934	
5°	1939	1918	1924	1919	1916	184
15°	1846	1822	1825	1822	1818	520
25°	1687	1659	1656	1646	1651	776
35°	1450	1430	1430	1416	1421	907
45°	1166	1156	1150	1147	1145	899
55°	864	862	864	852	850	771
65°	547	564	574	552	533	542
75°	252	276	290	270	245	270
85°	43	56	63	60	56	56
90°	3	8	17	18	17	7
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	

TEST NUMBER: P565163

CATALOG NUMBER: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1934.2	1934.2	1934.2	1934.2	1934.2
2.5°	1945.1	1929.1	1934.2	1929.9	1920.6
5°	1939.3	1917.7	1924.0	1918.8	1915.5
7.5°	1919.6	1899.6	1904.2	1898.7	1896.7
10°	1901.8	1881.8	1886.5	1879.6	1876.3
12.5°	1881.4	1860.1	1864.7	1857.8	1855.8
15°	1845.6	1822.3	1825.1	1821.7	1818.3
17.5°	1804.0	1780.4	1780.8	1775.4	1774.7
20°	1774.0	1749.0	1746.8	1740.0	1743.3
22.5°	1741.3	1715.0	1712.7	1703.2	1707.9
25°	1687.1	1658.8	1656.4	1646.3	1651.3
27.5°	1624.4	1596.4	1596.4	1582.3	1587.6
30°	1578.0	1551.4	1554.2	1537.3	1544.0
32.5°	1529.0	1505.0	1506.5	1489.6	1496.2
35°	1450.2	1430.2	1429.8	1416.3	1421.3
37.5°	1369.8	1352.1	1349.3	1341.5	1342.9
40°	1313.9	1298.9	1293.5	1288.3	1288.3
42.5°	1255.3	1241.6	1236.2	1232.4	1231.1
45°	1165.6	1155.6	1150.3	1146.9	1145.2
47.5°	1077.0	1067.7	1063.0	1060.6	1059.0
50°	1015.7	1009.0	1007.2	1002.0	1000.3
52.5°	954.3	950.3	948.5	942.0	940.4
55°	864.0	862.3	864.0	852.0	850.4
57.5°	769.9	772.6	778.1	762.0	758.0
60°	707.2	713.9	720.9	702.0	695.3
62.5°	643.1	653.8	663.6	641.9	632.6
65°	547.0	563.7	574.3	551.7	533.4
67.5°	454.3	475.0	487.7	463.4	442.7
70°	390.3	413.6	427.7	403.4	380.0
72.5°	334.4	360.3	371.8	348.8	325.5
75°	252.2	275.5	289.7	270.4	245.4
77.5°	178.9	200.9	212.7	195.8	175.2
80°	131.2	154.5	163.6	149.6	132.9
82.5°	93.0	112.4	118.6	110.2	98.8
85°	42.6	55.9	63.1	59.6	56.2
87.5°	11.4	21.8	29.3	29.6	30.7
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6

TEST NUMBER: P565163

CATALOG NUMBER: SQ4-PW1-150U-100D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)