

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565187

Luminaire Tested: **SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565187
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14133.9 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 127.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565187
CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565187

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	38
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15182	15182	15182
5°	15280	15160	15092
10°	15158	15036	14955
15°	14997	14831	14776
20°	14818	14591	14562
25°	14612	14346	14302
30°	14303	14086	13994
35°	13896	13700	13619
40°	13463	13253	13201
45°	12939	12769	12712
50°	12402	12299	12216
55°	11824	11824	11637
60°	11102	11316	10915
65°	10160	10667	9907
70°	8956	9817	8722
75°	7650	8786	7443
80°	5933	7396	6007
85°	3839	5681	5067



TEST NUMBER: P565187

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	1.6
10°-20°	656.2	4.6
20°-30°	973.4	6.9
30°-40°	1139.0	8.1
40°-50°	1133.9	8.0
50°-60°	979.1	6.9
60°-70°	704.8	5.0
70°-80°	369.6	2.6
80°-90°	94.2	0.7
90°-100°	565.9	4.0
100°-110°	1530.2	10.8
110°-120°	1608.7	11.4
120°-130°	1306.7	9.2
130°-140°	1025.0	7.3
140°-150°	786.7	5.6
150°-160°	565.8	4.0
160°-170°	345.6	2.4
170°-180°	116.5	0.8
0°-30°	1862.0	13.2
0°-40°	3001.0	21.2
0°-60°	5114.0	36.2
0°-90°	6282.6	44.5
90°-120°	3704.8	26.2
90°-150°	6823.3	48.3
90°-180°	7851.0	55.5
0°-180°	14133.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2468	2468	2468	2468	2468	
5°	2475	2447	2455	2449	2444	234
15°	2355	2326	2329	2325	2320	664
25°	2153	2117	2114	2101	2107	990
35°	1851	1825	1825	1807	1814	1157
45°	1488	1475	1468	1464	1461	1148
55°	1103	1100	1103	1087	1085	984
65°	698	719	733	704	681	692
75°	322	352	370	345	313	345
85°	54	71	80	76	72	72
90°	3	8	17	18	17	8
95°	88	308	941	487	290	92
105°	284	440	1698	2504	2401	300
115°	501	612	1408	2725	3076	494
125°	686	786	1269	2141	2515	611
135°	822	919	1235	1729	1957	635
145°	956	1027	1218	1480	1593	598
155°	1079	1121	1207	1328	1371	498
165°	1174	1186	1212	1260	1266	331
175°	1219	1218	1214	1230	1227	116
180°	1218	1218	1218	1218	1218	



TEST NUMBER: P565187

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2468.3	2468.3	2468.3	2468.3	2468.3
2.5°	2482.2	2461.8	2468.3	2462.8	2450.9
5°	2474.8	2447.2	2455.3	2448.6	2444.4
7.5°	2449.6	2424.1	2430.0	2423.0	2420.5
10°	2427.0	2401.5	2407.4	2398.6	2394.4
12.5°	2400.9	2373.7	2379.6	2370.8	2368.3
15°	2355.2	2325.5	2329.1	2324.7	2320.4
17.5°	2302.2	2272.0	2272.6	2265.6	2264.8
20°	2263.9	2232.0	2229.1	2220.5	2224.7
22.5°	2222.1	2188.5	2185.6	2173.6	2179.5
25°	2153.0	2116.8	2113.8	2100.9	2107.3
27.5°	2072.9	2037.2	2037.3	2019.2	2026.0
30°	2013.8	1979.8	1983.3	1961.8	1970.3
32.5°	1951.2	1920.5	1922.5	1900.9	1909.4
35°	1850.7	1825.2	1824.6	1807.3	1813.7
37.5°	1748.0	1725.5	1721.9	1712.0	1713.7
40°	1676.7	1657.6	1650.6	1644.1	1644.1
42.5°	1601.9	1584.5	1577.5	1572.7	1571.0
45°	1487.5	1474.8	1467.9	1463.5	1461.4
47.5°	1374.4	1362.5	1356.6	1353.5	1351.4
50°	1296.1	1287.6	1285.3	1278.7	1276.6
52.5°	1217.8	1212.7	1210.5	1202.1	1200.0
55°	1102.6	1100.5	1102.6	1087.3	1085.2
57.5°	982.5	985.9	993.0	972.4	967.3
60°	902.5	911.0	919.9	895.8	887.3
62.5°	820.7	834.4	846.8	819.2	807.3
65°	698.1	719.4	732.9	704.1	680.7
67.5°	579.8	606.1	622.4	591.4	565.0
70°	498.0	527.8	545.9	514.7	485.0
72.5°	426.7	459.9	474.5	445.1	415.4
75°	321.9	351.6	369.7	345.1	313.2
77.5°	228.3	256.4	271.4	249.9	223.6
80°	167.5	197.2	208.8	190.9	169.6
82.5°	118.7	143.4	151.4	140.6	126.1
85°	54.4	71.4	80.5	76.0	71.8
87.5°	14.4	27.4	36.5	36.8	38.2
90°	2.6	7.7	17.0	18.3	17.0
92.5°	37.2	135.7	267.7	116.2	84.2
95°	87.8	308.3	941.2	487.1	289.7
97.5°	141.0	353.5	1467.1	1214.1	891.6
100°	180.9	371.9	1630.7	1700.6	1375.0
102.5°	217.6	397.3	1688.3	2069.5	1826.0
105°	284.4	439.5	1697.5	2503.9	2401.4
107.5°	346.3	487.8	1623.3	2775.0	2809.1
110°	394.6	522.7	1557.2	2847.8	2992.6

TEST NUMBER: P565187

CATALOG NUMBER: SQ4-PW1-150U-125D-935-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	557.5	1496.4	2833.2	3076.5
115°	500.7	612.2	1407.8	2725.3	3076.5
117.5°	562.6	667.2	1349.4	2560.4	2958.5
120°	600.4	702.9	1314.7	2442.1	2848.4
122.5°	636.0	736.5	1293.8	2315.3	2724.7
125°	685.6	785.5	1268.9	2141.2	2515.4
127.5°	731.2	829.3	1254.2	1999.1	2328.3
130°	756.3	857.6	1247.9	1911.4	2208.7
132.5°	782.6	882.8	1241.6	1832.2	2106.0
135°	821.9	919.3	1234.8	1728.9	1957.0
137.5°	861.5	953.5	1229.0	1645.1	1830.9
140°	888.7	974.6	1226.9	1591.2	1756.5
142.5°	914.9	995.7	1222.7	1542.4	1687.3
145°	955.6	1027.4	1217.7	1479.8	1592.6
147.5°	992.5	1056.1	1212.0	1423.2	1509.8
150°	1019.8	1076.2	1209.9	1392.3	1461.6
152.5°	1045.0	1094.2	1208.8	1363.8	1420.7
155°	1078.8	1121.1	1207.3	1327.5	1371.1
157.5°	1113.9	1143.4	1207.5	1302.3	1331.0
160°	1133.9	1158.2	1208.6	1286.4	1306.9
162.5°	1149.6	1169.8	1209.6	1273.7	1289.1
165°	1174.5	1186.0	1212.5	1259.8	1266.2
167.5°	1191.5	1199.5	1212.8	1248.0	1251.0
170°	1202.0	1205.9	1213.8	1242.7	1242.7
172.5°	1210.4	1211.2	1213.8	1236.3	1235.3
175°	1219.1	1217.8	1213.8	1229.5	1226.9
177.5°	1221.9	1218.9	1213.6	1224.0	1220.9
180°	1217.7	1217.7	1217.7	1217.7	1217.7

(END OF REPORT)