

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519037

Luminaire Tested: **SQ4-WB-025U-100D-935-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519037  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2009-966-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5548.5 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 63.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519037  
CATALOG NUMBER: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519037

CATALOG NUMBER: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	89	89	89	81	81	81	77
1	106	102	98	95	101	97	94	92	89	87	85	82	80	78	75	73	72	69
2	98	91	86	81	93	87	82	78	80	76	73	74	71	68	68	66	64	60
3	90	82	75	70	86	79	73	68	73	68	64	67	63	60	62	59	56	53
4	84	74	67	61	80	71	65	59	66	61	56	61	57	53	57	53	50	48
5	78	67	60	54	74	65	58	53	60	54	50	56	51	48	52	48	45	43
6	73	61	54	48	69	59	52	47	55	49	45	51	47	43	48	44	41	39
7	68	56	49	43	65	54	47	42	51	45	41	48	43	39	45	40	37	35
8	63	52	44	39	61	50	43	38	47	41	37	44	39	35	41	37	34	32
9	60	48	41	36	57	46	40	35	44	38	34	41	36	33	39	34	31	29
10	56	44	37	33	54	43	37	32	41	35	31	38	33	30	36	32	29	27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18102	18102	18102
5°	17876	17812	17916
10°	16889	17042	17437
15°	15591	15953	16668
20°	14158	14691	15663
25°	12699	13391	14592
30°	11355	12097	13482
35°	9929	10647	12169
40°	8357	9021	10534
45°	6897	7492	8795
50°	5759	6277	7328
55°	4888	5386	6051
60°	4178	4671	4830
65°	3327	3928	3120
70°	2949	3066	1904
75°	2731	2486	1167
80°	2515	2288	1006
85°	2279	2096	819



TEST NUMBER: P519037

CATALOG NUMBER: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	269.9	4.9
10°-20°	702.1	12.7
20°-30°	909.5	16.4
30°-40°	890.6	16.1
40°-50°	681.7	12.3
50°-60°	454.2	8.2
60°-70°	247.9	4.5
70°-80°	103.3	1.9
80°-90°	30.3	0.5
90°-100°	94.7	1.7
100°-110°	248.9	4.5
110°-120°	258.1	4.7
120°-130°	207.0	3.7
130°-140°	162.4	2.9
140°-150°	124.6	2.2
150°-160°	89.8	1.6
160°-170°	54.9	1.0
170°-180°	18.6	0.3
0°-30°	1881.5	33.9
0°-40°	2772.1	50.0
0°-60°	3908.1	70.4
0°-90°	4289.5	77.3
90°-120°	601.6	10.8
90°-150°	1095.7	19.7
90°-180°	1259.0	22.7
0°-180°	5548.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2943	2943	2943	2943	2943	
5°	2895	2866	2885	2892	2902	269
15°	2448	2440	2505	2573	2618	684
25°	1871	1876	1973	2059	2150	861
35°	1322	1329	1418	1513	1621	822
45°	793	808	861	926	1011	618
55°	456	475	502	521	564	413
65°	229	248	270	236	214	238
75°	115	115	105	72	49	123
85°	32	32	30	19	12	35
90°	1	4	10	5	5	3
95°	12	49	163	84	57	14
105°	45	68	275	418	390	48
115°	80	97	220	440	502	79
125°	111	124	200	339	400	98
135°	132	145	194	274	310	102
145°	153	163	192	233	252	96
155°	173	178	192	211	217	80
165°	187	189	192	199	202	53
175°	194	194	193	196	196	18
180°	194	194	194	194	194	



TEST NUMBER: P519037

CATALOG NUMBER: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2943.0	2943.0	2943.0	2943.0	2943.0
2.5°	2950.2	2924.0	2930.6	2930.4	2922.3
5°	2895.2	2866.2	2884.9	2891.6	2901.7
7.5°	2787.8	2765.8	2799.9	2825.2	2845.6
10°	2704.1	2685.2	2728.6	2765.4	2791.9
12.5°	2607.0	2591.1	2645.0	2694.3	2728.9
15°	2448.4	2439.6	2505.2	2573.4	2617.6
17.5°	2278.7	2274.4	2349.8	2429.3	2485.9
20°	2163.0	2161.8	2244.4	2327.2	2392.9
22.5°	2046.3	2049.1	2135.9	2222.1	2296.8
25°	1871.2	1876.2	1973.2	2059.2	2150.1
27.5°	1709.2	1711.5	1811.8	1902.6	1999.5
30°	1598.7	1605.0	1703.3	1797.3	1898.3
32.5°	1488.2	1495.5	1591.7	1688.9	1791.9
35°	1322.3	1328.7	1417.9	1513.3	1620.7
37.5°	1151.4	1160.0	1239.2	1329.4	1435.0
40°	1040.8	1053.5	1123.5	1208.5	1312.0
42.5°	934.4	950.1	1015.0	1095.6	1189.1
45°	792.9	808.0	861.3	926.5	1011.1
47.5°	671.0	688.4	729.4	785.5	857.7
50°	601.8	618.2	656.0	697.6	765.8
52.5°	540.8	557.2	590.9	623.0	681.1
55°	455.8	474.8	502.3	521.4	564.3
57.5°	386.1	404.3	426.1	434.7	460.8
60°	339.6	359.8	379.7	378.7	392.6
62.5°	297.3	314.4	334.2	320.5	321.3
65°	228.6	247.5	269.9	235.8	214.4
67.5°	184.7	188.7	211.8	164.5	139.0
70°	164.0	164.0	170.5	127.4	105.9
72.5°	144.4	144.4	138.4	103.6	81.1
75°	114.9	114.9	104.6	71.8	49.1
77.5°	88.6	87.6	80.1	53.6	35.6
80°	71.0	71.0	64.6	42.3	28.4
82.5°	55.5	55.5	50.1	33.0	21.2
85°	32.3	32.3	29.7	19.2	11.6
87.5°	11.6	12.1	12.3	7.2	6.2
90°	1.2	3.7	10.0	5.0	5.0
92.5°	5.2	25.2	55.8	24.7	15.9
95°	12.5	49.0	163.1	84.1	57.3
97.5°	21.7	53.8	244.0	194.1	142.9
100°	28.6	57.9	268.9	272.5	211.7
102.5°	34.6	61.9	275.9	339.5	287.4
105°	44.8	68.0	275.2	417.7	389.7
107.5°	55.3	76.7	259.5	458.3	465.2
110°	62.3	81.7	246.5	468.8	498.0



TEST NUMBER: P519037

CATALOG NUMBER: SQ4-WB-025U-100D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	69.2	87.7	234.6	462.2	507.0
115°	79.7	96.7	220.4	439.7	501.8
117.5°	89.9	105.5	210.7	408.5	477.4
120°	95.9	110.5	206.7	387.5	454.4
122.5°	101.8	116.5	203.7	366.6	432.5
125°	110.8	124.2	200.5	338.8	399.7
127.5°	118.0	131.7	197.7	316.4	367.8
130°	122.0	136.6	196.7	302.4	349.9
132.5°	126.0	140.6	195.7	290.3	332.9
135°	132.0	145.4	194.2	273.5	310.0
137.5°	138.2	151.3	194.0	260.9	290.8
140°	143.2	155.4	193.0	250.9	278.9
142.5°	147.2	158.4	193.0	243.8	267.9
145°	153.1	162.9	191.7	233.2	251.5
147.5°	159.1	168.6	191.7	224.5	239.6
150°	163.1	171.6	191.7	219.4	231.6
152.5°	167.1	173.7	191.7	215.4	224.6
155°	173.1	177.9	191.7	210.6	216.6
157.5°	177.5	182.2	191.7	206.3	210.7
160°	180.5	184.2	191.7	204.2	206.7
162.5°	183.5	186.2	191.7	202.3	204.7
165°	186.8	189.2	191.7	199.3	201.7
167.5°	189.7	191.0	193.0	198.0	199.0
170°	191.7	193.0	193.0	198.0	198.0
172.5°	192.7	193.0	193.0	196.9	196.0
175°	194.2	194.2	193.0	195.5	195.5
177.5°	194.2	194.2	193.2	195.2	194.2
180°	194.2	194.2	194.2	194.2	194.2

(END OF REPORT)