

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562642

Luminaire Tested: **SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562642
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4252.0 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 36.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562642

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562642

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8519	8519	8519
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8511
20°	8462	8487	8487
25°	8382	8443	8417
30°	8280	8380	8344
35°	8157	8282	8224
40°	8022	8136	8053
45°	7877	7932	7809
50°	7670	7670	7548
55°	7427	7330	7221
60°	7069	6927	6816
65°	6534	6403	6346
70°	5722	5767	5743
75°	4602	5090	5119
80°	3273	4314	4362
85°	1990	3620	3620



TEST NUMBER: P562642

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.4	2.1
10°-20°	250.8	5.9
20°-30°	379.8	8.9
30°-40°	455.3	10.7
40°-50°	464.3	10.9
50°-60°	405.3	9.5
60°-70°	290.2	6.8
70°-80°	149.4	3.5
80°-90°	38.8	0.9
90°-100°	127.2	3.0
100°-110°	345.7	8.1
110°-120°	355.4	8.4
120°-130°	284.2	6.7
130°-140°	223.3	5.3
140°-150°	171.2	4.0
150°-160°	123.1	2.9
160°-170°	75.3	1.8
170°-180°	25.4	0.6
0°-30°	718.0	16.9
0°-40°	1173.3	27.6
0°-60°	2042.9	48.0
0°-90°	2521.3	59.3
90°-120°	828.3	19.5
90°-150°	1507.0	35.4
90°-180°	1731.0	40.7
0°-180°	4252.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	923	923	923	923	923	
5°	927	918	921	918	918	88
15°	892	884	892	892	891	251
25°	823	818	829	827	827	379
35°	724	723	735	730	730	453
45°	604	602	608	600	598	465
55°	462	456	456	449	449	412
65°	299	293	293	291	291	296
75°	129	135	143	144	144	140
85°	19	29	34	35	34	26
90°	1	3	6	8	8	2
95°	19	70	222	96	65	20
105°	61	96	380	579	545	65
115°	109	132	304	605	690	108
125°	150	171	275	464	547	134
135°	181	201	268	378	426	140
145°	209	224	264	321	345	131
155°	236	244	262	288	297	109
165°	256	259	263	274	275	72
175°	265	266	264	268	267	25
180°	265	265	265	265	265	

TEST NUMBER: P562642

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	923.4	923.4	923.4	923.4	923.4
2.5°	928.9	920.9	923.4	921.3	918.0
5°	926.9	917.7	920.9	918.3	917.5
7.5°	920.2	911.0	915.2	913.5	912.7
10°	914.0	904.8	909.8	908.0	907.2
12.5°	905.8	897.3	902.9	901.2	901.0
15°	891.8	884.3	891.8	891.8	891.0
17.5°	874.2	867.3	875.4	875.9	875.4
20°	861.9	854.4	864.4	863.6	864.4
22.5°	846.8	840.6	851.5	849.2	850.1
25°	823.4	817.6	829.4	826.8	826.8
27.5°	795.7	791.5	804.4	801.7	801.7
30°	777.2	773.1	786.6	783.2	783.2
32.5°	756.7	753.9	766.8	762.7	762.7
35°	724.2	722.6	735.3	730.2	730.2
37.5°	690.7	689.2	700.8	694.6	692.6
40°	666.1	665.2	675.5	668.6	668.6
42.5°	641.5	640.6	649.5	641.3	641.3
45°	603.7	602.0	607.9	600.2	598.5
47.5°	562.4	560.8	564.5	556.1	555.3
50°	534.4	532.7	534.4	526.7	525.9
52.5°	505.7	502.7	502.9	495.2	495.1
55°	461.7	455.9	455.7	448.9	448.9
57.5°	415.2	407.5	408.2	402.4	401.5
60°	383.1	374.7	375.4	370.2	369.4
62.5°	351.6	341.9	343.9	338.1	337.9
65°	299.3	292.6	293.3	290.7	290.7
67.5°	249.0	242.8	247.3	245.2	245.1
70°	212.1	207.9	213.8	213.7	212.9
72.5°	177.8	177.7	185.0	185.0	185.5
75°	129.1	135.0	142.8	143.6	143.6
77.5°	86.2	96.6	105.2	105.5	105.3
80°	61.6	73.3	81.2	82.9	82.1
82.5°	41.7	54.1	60.7	62.4	61.6
85°	18.8	28.8	34.2	35.0	34.2
87.5°	5.6	12.2	14.9	15.2	13.8
90°	0.9	3.4	6.0	7.7	7.7
92.5°	7.7	34.8	60.5	26.0	22.0
95°	18.8	69.6	221.6	96.4	64.8
97.5°	31.0	76.9	339.7	264.3	185.6
100°	39.2	81.7	375.9	381.0	307.7
102.5°	47.4	86.6	385.4	471.2	406.6
105°	61.4	95.5	380.1	578.8	544.6
107.5°	75.9	106.0	358.2	634.4	643.9
110°	86.1	113.6	341.8	645.3	686.1



TEST NUMBER: P562642

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.0	121.1	325.4	636.2	697.7
115°	109.1	132.4	304.3	605.4	689.5
117.5°	122.4	144.7	290.8	561.6	656.5
120°	131.3	152.9	284.7	532.3	626.5
122.5°	138.8	160.4	280.6	502.9	593.7
125°	150.0	170.8	275.3	463.9	547.2
127.5°	160.1	180.7	272.4	434.3	505.8
130°	166.2	186.2	271.0	415.7	479.9
132.5°	172.3	192.3	269.7	399.8	456.7
135°	180.7	200.7	267.6	377.8	426.2
137.5°	189.7	207.9	266.6	358.4	399.1
140°	195.2	212.7	265.9	346.0	382.7
142.5°	200.6	216.8	265.2	336.3	367.0
145°	208.8	223.8	264.2	321.0	345.2
147.5°	218.0	230.9	263.4	309.0	328.0
150°	224.2	235.0	263.4	302.1	317.1
152.5°	228.9	238.4	262.7	295.9	308.2
155°	236.1	244.4	262.5	288.3	296.6
157.5°	243.1	249.6	262.5	283.1	289.5
160°	247.2	253.0	262.5	279.7	284.7
162.5°	251.3	255.8	263.2	276.9	280.6
165°	255.7	259.0	263.4	274.5	275.3
167.5°	260.3	262.0	264.2	271.6	272.2
170°	261.7	263.3	264.2	270.2	270.2
172.5°	263.0	264.0	264.2	268.8	268.8
175°	265.1	265.9	264.2	267.6	266.8
177.5°	265.8	265.8	263.7	266.4	265.1
180°	265.1	265.1	265.1	265.1	265.1

(END OF REPORT)