

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519686

Luminaire Tested: **SQ4-050U-0D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519686  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3461.5 lumens  
Efficiency: N/A  
Efficacy: 146.1 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Indirect

Input Watts (W): 23.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519686  
CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P519686

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	1985	23458	6860
100°	2083	19972	16349
105°	2187	13551	19415
110°	2323	9220	18509
115°	2382	6643	15054
120°	2422	5253	11560
125°	2413	4428	8802
130°	2386	3890	6887
135°	2358	3492	5560
140°	2351	3203	4609
145°	2352	2976	3888
150°	2388	2806	3378
155°	2403	2672	3019
160°	2427	2577	2795
165°	2442	2515	2630
170°	2451	2475	2531
175°	2455	2447	2471



TEST NUMBER: P519686

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	254.5	7.4
100°-110°	691.4	20.0
110°-120°	710.8	20.5
120°-130°	568.3	16.4
130°-140°	446.6	12.9
140°-150°	342.4	9.9
150°-160°	246.2	7.1
160°-170°	150.6	4.4
170°-180°	50.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1656.7	47.9
90°-150°	3014.0	87.1
90°-180°	3462.0	100.0
0°-180°	3461.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	12	15	15	
95°	38	139	443	193	130	42
105°	123	191	760	1158	1089	130
115°	218	265	609	1211	1379	215
125°	300	342	551	928	1094	267
135°	361	401	535	756	852	279
145°	418	448	528	642	690	262
155°	472	489	525	577	593	218
165°	511	518	527	549	551	144
175°	530	532	528	535	534	50
180°	530	530	530	530	530	



TEST NUMBER: P519686

CATALOG NUMBER: SQ4-050U-0D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.7	6.7	11.9	15.3	15.3
92.5°	15.3	69.7	121.0	52.0	44.0
95°	37.5	139.2	443.2	192.9	129.6
97.5°	62.1	153.7	679.5	528.6	371.3
100°	78.4	163.4	751.8	762.1	615.4
102.5°	94.8	173.1	770.9	942.5	813.1
105°	122.7	191.1	760.3	1157.6	1089.3
107.5°	151.7	212.1	716.3	1268.7	1287.7
110°	172.2	227.2	683.6	1290.6	1372.3
112.5°	189.9	242.2	650.8	1272.4	1395.4
115°	218.2	264.9	608.6	1210.7	1379.1
117.5°	244.8	289.5	581.6	1123.3	1312.9
120°	262.5	305.9	569.4	1064.6	1252.9
122.5°	277.5	320.9	561.2	1005.8	1187.5
125°	300.0	341.7	550.6	927.7	1094.4
127.5°	320.1	361.5	544.8	868.5	1011.6
130°	332.4	372.4	542.1	831.4	959.7
132.5°	344.7	384.7	539.4	799.7	913.4
135°	361.4	401.4	535.3	755.7	852.3
137.5°	379.5	415.8	533.2	716.8	798.1
140°	390.4	425.4	531.9	692.1	765.4
142.5°	401.3	433.6	530.5	672.7	734.0
145°	417.6	447.6	528.4	642.1	690.4
147.5°	436.1	461.7	526.7	618.0	656.0
150°	448.3	470.0	526.7	604.1	634.1
152.5°	457.9	476.9	525.4	591.7	616.4
155°	472.2	488.9	525.0	576.6	593.2
157.5°	486.2	499.2	525.0	566.2	578.9
160°	494.4	506.0	525.0	559.4	569.4
162.5°	502.5	511.5	526.4	553.8	561.2
165°	511.4	518.1	526.7	548.9	550.6
167.5°	520.6	523.9	528.4	543.1	544.5
170°	523.3	526.7	528.4	540.4	540.4
172.5°	526.1	528.1	528.4	537.7	537.7
175°	530.2	531.8	528.4	535.2	533.6
177.5°	531.5	531.5	527.4	532.8	530.2
180°	530.2	530.2	530.2	530.2	530.2

(END OF REPORT)