

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562858

Luminaire Tested: **SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562858  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3348.7 lumens  
Efficiency: N/A  
Efficacy: 102.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562858  
CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562858

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11321	11321	11321
5°	11405	11332	11290
10°	11378	11325	11293
15°	11319	11319	11307
20°	11244	11277	11277
25°	11138	11218	11184
30°	11002	11135	11087
35°	10838	11004	10927
40°	10659	10809	10700
45°	10466	10540	10377
50°	10192	10192	10029
55°	9868	9740	9595
60°	9392	9202	9056
65°	8680	8508	8433
70°	7602	7661	7631
75°	6117	6762	6805
80°	4346	5733	5797
85°	2646	4806	4806



TEST NUMBER: P562858

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.1	3.5
10°-20°	333.2	10.0
20°-30°	504.6	15.1
30°-40°	605.0	18.1
40°-50°	616.9	18.4
50°-60°	538.5	16.1
60°-70°	385.5	11.5
70°-80°	198.6	5.9
80°-90°	50.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.0	28.5
0°-40°	1559.0	46.6
0°-60°	2714.4	81.1
0°-90°	3348.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3348.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1227	1227	1227	1227	1227	
5°	1232	1219	1224	1220	1219	117
15°	1185	1175	1185	1185	1184	334
25°	1094	1086	1102	1099	1099	504
35°	962	960	977	970	970	602
45°	802	800	808	798	795	617
55°	614	606	606	596	596	547
65°	398	389	390	386	386	393
75°	172	179	190	191	191	185
85°	25	38	45	47	45	35
90°	0	0	0	0	0	



TEST NUMBER: P562858

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1227.0	1227.0	1227.0	1227.0	1227.0
2.5°	1234.3	1223.6	1227.0	1224.2	1219.7
5°	1231.5	1219.3	1223.6	1220.1	1219.0
7.5°	1222.7	1210.5	1216.1	1213.8	1212.7
10°	1214.5	1202.3	1208.8	1206.5	1205.4
12.5°	1203.6	1192.3	1199.7	1197.4	1197.2
15°	1185.0	1175.0	1185.0	1184.9	1183.8
17.5°	1161.5	1152.4	1163.1	1163.8	1163.1
20°	1145.2	1135.2	1148.6	1147.5	1148.6
22.5°	1125.2	1117.0	1131.3	1128.4	1129.5
25°	1094.1	1086.3	1102.0	1098.6	1098.6
27.5°	1057.3	1051.7	1068.8	1065.2	1065.2
30°	1032.7	1027.2	1045.2	1040.7	1040.7
32.5°	1005.4	1001.7	1018.9	1013.4	1013.4
35°	962.3	960.1	977.0	970.2	970.2
37.5°	917.7	915.7	931.1	922.9	920.2
40°	885.0	883.9	897.5	888.4	888.4
42.5°	852.3	851.2	863.0	852.1	852.1
45°	802.1	799.9	807.8	797.5	795.3
47.5°	747.3	745.1	750.1	738.9	737.8
50°	710.1	707.8	710.1	699.8	698.7
52.5°	671.9	667.9	668.3	658.0	657.8
55°	613.5	605.7	605.5	596.5	596.5
57.5°	551.7	541.5	542.4	534.6	533.5
60°	509.0	497.9	498.7	491.9	490.8
62.5°	467.2	454.3	456.9	449.2	449.0
65°	397.6	388.7	389.7	386.3	386.3
67.5°	330.8	322.6	328.6	325.8	325.6
70°	281.8	276.2	284.0	284.0	282.9
72.5°	236.3	236.1	245.9	245.9	246.5
75°	171.6	179.3	189.7	190.9	190.9
77.5°	114.5	128.3	139.7	140.2	140.0
80°	81.8	97.4	107.9	110.2	109.1
82.5°	55.4	71.9	80.7	82.9	81.8
85°	25.0	38.3	45.4	46.6	45.4
87.5°	7.3	15.3	18.2	18.1	16.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)