

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P518702

Luminaire Tested: **SQ4-BB-100U-050D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518702
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9159.9 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518702
CATALOG NUMBER: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518702

CATALOG NUMBER: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	93	89	86	82	82	79	77	74	61	60	58	45	44	43	30	29	29	22
2	85	79	73	69	76	70	66	62	55	52	49	40	39	37	27	26	25	20
3	78	70	63	58	70	63	57	53	49	45	42	36	34	32	25	24	23	18
4	72	62	55	50	64	56	50	45	44	40	37	33	31	28	23	21	20	16
5	66	56	49	43	59	50	44	39	40	36	32	30	27	25	21	19	18	15
6	61	50	43	38	55	45	39	35	36	32	28	27	25	22	19	18	17	13
7	57	46	38	33	51	41	35	31	33	29	25	25	22	20	18	16	15	12
8	53	41	34	30	47	38	31	27	30	26	23	23	20	18	17	15	14	11
9	49	38	31	26	44	34	28	24	28	23	20	21	19	17	16	14	13	10
10	46	35	28	24	41	32	26	22	26	21	19	20	17	15	15	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8424	8424	8424
5°	8288	8267	8329
10°	7755	7858	8078
15°	7050	7274	7679
20°	6258	6583	7160
25°	5450	5881	6578
30°	4668	5181	6028
35°	3871	4398	5363
40°	2974	3516	4569
45°	2150	2662	3677
50°	1465	1984	2917
55°	952	1435	2266
60°	546	1010	1639
65°	145	617	830
70°	71	190	239
75°	32	16	0
80°	24	0	0
85°	0	0	0



TEST NUMBER: P518702

CATALOG NUMBER: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	1.8
10°-20°	426.2	4.7
20°-30°	533.5	5.8
30°-40°	492.8	5.4
40°-50°	331.1	3.6
50°-60°	171.0	1.9
60°-70°	53.6	0.6
70°-80°	3.4	0.0
80°-90°	2.3	0.0
90°-100°	503.0	5.5
100°-110°	1388.8	15.2
110°-120°	1432.3	15.6
120°-130°	1150.9	12.6
130°-140°	904.5	9.9
140°-150°	693.7	7.6
150°-160°	498.6	5.4
160°-170°	304.9	3.3
170°-180°	102.8	1.1
0°-30°	1126.3	12.3
0°-40°	1619.1	17.7
0°-60°	2121.2	23.2
0°-90°	2180.4	23.8
90°-120°	3324.1	36.3
90°-150°	6073.2	66.3
90°-180°	6979.0	76.2
0°-180°	9159.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1826	1826	1826	1826	1826	
5°	1790	1772	1785	1792	1799	166
15°	1476	1471	1523	1574	1608	411
25°	1071	1079	1156	1234	1292	491
35°	687	704	781	873	952	426
45°	330	349	408	488	564	259
55°	118	138	178	229	282	110
65°	13	25	56	68	76	22
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	3	7	14	16	17	5
95°	74	272	913	375	244	79
105°	248	382	1528	2333	2196	263
115°	443	536	1231	2436	2770	436
125°	608	692	1115	1888	2215	541
135°	732	811	1084	1529	1724	566
145°	849	908	1071	1302	1401	532
155°	957	989	1062	1168	1205	441
165°	1036	1050	1067	1109	1117	292
175°	1074	1076	1069	1084	1081	102
180°	1074	1074	1074	1074	1074	

TEST NUMBER: P518702

CATALOG NUMBER: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1826.0	1826.0	1826.0	1826.0	1826.0
2.5°	1830.2	1812.9	1817.5	1817.4	1812.5
5°	1789.7	1771.6	1785.3	1791.7	1798.6
7.5°	1714.1	1700.0	1726.3	1746.1	1760.4
10°	1655.5	1643.4	1677.5	1704.5	1724.4
12.5°	1587.6	1578.3	1619.6	1656.6	1682.0
15°	1476.1	1471.0	1523.0	1574.1	1607.8
17.5°	1356.7	1356.5	1415.9	1479.4	1520.0
20°	1274.7	1277.3	1341.0	1411.0	1458.5
22.5°	1192.7	1198.8	1266.8	1339.7	1394.2
25°	1070.7	1079.3	1155.5	1234.5	1292.4
27.5°	953.3	966.0	1046.1	1128.3	1198.8
30°	876.3	891.0	972.6	1059.1	1131.6
32.5°	800.7	818.1	897.7	989.1	1063.1
35°	687.3	704.5	780.9	872.8	952.3
37.5°	570.1	587.1	661.7	752.1	838.0
40°	493.8	512.8	583.9	671.6	758.8
42.5°	424.6	443.6	510.4	596.6	679.0
45°	329.5	349.4	408.1	487.6	563.6
47.5°	250.7	272.3	323.8	395.7	465.0
50°	204.1	225.7	276.5	339.8	406.4
52.5°	166.6	187.5	233.4	293.1	354.1
55°	118.4	138.2	178.4	229.1	281.8
57.5°	81.8	98.9	135.0	177.3	218.5
60°	59.2	75.6	109.5	143.9	177.6
62.5°	39.4	54.4	87.6	113.9	136.6
65°	13.3	25.3	56.5	68.2	76.0
67.5°	6.7	8.1	29.7	31.3	33.9
70°	5.3	5.3	14.1	15.1	17.7
72.5°	3.9	3.9	5.7	7.3	7.8
75°	1.8	1.8	0.9	0.0	0.0
77.5°	0.9	0.9	0.7	0.0	0.0
80°	0.9	0.9	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.7	1.4	2.7	3.1	3.4
90°	3.4	6.8	13.7	15.5	17.2
92.5°	30.9	128.4	229.6	83.8	65.3
95°	73.9	272.2	912.6	375.1	244.1
97.5°	122.4	304.9	1351.9	1040.9	753.8
100°	158.1	324.5	1514.2	1524.9	1239.2
102.5°	192.5	346.8	1545.8	1884.1	1613.2
105°	247.5	381.9	1527.9	2332.6	2196.5
107.5°	305.9	425.6	1442.7	2548.9	2598.7
110°	347.2	454.7	1376.7	2595.5	2756.8



TEST NUMBER: P518702

CATALOG NUMBER: SQ4-BB-100U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.3	487.8	1314.8	2558.7	2796.7
115°	443.4	535.9	1230.6	2436.1	2770.5
117.5°	495.0	587.1	1175.2	2263.6	2644.0
120°	529.4	620.1	1153.2	2146.8	2529.9
122.5°	562.4	649.1	1135.4	2037.7	2400.7
125°	608.4	692.4	1115.4	1887.7	2215.4
127.5°	647.6	731.6	1103.7	1760.9	2043.5
130°	673.7	757.8	1098.2	1683.3	1940.4
132.5°	698.5	778.5	1092.7	1618.1	1851.0
135°	732.2	811.1	1084.5	1528.9	1723.9
137.5°	770.0	841.9	1080.4	1454.0	1620.4
140°	790.6	861.2	1077.6	1404.1	1550.3
142.5°	814.0	879.2	1074.9	1359.7	1488.4
145°	849.0	907.9	1070.7	1301.6	1400.7
147.5°	882.7	934.1	1067.0	1252.6	1329.6
150°	907.5	949.5	1065.6	1223.4	1285.6
152.5°	926.7	966.0	1064.2	1198.4	1249.8
155°	957.3	989.2	1062.2	1167.8	1204.8
157.5°	985.5	1010.0	1062.5	1145.6	1170.8
160°	1002.0	1023.8	1063.9	1133.0	1151.5
162.5°	1015.8	1034.9	1065.2	1122.0	1136.4
165°	1036.4	1049.8	1067.3	1108.8	1117.2
167.5°	1052.2	1060.3	1069.0	1100.7	1103.4
170°	1060.4	1067.2	1069.0	1096.5	1096.5
172.5°	1067.3	1071.3	1069.0	1091.0	1089.7
175°	1074.2	1075.9	1069.0	1084.4	1081.1
177.5°	1076.9	1075.6	1068.7	1078.2	1075.6
180°	1074.2	1074.2	1074.2	1074.2	1074.2

(END OF REPORT)