

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P518942

Luminaire Tested: **SQ4-BB-150U-100D-935-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518942
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14716.9 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 148.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518942

CATALOG NUMBER: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518942

CATALOG NUMBER: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	94	90	87	84	84	81	78	76	64	62	61	48	47	46	34	33	33	26				
2	86	80	75	70	77	72	68	64	57	54	52	44	42	40	31	30	29	24				
3	80	71	65	60	71	64	59	55	52	48	45	40	37	35	29	27	26	21				
4	73	64	57	51	66	58	52	47	46	42	39	36	33	31	26	25	24	19				
5	68	57	50	45	61	52	46	41	42	38	34	33	30	28	24	23	21	18				
6	63	52	44	39	56	47	41	36	38	34	30	30	27	25	22	21	19	16				
7	58	47	40	35	52	43	37	32	35	30	27	28	25	22	21	19	18	15				
8	54	43	36	31	49	39	33	29	32	28	24	26	22	20	19	17	16	14				
9	50	39	32	28	45	36	30	26	30	25	22	24	21	18	18	16	15	13				
10	47	36	29	25	43	33	27	23	27	23	20	22	19	17	17	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16417	16417	16417
5°	16152	16113	16232
10°	15113	15315	15742
15°	13740	14175	14965
20°	12196	12830	13954
25°	10621	11462	12821
30°	9098	10097	11748
35°	7543	8571	10452
40°	5796	6853	8906
45°	4190	5189	7166
50°	2854	3868	5684
55°	1855	2797	4417
60°	1065	1970	3193
65°	282	1203	1617
70°	139	371	464
75°	61	30	0
80°	45	0	0
85°	0	0	0



TEST NUMBER: P518942

CATALOG NUMBER: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.8	2.2
10°-20°	830.5	5.6
20°-30°	1039.7	7.1
30°-40°	960.4	6.5
40°-50°	645.3	4.4
50°-60°	333.3	2.3
60°-70°	104.4	0.7
70°-80°	6.6	0.0
80°-90°	3.5	0.0
90°-100°	754.6	5.1
100°-110°	2040.2	13.9
110°-120°	2145.0	14.6
120°-130°	1742.3	11.8
130°-140°	1366.7	9.3
140°-150°	1049.0	7.1
150°-160°	754.4	5.1
160°-170°	460.8	3.1
170°-180°	155.4	1.1
0°-30°	2195.0	14.9
0°-40°	3155.4	21.4
0°-60°	4134.1	28.1
0°-90°	4248.6	28.9
90°-120°	4939.8	33.6
90°-150°	9097.7	61.8
90°-180°	10468.0	71.1
0°-180°	14716.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3559	3559	3559	3559	3559	
5°	3488	3453	3480	3492	3505	323
15°	2877	2867	2968	3068	3133	801
25°	2087	2104	2252	2406	2519	957
35°	1339	1373	1522	1701	1856	830
45°	642	681	795	950	1098	504
55°	231	269	348	446	549	215
65°	26	49	110	133	148	44
75°	3	3	2	0	0	5
85°	0	0	0	0	0	0
90°	4	10	23	24	23	8
95°	117	411	1255	649	386	123
105°	379	586	2263	3339	3202	399
115°	668	816	1877	3634	4102	659
125°	914	1047	1692	2855	3354	815
135°	1096	1226	1646	2305	2609	847
145°	1274	1370	1624	1973	2124	797
155°	1438	1495	1610	1770	1828	663
165°	1566	1581	1617	1680	1688	441
175°	1625	1624	1618	1639	1636	154
180°	1624	1624	1624	1624	1624	

TEST NUMBER: P518942

CATALOG NUMBER: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3558.7	3558.7	3558.7	3558.7	3558.7
2.5°	3566.9	3533.3	3542.1	3541.9	3532.5
5°	3488.1	3452.7	3479.5	3491.8	3505.3
7.5°	3340.7	3313.1	3364.5	3403.0	3430.9
10°	3226.4	3202.8	3269.4	3322.0	3360.7
12.5°	3094.2	3076.0	3156.5	3228.5	3278.0
15°	2876.9	2866.8	2968.1	3067.8	3133.4
17.5°	2644.1	2643.8	2759.5	2883.2	2962.3
20°	2484.4	2489.4	2613.5	2749.9	2842.5
22.5°	2324.6	2336.4	2468.9	2611.1	2717.1
25°	2086.6	2103.5	2251.9	2406.0	2518.8
27.5°	1858.0	1882.6	2038.8	2198.9	2336.3
30°	1707.9	1736.5	1895.5	2064.0	2205.4
32.5°	1560.5	1594.5	1749.5	1927.7	2071.8
35°	1339.4	1373.1	1521.9	1701.1	1855.9
37.5°	1111.2	1144.2	1289.5	1465.8	1633.2
40°	962.4	999.4	1138.0	1308.9	1478.9
42.5°	827.4	864.5	994.8	1162.7	1323.3
45°	642.2	680.9	795.4	950.3	1098.4
47.5°	488.6	530.7	631.2	771.3	906.3
50°	397.7	439.8	538.9	662.3	792.0
52.5°	324.7	365.4	454.9	571.2	690.0
55°	230.7	269.4	347.8	446.5	549.2
57.5°	159.4	192.8	263.1	345.5	425.9
60°	115.4	147.3	213.5	280.4	346.1
62.5°	76.8	106.1	170.8	222.1	266.2
65°	25.8	49.4	110.2	132.9	148.1
67.5°	13.1	15.8	57.8	61.1	66.1
70°	10.3	10.3	27.5	29.4	34.4
72.5°	7.6	7.6	11.0	14.1	15.2
75°	3.4	3.4	1.7	0.0	0.0
77.5°	1.7	1.7	1.4	0.0	0.0
80°	1.7	1.7	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.7	2.1	4.5	4.9	4.5
90°	3.5	10.3	22.7	24.4	22.7
92.5°	49.6	180.9	356.9	154.9	112.2
95°	117.1	411.0	1254.9	649.4	386.3
97.5°	188.1	471.4	1956.1	1618.8	1188.8
100°	241.2	495.8	2174.2	2267.5	1833.4
102.5°	290.1	529.7	2251.1	2759.3	2434.6
105°	379.3	586.0	2263.3	3338.6	3201.9
107.5°	461.8	650.4	2164.4	3700.0	3745.4
110°	526.1	697.0	2076.3	3797.0	3990.1

TEST NUMBER: P518942

CATALOG NUMBER: SQ4-BB-150U-100D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	583.4	743.4	1995.2	3777.6	4102.0
115°	667.6	816.3	1877.1	3633.7	4102.0
117.5°	750.1	889.6	1799.1	3413.9	3944.7
120°	800.5	937.2	1753.0	3256.1	3797.9
122.5°	848.0	982.0	1725.0	3087.0	3632.9
125°	914.1	1047.4	1691.8	2854.9	3353.9
127.5°	974.9	1105.8	1672.2	2665.5	3104.4
130°	1008.5	1143.5	1663.9	2548.5	2945.0
132.5°	1043.4	1177.0	1655.5	2442.9	2807.9
135°	1095.8	1225.7	1646.4	2305.2	2609.4
137.5°	1148.6	1271.3	1638.7	2193.5	2441.3
140°	1185.0	1299.5	1635.9	2121.5	2342.0
142.5°	1219.9	1327.6	1630.3	2056.6	2249.7
145°	1274.1	1369.8	1623.7	1973.1	2123.5
147.5°	1323.4	1408.2	1616.0	1897.5	2013.1
150°	1359.7	1434.9	1613.2	1856.5	1948.7
152.5°	1393.3	1458.9	1611.8	1818.3	1894.2
155°	1438.4	1494.8	1609.7	1770.0	1828.1
157.5°	1485.2	1524.5	1610.0	1736.4	1774.7
160°	1511.8	1544.3	1611.4	1715.2	1742.5
162.5°	1532.8	1559.8	1612.8	1698.2	1718.7
165°	1566.0	1581.4	1616.7	1679.8	1688.3
167.5°	1588.7	1599.3	1617.0	1664.0	1668.1
170°	1602.7	1607.8	1618.4	1656.9	1656.9
172.5°	1613.9	1614.9	1618.4	1648.4	1647.1
175°	1625.4	1623.7	1618.4	1639.3	1635.9
177.5°	1629.3	1625.2	1618.1	1632.0	1627.9
180°	1623.7	1623.7	1623.7	1623.7	1623.7

(END OF REPORT)