

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563098

Luminaire Tested: **SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563098
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6945.8 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563098
CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563098

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	24	23	17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5780	5780	5780
5°	5825	5787	5765
10°	5810	5783	5766
15°	5780	5780	5774
20°	5742	5758	5758
25°	5688	5728	5711
30°	5618	5686	5661
35°	5535	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5205	5205	5121
55°	5040	4974	4900
60°	4796	4700	4624
65°	4432	4344	4305
70°	3882	3911	3898
75°	3123	3454	3476
80°	2221	2928	2959
85°	1355	2456	2456



TEST NUMBER: P563098

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.3	0.9
10°-20°	170.2	2.4
20°-30°	257.7	3.7
30°-40°	308.9	4.4
40°-50°	315.0	4.5
50°-60°	275.0	4.0
60°-70°	196.9	2.8
70°-80°	101.4	1.5
80°-90°	27.3	0.4
90°-100°	377.3	5.4
100°-110°	1020.1	14.7
110°-120°	1072.5	15.4
120°-130°	871.2	12.5
130°-140°	683.3	9.8
140°-150°	524.5	7.6
150°-160°	377.2	5.4
160°-170°	230.4	3.3
170°-180°	77.7	1.1
0°-30°	487.1	7.0
0°-40°	796.1	11.5
0°-60°	1386.1	20.0
0°-90°	1711.7	24.6
90°-120°	2469.9	35.6
90°-150°	4548.9	65.5
90°-180°	5234.0	75.4
0°-180°	6945.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	626	626	626	626	626	
5°	629	623	625	623	622	60
15°	605	600	605	605	604	171
25°	559	555	563	561	561	257
35°	491	490	499	495	495	307
45°	410	408	412	407	406	315
55°	313	309	309	305	305	279
65°	203	198	199	197	197	201
75°	88	92	97	98	98	95
85°	13	20	23	24	23	17
90°	2	5	11	12	11	4
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	



TEST NUMBER: P563098

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	626.5	626.5	626.5	626.5	626.5
2.5°	630.3	624.8	626.5	625.1	622.8
5°	628.9	622.6	624.8	623.0	622.5
7.5°	624.3	618.1	621.0	619.8	619.2
10°	620.2	613.9	617.3	616.1	615.5
12.5°	614.6	608.8	612.6	611.5	611.3
15°	605.1	600.0	605.1	605.1	604.5
17.5°	593.1	588.5	593.9	594.3	593.9
20°	584.8	579.7	586.5	585.9	586.5
22.5°	574.6	570.4	577.7	576.2	576.8
25°	558.7	554.7	562.7	561.0	561.0
27.5°	539.9	537.0	545.8	543.9	543.9
30°	527.3	524.5	533.7	531.4	531.4
32.5°	513.4	511.5	520.3	517.5	517.5
35°	491.4	490.2	498.9	495.4	495.4
37.5°	468.6	467.6	475.5	471.3	469.9
40°	451.9	451.4	458.3	453.7	453.7
42.5°	435.2	434.6	440.7	435.1	435.1
45°	409.6	408.4	412.5	407.2	406.1
47.5°	381.6	380.5	383.0	377.3	376.7
50°	362.6	361.4	362.6	357.3	356.8
52.5°	343.1	341.0	341.2	336.0	335.9
55°	313.3	309.3	309.2	304.6	304.6
57.5°	281.7	276.5	277.0	273.0	272.4
60°	259.9	254.2	254.7	251.2	250.6
62.5°	238.5	232.0	233.3	229.4	229.3
65°	203.0	198.5	199.0	197.2	197.2
67.5°	168.9	164.7	167.8	166.4	166.3
70°	143.9	141.0	145.0	145.0	144.5
72.5°	120.7	120.6	125.5	125.5	125.9
75°	87.6	91.6	96.9	97.5	97.5
77.5°	58.5	65.5	71.4	71.6	71.5
80°	41.8	49.7	55.1	56.3	55.7
82.5°	28.3	36.7	41.2	42.3	41.8
85°	12.8	19.6	23.2	23.8	23.2
87.5°	4.1	8.8	11.6	11.7	10.6
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1



TEST NUMBER: P563098

CATALOG NUMBER: SQ4-PC3-150U-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)