

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563482

Luminaire Tested: **SQ4-PP3-0U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563482
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-050D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1693.8 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563482
CATALOG NUMBER: SQ4-PP3-0U-050D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563482

CATALOG NUMBER: SQ4-PP3-0U-050D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6106	6106	6106
5°	6151	6113	6091
10°	6140	6097	6070
15°	6100	6066	6033
20°	6059	6025	5979
25°	5987	5946	5887
30°	5876	5846	5771
35°	5723	5683	5611
40°	5539	5504	5441
45°	5389	5351	5297
50°	5195	5161	5111
55°	4925	4861	4824
60°	4484	4357	4334
65°	3951	3786	3772
70°	3410	3269	3269
75°	2937	2895	2852
80°	2588	2619	2556
85°	2022	2212	2212



TEST NUMBER: P563482

CATALOG NUMBER: SQ4-PP3-0U-050D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	3.7
10°-20°	178.7	10.5
20°-30°	267.6	15.8
30°-40°	313.9	18.5
40°-50°	314.9	18.6
50°-60°	268.6	15.9
60°-70°	175.2	10.3
70°-80°	87.9	5.2
80°-90°	24.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.9	30.0
0°-40°	822.8	48.6
0°-60°	1406.3	83.0
0°-90°	1693.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1693.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	662	662	662	662	662	
5°	664	658	660	658	658	63
15°	639	632	635	633	632	180
25°	588	581	584	579	578	270
35°	508	503	505	499	498	317
45°	413	410	410	406	406	318
55°	306	305	302	300	300	272
65°	181	178	173	172	173	181
75°	82	82	81	81	80	89
85°	19	21	21	21	21	23
90°	0	0	0	0	0	



TEST NUMBER: P563482

CATALOG NUMBER: SQ4-PP3-OU-050D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	661.8	661.8	661.8	661.8	661.8
2.5°	665.9	660.5	661.8	660.8	658.1
5°	664.1	657.9	660.0	657.7	657.7
7.5°	659.6	652.8	654.9	652.6	652.5
10°	655.4	648.6	650.8	648.4	647.9
12.5°	649.4	642.6	645.2	642.4	642.3
15°	638.6	632.3	635.1	632.7	631.6
17.5°	626.4	619.6	622.9	619.7	619.2
20°	617.1	610.3	613.6	609.0	609.0
22.5°	606.0	599.2	603.0	596.9	596.9
25°	588.1	581.3	584.1	578.8	578.3
27.5°	566.9	560.2	563.1	557.1	557.0
30°	551.6	545.3	548.7	542.3	541.7
32.5°	534.9	529.1	531.5	525.1	524.5
35°	508.1	503.0	504.6	498.8	498.2
37.5°	479.9	474.7	476.5	471.5	471.3
40°	459.9	456.5	457.0	452.9	451.8
42.5°	441.4	437.5	438.0	433.9	433.7
45°	413.0	410.1	410.1	406.0	406.0
47.5°	382.8	380.6	380.0	376.6	376.5
50°	361.9	360.2	359.6	356.7	356.1
52.5°	340.1	339.3	337.3	334.9	334.8
55°	306.2	305.1	302.2	300.4	299.9
57.5°	269.5	267.2	263.9	261.4	261.8
60°	243.0	240.7	236.1	234.9	234.9
62.5°	217.5	214.8	210.1	208.5	209.4
65°	181.0	177.6	173.4	172.3	172.8
67.5°	147.8	144.7	140.2	140.2	139.8
70°	126.4	124.7	121.2	121.2	121.2
72.5°	107.4	106.6	104.1	104.0	103.6
75°	82.4	82.4	81.2	80.6	80.0
77.5°	61.7	61.9	61.4	60.8	59.7
80°	48.7	49.9	49.3	48.7	48.1
82.5°	36.7	37.8	37.7	36.7	36.5
85°	19.1	20.8	20.9	20.9	20.9
87.5°	5.1	6.9	7.4	7.4	7.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)