

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563794

Luminaire Tested: **SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563794
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7732.3 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563794
CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563794

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8985	8946
15°	8990	8941	8892
20°	8931	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8434	8376	8271
40°	8165	8113	8020
45°	7941	7886	7808
50°	7656	7607	7534
55°	7261	7164	7110
60°	6610	6420	6388
65°	5822	5580	5560
70°	5028	4821	4821
75°	4328	4267	4206
80°	3815	3863	3772
85°	2985	3260	3260



TEST NUMBER: P563794

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	1.2
10°-20°	263.4	3.4
20°-30°	394.5	5.1
30°-40°	462.7	6.0
40°-50°	464.1	6.0
50°-60°	395.9	5.1
60°-70°	258.2	3.3
70°-80°	129.6	1.7
80°-90°	37.6	0.5
90°-100°	377.3	4.9
100°-110°	1020.1	13.2
110°-120°	1072.5	13.9
120°-130°	871.2	11.3
130°-140°	683.3	8.8
140°-150°	524.5	6.8
150°-160°	377.2	4.9
160°-170°	230.4	3.0
170°-180°	77.7	1.0
0°-30°	750.0	9.7
0°-40°	1212.7	15.7
0°-60°	2072.8	26.8
0°-90°	2498.1	32.3
90°-120°	2469.9	31.9
90°-150°	4548.9	58.8
90°-180°	5234.0	67.7
0°-180°	7732.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	975	975	975	975	975	
5°	979	970	973	969	969	93
15°	941	932	936	933	931	266
25°	867	857	861	853	852	399
35°	749	741	744	735	734	468
45°	609	604	604	598	598	469
55°	451	450	445	443	442	401
65°	267	262	256	254	255	266
75°	121	121	120	119	118	132
85°	28	31	31	31	31	33
90°	2	5	11	12	11	5
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	

TEST NUMBER: P563794

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	975.4	975.4	975.4	975.4	975.4
2.5°	981.5	973.5	975.4	973.9	969.9
5°	978.8	969.6	972.8	969.4	969.4
7.5°	972.1	962.1	965.3	961.9	961.7
10°	966.0	955.9	959.1	955.7	954.9
12.5°	957.1	947.1	950.9	946.8	946.7
15°	941.2	932.0	936.1	932.6	930.9
17.5°	923.2	913.2	918.1	913.3	912.6
20°	909.6	899.5	904.4	897.6	897.6
22.5°	893.1	883.1	888.7	879.8	879.8
25°	866.8	856.8	860.8	853.1	852.3
27.5°	835.5	825.7	829.9	821.2	821.0
30°	813.0	803.8	808.7	799.3	798.4
32.5°	788.3	779.8	783.4	774.0	773.1
35°	748.8	741.3	743.7	735.1	734.3
37.5°	707.3	699.6	702.3	695.0	694.6
40°	677.9	672.9	673.6	667.6	665.9
42.5°	650.5	644.9	645.6	639.6	639.3
45°	608.6	604.5	604.4	598.4	598.4
47.5°	564.2	561.0	560.1	555.1	555.0
50°	533.4	530.9	530.0	525.7	524.9
52.5°	501.3	500.1	497.2	493.6	493.4
55°	451.4	449.7	445.4	442.8	442.0
57.5°	397.2	393.8	389.0	385.2	385.9
60°	358.2	354.8	347.9	346.2	346.2
62.5°	320.6	316.6	309.6	307.3	308.6
65°	266.7	261.7	255.6	253.9	254.7
67.5°	217.8	213.3	206.7	206.7	206.0
70°	186.4	183.8	178.7	178.7	178.7
72.5°	158.3	157.1	153.4	153.3	152.7
75°	121.4	121.4	119.7	118.8	118.0
77.5°	91.0	91.3	90.4	89.6	88.0
80°	71.8	73.5	72.7	71.8	71.0
82.5°	54.0	55.7	55.6	54.0	53.9
85°	28.2	30.7	30.8	30.8	30.8
87.5°	7.9	11.2	13.2	13.4	13.9
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1



TEST NUMBER: P563794

CATALOG NUMBER: SQ4-PP3-150U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)