

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563986

Luminaire Tested: **SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563986
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4213.4 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563986
CATALOG NUMBER: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563986

CATALOG NUMBER: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9159	9159	9159
5°	9241	9170	9123
10°	9212	9148	9100
15°	9172	9114	9065
20°	9125	9066	8999
25°	9061	9000	8896
30°	8964	8900	8772
35°	8831	8754	8629
40°	8629	8537	8383
45°	8278	8133	7966
50°	7658	7474	7327
55°	6685	6532	6396
60°	5634	5586	5475
65°	4873	4890	4853
70°	4475	4497	4497
75°	4299	4299	4328
80°	4043	4091	4043
85°	3260	3620	3620



TEST NUMBER: P563986

CATALOG NUMBER: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.9	2.2
10°-20°	268.6	6.4
20°-30°	405.1	9.6
30°-40°	482.7	11.5
40°-50°	475.9	11.3
50°-60°	363.7	8.6
60°-70°	225.1	5.3
70°-80°	127.8	3.0
80°-90°	39.9	0.9
90°-100°	127.2	3.0
100°-110°	345.7	8.2
110°-120°	355.4	8.4
120°-130°	284.2	6.7
130°-140°	223.3	5.3
140°-150°	171.2	4.1
150°-160°	123.1	2.9
160°-170°	75.3	1.8
170°-180°	25.4	0.6
0°-30°	767.6	18.2
0°-40°	1250.3	29.7
0°-60°	2089.9	49.6
0°-90°	2482.7	58.9
90°-120°	828.3	19.7
90°-150°	1507.0	35.8
90°-180°	1731.0	41.1
0°-180°	4213.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	998	987	990	987	985	95
15°	960	950	954	951	949	271
25°	890	879	884	875	874	410
35°	784	775	777	767	766	489
45°	634	626	623	612	610	486
55°	416	409	406	399	398	372
65°	223	222	224	222	222	226
75°	121	121	121	121	121	127
85°	31	32	34	34	34	36
90°	1	3	6	8	8	3
95°	19	70	222	96	65	20
105°	61	96	380	579	545	65
115°	109	132	304	605	690	108
125°	150	171	275	464	547	134
135°	181	201	268	378	426	140
145°	209	224	264	321	345	131
155°	236	244	262	288	297	109
165°	256	259	263	274	275	72
175°	265	266	264	268	267	25
180°	265	265	265	265	265	



TEST NUMBER: P563986

CATALOG NUMBER: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	992.7	992.7	992.7	992.7	992.7
2.5°	998.9	990.2	992.7	990.5	985.9
5°	997.8	987.0	990.1	986.7	985.0
7.5°	990.1	979.4	982.6	979.2	978.2
10°	983.3	973.3	976.5	973.0	971.3
12.5°	975.8	965.1	968.9	964.8	963.1
15°	960.2	950.2	954.2	950.8	949.1
17.5°	943.1	932.4	936.4	932.5	930.3
20°	929.4	919.4	923.4	917.4	916.6
22.5°	914.4	904.4	908.4	900.4	900.2
25°	890.1	879.2	884.1	874.7	873.9
27.5°	861.2	851.2	855.2	845.6	844.6
30°	841.4	831.3	835.4	825.1	823.4
32.5°	818.8	809.4	812.8	802.5	801.5
35°	784.1	774.9	777.2	767.0	766.1
37.5°	744.6	736.2	737.6	726.3	725.4
40°	716.5	708.2	708.8	696.8	696.0
42.5°	685.7	677.4	676.7	664.7	663.9
45°	634.4	626.1	623.3	612.2	610.5
47.5°	576.0	567.6	562.4	553.4	552.2
50°	533.5	525.2	520.7	513.0	510.5
52.5°	487.7	479.4	475.6	468.5	466.0
55°	415.6	408.9	406.1	399.3	397.6
57.5°	347.0	342.5	341.7	335.0	334.3
60°	305.3	302.7	302.7	296.7	296.7
62.5°	269.7	267.8	269.2	265.2	264.6
65°	223.2	221.5	224.0	222.3	222.3
67.5°	186.4	186.4	187.9	187.3	187.3
70°	165.9	165.9	166.7	166.7	166.7
72.5°	147.4	146.7	148.9	148.9	148.3
75°	120.6	120.6	120.6	121.4	121.4
77.5°	93.9	94.1	94.7	94.6	93.9
80°	76.1	76.9	77.0	76.1	76.1
82.5°	58.3	59.1	59.2	59.0	58.3
85°	30.8	32.5	34.2	34.2	34.2
87.5°	9.1	12.2	14.9	15.2	14.5
90°	0.9	3.4	6.0	7.7	7.7
92.5°	7.7	34.8	60.5	26.0	22.0
95°	18.8	69.6	221.6	96.4	64.8
97.5°	31.0	76.9	339.7	264.3	185.6
100°	39.2	81.7	375.9	381.0	307.7
102.5°	47.4	86.6	385.4	471.2	406.6
105°	61.4	95.5	380.1	578.8	544.6
107.5°	75.9	106.0	358.2	634.4	643.9
110°	86.1	113.6	341.8	645.3	686.1

TEST NUMBER: P563986

CATALOG NUMBER: SQ4-PR1-050U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.0	121.1	325.4	636.2	697.7
115°	109.1	132.4	304.3	605.4	689.5
117.5°	122.4	144.7	290.8	561.6	656.5
120°	131.3	152.9	284.7	532.3	626.5
122.5°	138.8	160.4	280.6	502.9	593.7
125°	150.0	170.8	275.3	463.9	547.2
127.5°	160.1	180.7	272.4	434.3	505.8
130°	166.2	186.2	271.0	415.7	479.9
132.5°	172.3	192.3	269.7	399.8	456.7
135°	180.7	200.7	267.6	377.8	426.2
137.5°	189.7	207.9	266.6	358.4	399.1
140°	195.2	212.7	265.9	346.0	382.7
142.5°	200.6	216.8	265.2	336.3	367.0
145°	208.8	223.8	264.2	321.0	345.2
147.5°	218.0	230.9	263.4	309.0	328.0
150°	224.2	235.0	263.4	302.1	317.1
152.5°	228.9	238.4	262.7	295.9	308.2
155°	236.1	244.4	262.5	288.3	296.6
157.5°	243.1	249.6	262.5	283.1	289.5
160°	247.2	253.0	262.5	279.7	284.7
162.5°	251.3	255.8	263.2	276.9	280.6
165°	255.7	259.0	263.4	274.5	275.3
167.5°	260.3	262.0	264.2	271.6	272.2
170°	261.7	263.3	264.2	270.2	270.2
172.5°	263.0	264.0	264.2	268.8	268.8
175°	265.1	265.9	264.2	267.6	266.8
177.5°	265.8	265.8	263.7	266.4	265.1
180°	265.1	265.1	265.1	265.1	265.1

(END OF REPORT)