

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938372

Luminaire Tested: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938372
REPORT IS A COMBINATION OF REPORTS P933646 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14371.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 127.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938372
CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	36	29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30	32	31	30	23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25	27	26	25	19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	24	22	21	16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17	21	19	17	13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	19	17	15	11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	17	15	13	10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	15	13	11	8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	14	12	10	7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9	13	10	9	6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8	12	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2459	2459	2459
5°	2402	2842	3305
10°	2179	4143	5480
15°	1852	5412	6616
20°	1507	6272	6743
25°	1258	6563	6606
30°	1061	6605	6593
35°	938	6495	6764
40°	817	6353	6940
45°	740	6248	6967
50°	678	6154	6852
55°	650	6017	6548
60°	666	5752	6069
65°	693	5351	5409
70°	737	4666	4570
75°	817	3805	3567
80°	893	2639	2403
85°	792	1399	1230

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 6967 cd/sqm



TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	0.5
10°-20°	303.8	2.1
20°-30°	531.4	3.7
30°-40°	684.1	4.8
40°-50°	764.2	5.3
50°-60°	731.9	5.1
60°-70°	580.0	4.0
70°-80°	341.0	2.4
80°-90°	100.8	0.7
90°-100°	771.9	5.4
100°-110°	2029.4	14.1
110°-120°	2104.3	14.6
120°-130°	1687.9	11.7
130°-140°	1324.4	9.2
140°-150°	1016.5	7.1
150°-160°	732.1	5.1
160°-170°	447.9	3.1
170°-180°	151.3	1.1
0°-30°	903.8	6.3
0°-40°	1588.0	11.0
0°-60°	3084.0	21.5
0°-90°	4105.8	28.6
90°-120°	4905.6	34.1
90°-150°	8934.4	62.2
90°-180°	10266.0	71.4
0°-180°	14371.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	516	554	624	706	731	48
15°	387	714	1203	1459	1505	108
25°	247	809	1433	1496	1498	114
35°	167	774	1350	1426	1483	104
45°	114	617	1193	1367	1428	88
55°	82	392	1012	1176	1208	75
65°	65	208	752	845	857	64
75°	48	128	412	453	455	50
85°	17	39	102	112	114	18
90°	11	30	81	40	40	10
95°	102	400	1330	686	467	113
105°	366	554	2244	3406	3178	388
115°	649	789	1797	3585	4092	641
125°	903	1013	1635	2762	3259	802
135°	1077	1185	1584	2230	2528	833
145°	1249	1328	1563	1902	2051	782
155°	1411	1451	1563	1716	1766	648
165°	1523	1543	1563	1625	1645	430
175°	1584	1584	1574	1594	1594	150
180°	1584	1584	1584	1584	1584	



TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9	529.9
2.5°	529.9	529.9	533.4	535.1	538.5	540.2	543.6	547.0	557.2	558.9	562.3
5°	516.3	523.1	545.3	553.8	577.7	610.0	623.7	645.8	691.8	705.5	714.0
7.5°	495.9	511.2	565.7	579.4	639.0	724.2	760.0	807.7	881.0	916.8	945.7
10°	463.5	495.9	593.0	625.4	722.5	852.0	918.5	985.0	1095.8	1145.2	1163.9
12.5°	427.7	480.5	622.0	666.3	806.0	995.2	1075.3	1148.6	1274.7	1341.1	1351.4
15°	386.8	458.4	649.2	714.0	894.6	1114.5	1203.1	1293.4	1411.0	1458.7	1470.6
17.5°	351.0	441.3	674.8	742.9	962.8	1221.9	1312.2	1387.1	1482.6	1514.9	1523.5
20°	306.7	414.1	691.8	780.4	1034.4	1300.2	1387.1	1445.1	1509.8	1530.3	1533.7
22.5°	274.3	385.1	702.0	794.1	1082.1	1347.9	1421.2	1467.2	1511.5	1518.3	1520.1
25°	247.1	352.7	700.3	809.4	1123.0	1376.9	1433.1	1467.2	1492.8	1496.2	1496.2
27.5°	221.5	316.9	693.5	812.8	1153.7	1383.7	1428.0	1451.9	1463.8	1470.6	1470.6
30°	199.4	282.9	676.5	806.0	1167.3	1376.9	1412.7	1424.6	1436.6	1446.8	1451.9
32.5°	182.3	250.5	650.9	792.4	1169.0	1359.9	1385.4	1392.3	1409.3	1433.1	1441.7
35°	167.0	218.1	622.0	773.6	1158.8	1332.6	1349.7	1356.5	1390.5	1426.3	1438.3
37.5°	151.7	194.3	584.5	741.2	1143.5	1300.2	1312.2	1324.1	1376.9	1419.5	1433.1
40°	136.3	173.8	540.2	705.5	1119.6	1261.0	1271.3	1290.0	1359.9	1409.3	1422.9
42.5°	124.4	156.8	492.5	668.0	1088.9	1216.7	1232.1	1259.3	1339.4	1392.3	1407.6
45°	114.2	139.7	441.3	616.8	1049.7	1170.7	1192.9	1230.4	1315.6	1366.7	1380.3
47.5°	103.9	127.8	388.5	564.0	1007.1	1124.7	1153.7	1196.3	1283.2	1332.6	1344.5
50°	95.4	115.9	335.7	507.8	961.1	1075.3	1109.4	1153.7	1242.3	1288.3	1303.6
52.5°	88.6	105.6	286.3	451.6	908.2	1024.2	1063.4	1109.4	1192.9	1237.2	1247.4
55°	81.8	97.1	243.7	391.9	853.7	969.7	1012.3	1056.6	1138.4	1175.8	1182.7
57.5°	78.4	90.3	207.9	335.7	795.8	908.2	955.9	996.9	1073.6	1102.6	1109.4
60°	73.3	85.2	180.6	288.0	732.7	850.3	891.2	932.1	996.9	1020.8	1025.9
62.5°	68.2	81.8	160.2	242.0	668.0	782.1	823.0	860.5	915.0	932.1	938.9
65°	64.8	78.4	144.8	207.9	601.5	710.6	751.5	783.8	828.1	845.2	848.6
67.5°	61.3	75.0	132.9	178.9	535.1	639.0	669.7	700.3	734.4	751.5	753.2
70°	56.2	71.6	122.7	158.5	466.9	557.2	582.8	615.1	642.4	650.9	656.0
72.5°	52.8	66.5	115.9	143.1	397.0	478.8	502.7	521.4	545.3	553.8	553.8
75°	47.7	59.6	109.1	127.8	325.5	391.9	412.4	431.1	449.9	453.3	448.2
77.5°	42.6	52.8	93.7	107.4	253.9	310.1	327.2	337.4	352.7	356.1	357.8
80°	35.8	46.0	73.3	83.5	184.0	228.3	240.3	248.8	262.4	262.4	265.8
82.5°	27.3	35.8	52.8	59.6	124.4	156.8	167.0	172.1	180.6	180.6	180.6
85°	17.0	22.2	34.1	39.2	75.0	95.4	102.2	103.9	110.8	112.5	112.5
87.5°	8.5	11.9	22.2	23.9	39.2	49.4	49.4	52.8	52.8	51.1	49.4
90°	10.6	19.2	27.6	29.7	46.8	69.4	80.8	71.8	53.8	40.4	40.4
92.5°	42.5	114.8	187.1	205.2	288.4	399.4	454.9	398.7	286.3	201.9	193.9
95°	102.1	234.3	366.5	399.6	709.5	1122.9	1329.5	1186.4	900.2	685.5	661.2
97.5°	176.4	293.1	409.8	439.0	955.9	1645.0	1989.6	1899.1	1718.2	1582.5	1536.2
100°	233.8	339.6	445.4	471.9	1045.5	1810.2	2192.5	2199.2	2212.4	2222.3	2167.1
102.5°	282.7	381.4	480.1	504.8	1086.6	1862.1	2250.0	2365.2	2595.7	2768.6	2721.4
105°	365.6	449.2	532.8	553.7	1117.0	1868.0	2243.6	2502.0	3018.7	3406.3	3380.9
107.5°	450.6	528.6	606.5	626.0	1122.7	1784.9	2116.0	2476.4	3197.3	3737.9	3744.0
110°	508.0	578.4	648.8	666.3	1114.2	1711.2	2009.8	2412.7	3218.5	3822.9	3849.3



TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	564.4	631.4	698.5	715.3	1114.5	1646.8	1913.0	2325.4	3150.1	3768.7	3809.3
115°	649.4	711.2	773.1	788.6	1124.8	1573.0	1797.2	2194.4	2988.9	3584.8	3641.1
117.5°	733.3	789.5	845.8	859.8	1145.7	1526.9	1717.5	2076.0	2793.0	3330.8	3393.3
120°	782.2	835.1	888.0	901.2	1162.7	1511.3	1685.6	2013.2	2668.4	3159.7	3220.4
122.5°	830.0	883.4	936.8	950.2	1187.2	1503.2	1661.1	1956.1	2546.1	2988.6	3048.5
125°	903.4	952.0	1000.7	1012.9	1220.1	1496.4	1634.6	1885.1	2386.3	2762.2	2817.3
127.5°	962.9	1012.0	1061.2	1073.4	1253.0	1492.5	1612.2	1827.4	2257.7	2580.5	2627.0
130°	994.8	1047.7	1100.6	1113.8	1277.1	1494.8	1603.7	1795.2	2178.4	2465.7	2508.7
132.5°	1027.8	1080.7	1133.6	1146.8	1296.7	1496.5	1596.3	1767.7	2110.7	2367.9	2406.4
135°	1076.6	1124.8	1173.0	1185.0	1317.9	1495.0	1583.5	1727.2	2014.4	2229.8	2262.9
137.5°	1126.6	1174.3	1221.9	1233.9	1349.7	1504.2	1581.5	1702.9	1945.6	2127.7	2154.9
140°	1168.0	1212.0	1255.8	1266.8	1369.2	1505.7	1574.0	1678.9	1888.6	2045.9	2071.3
142.5°	1199.9	1240.5	1281.2	1291.3	1385.5	1511.2	1574.0	1666.1	1850.3	1988.5	2010.3
145°	1248.8	1284.2	1319.7	1328.5	1406.8	1511.2	1563.3	1638.7	1789.4	1902.4	1919.0
147.5°	1297.7	1332.2	1366.7	1375.3	1438.0	1521.6	1563.3	1622.6	1741.1	1830.1	1843.8
150°	1329.5	1360.7	1391.9	1399.7	1454.2	1527.0	1563.3	1613.4	1713.5	1788.7	1799.8
152.5°	1362.5	1386.1	1409.8	1415.7	1464.9	1530.5	1563.3	1606.1	1691.6	1755.7	1764.1
155°	1411.4	1428.9	1446.4	1450.7	1488.3	1538.3	1563.3	1597.3	1665.4	1716.4	1722.0
157.5°	1447.5	1464.6	1481.5	1485.8	1511.6	1546.1	1563.3	1589.8	1642.7	1682.4	1686.4
160°	1472.0	1485.2	1498.4	1501.7	1522.3	1549.6	1563.3	1586.0	1631.4	1665.4	1667.6
162.5°	1496.5	1506.3	1516.3	1518.8	1533.6	1553.5	1563.3	1582.5	1620.8	1649.5	1651.6
165°	1523.0	1531.9	1540.9	1543.1	1549.9	1558.8	1563.3	1577.1	1604.5	1625.0	1627.2
167.5°	1547.4	1551.7	1555.9	1557.0	1562.7	1570.2	1574.0	1582.9	1600.9	1614.4	1615.3
170°	1563.3	1567.6	1571.9	1573.0	1573.3	1573.7	1574.0	1582.9	1600.9	1614.4	1614.4
172.5°	1571.9	1572.8	1573.7	1574.0	1574.0	1574.0	1574.0	1581.1	1595.2	1605.8	1605.0
175°	1583.5	1583.5	1583.5	1583.5	1580.4	1576.1	1574.0	1578.5	1587.4	1594.2	1594.2
177.5°	1583.5	1583.5	1583.5	1583.5	1581.1	1577.7	1576.1	1579.7	1586.8	1592.0	1591.1
180°	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5	1583.5



TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	529.9	529.9
2.5°	565.7	562.3
5°	727.6	731.0
7.5°	979.9	978.2
10°	1218.4	1233.8
12.5°	1392.3	1395.7
15°	1497.9	1504.7
17.5°	1538.8	1540.5
20°	1540.5	1537.1
22.5°	1521.8	1518.3
25°	1499.6	1497.9
27.5°	1479.2	1480.9
30°	1470.6	1475.7
32.5°	1470.6	1479.2
35°	1474.0	1482.6
37.5°	1472.3	1482.6
40°	1465.5	1477.5
42.5°	1446.8	1455.3
45°	1417.8	1428.0
47.5°	1380.3	1387.1
50°	1332.6	1339.4
52.5°	1273.0	1274.7
55°	1201.4	1208.2
57.5°	1124.7	1126.4
60°	1039.5	1044.6
62.5°	949.1	949.1
65°	853.7	857.1
67.5°	754.9	763.4
70°	654.3	656.0
72.5°	555.5	555.5
75°	453.3	455.0
77.5°	356.1	356.1
80°	264.1	265.8
82.5°	182.3	185.7
85°	114.2	114.2
87.5°	52.8	47.7
90°	40.4	40.4
92.5°	161.8	129.7
95°	563.9	466.6
97.5°	1351.0	1165.9
100°	1946.6	1726.0
102.5°	2532.4	2343.5
105°	3279.3	3177.8
107.5°	3768.6	3793.1
110°	3955.2	4061.0



TEST NUMBER: P938372

CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3971.8	4134.2
115°	3866.5	4091.7
117.5°	3643.2	3893.0
120°	3463.2	3705.9
122.5°	3288.0	3527.5
125°	3038.0	3258.6
127.5°	2813.1	2999.2
130°	2680.6	2852.6
132.5°	2560.3	2714.4
135°	2395.7	2528.4
137.5°	2263.5	2372.1
140°	2172.9	2274.4
142.5°	2097.7	2185.1
145°	1985.1	2051.2
147.5°	1898.6	1953.4
150°	1844.2	1888.6
152.5°	1797.6	1831.2
155°	1744.2	1766.4
157.5°	1701.9	1717.5
160°	1676.7	1685.6
162.5°	1660.0	1668.6
165°	1636.3	1645.2
167.5°	1619.1	1622.9
170°	1614.4	1614.4
172.5°	1601.8	1598.4
175°	1594.2	1594.2
177.5°	1587.3	1583.5
180°	1583.5	1583.5



TEST NUMBER: P938372
 CATALOG NUMBER: SQ4-FB-150U-075D-935-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.74	2.46	2.86	3.57	5.12	14.92	15.64	16.04	16.75	18.30
	3H	2.44	3.08	3.56	4.20	5.76	16.75	17.39	17.87	18.51	20.07
	4H	2.73	3.34	3.86	4.46	6.03	17.39	18.00	18.52	19.12	20.69
	6H	2.97	3.53	4.11	4.66	6.24	17.81	18.37	18.95	19.50	21.08
	8H	3.03	3.57	4.18	4.71	6.28	17.93	18.46	19.07	19.60	21.17
	12H	3.05	3.55	4.20	4.69	6.28	17.99	18.50	19.14	19.63	21.23
4H	2H	8.94	9.55	10.08	10.67	12.24	15.18	15.79	16.32	16.91	18.48
	3H	10.49	11.00	11.64	12.15	13.73	17.21	17.72	18.36	18.87	20.45
	4H	10.58	11.05	11.73	12.19	13.79	17.97	18.44	19.12	19.58	21.17
	6H	10.58	10.99	11.74	12.15	13.74	18.50	18.90	19.66	20.06	21.65
	8H	10.56	10.93	11.71	12.08	13.69	18.66	19.03	19.81	20.19	21.79
	12H	10.50	10.85	11.68	12.01	13.62	18.74	19.08	19.92	20.25	21.86
8H	4H	12.01	12.39	13.17	13.54	15.15	18.02	18.39	19.17	19.54	21.15
	6H	12.25	12.56	13.42	13.75	15.36	18.64	18.95	19.82	20.14	21.75
	8H	12.26	12.54	13.45	13.71	15.33	18.86	19.13	20.04	20.30	21.92
	12H	12.23	12.46	13.41	13.63	15.29	18.99	19.23	20.18	20.40	22.06
12H	4H	12.15	12.49	13.32	13.65	15.27	17.96	18.30	19.13	19.47	21.08
	6H	12.51	12.78	13.69	13.95	15.57	18.62	18.89	19.80	20.06	21.69
	8H	12.57	12.81	13.75	13.98	15.63	18.84	19.08	20.03	20.25	21.91