

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564082

Luminaire Tested: **SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5083.9 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 42.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564082
CATALOG NUMBER: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564082

CATALOG NUMBER: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	86	90	86	83	80	73	71	68	60	59	57	49	48	47				42	
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40				35	
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34				30	
4	75	64	56	50	69	59	53	47	51	45	41	42	39	36	35	32	30				26	
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26				23	
6	63	51	43	38	58	48	41	36	41	35	31	35	30	27	29	25	23				20	
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21				18	
8	54	42	35	29	50	39	32	28	34	28	25	29	25	21	24	21	18				16	
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17				14	
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9159	9159	9159
5°	9241	9170	9123
10°	9212	9148	9100
15°	9172	9114	9065
20°	9125	9066	8999
25°	9061	9000	8896
30°	8964	8900	8772
35°	8831	8754	8629
40°	8629	8537	8383
45°	8278	8133	7966
50°	7658	7474	7327
55°	6685	6532	6396
60°	5634	5586	5475
65°	4873	4890	4853
70°	4475	4497	4497
75°	4299	4299	4328
80°	4043	4091	4043
85°	3260	3620	3620



TEST NUMBER: P564082

CATALOG NUMBER: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.9	1.8
10°-20°	268.6	5.3
20°-30°	405.1	8.0
30°-40°	482.7	9.5
40°-50°	475.9	9.4
50°-60°	363.7	7.2
60°-70°	225.1	4.4
70°-80°	127.8	2.5
80°-90°	39.9	0.8
90°-100°	188.3	3.7
100°-110°	518.1	10.2
110°-120°	534.8	10.5
120°-130°	428.5	8.4
130°-140°	336.5	6.6
140°-150°	257.9	5.1
150°-160°	185.4	3.6
160°-170°	113.4	2.2
170°-180°	38.2	0.8
0°-30°	767.6	15.1
0°-40°	1250.3	24.6
0°-60°	2089.9	41.1
0°-90°	2482.7	48.8
90°-120°	1241.3	24.4
90°-150°	2264.2	44.5
90°-180°	2601.0	51.2
0°-180°	5083.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	998	987	990	987	985	95
15°	960	950	954	951	949	271
25°	890	879	884	875	874	410
35°	784	775	777	767	766	489
45°	634	626	623	612	610	486
55°	416	409	406	399	398	372
65°	223	222	224	222	222	226
75°	121	121	121	121	121	127
85°	31	32	34	34	34	36
90°	1	3	6	8	8	3
95°	28	103	333	142	91	30
105°	93	142	571	870	811	98
115°	164	200	458	912	1035	162
125°	226	258	415	703	823	202
135°	273	303	404	568	643	210
145°	315	337	398	484	522	198
155°	357	368	395	435	448	164
165°	386	391	397	413	415	109
175°	399	400	398	403	402	38
180°	399	399	399	399	399	



TEST NUMBER: P564082

CATALOG NUMBER: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	992.7	992.7	992.7	992.7	992.7
2.5°	998.9	990.2	992.7	990.5	985.9
5°	997.8	987.0	990.1	986.7	985.0
7.5°	990.1	979.4	982.6	979.2	978.2
10°	983.3	973.3	976.5	973.0	971.3
12.5°	975.8	965.1	968.9	964.8	963.1
15°	960.2	950.2	954.2	950.8	949.1
17.5°	943.1	932.4	936.4	932.5	930.3
20°	929.4	919.4	923.4	917.4	916.6
22.5°	914.4	904.4	908.4	900.4	900.2
25°	890.1	879.2	884.1	874.7	873.9
27.5°	861.2	851.2	855.2	845.6	844.6
30°	841.4	831.3	835.4	825.1	823.4
32.5°	818.8	809.4	812.8	802.5	801.5
35°	784.1	774.9	777.2	767.0	766.1
37.5°	744.6	736.2	737.6	726.3	725.4
40°	716.5	708.2	708.8	696.8	696.0
42.5°	685.7	677.4	676.7	664.7	663.9
45°	634.4	626.1	623.3	612.2	610.5
47.5°	576.0	567.6	562.4	553.4	552.2
50°	533.5	525.2	520.7	513.0	510.5
52.5°	487.7	479.4	475.6	468.5	466.0
55°	415.6	408.9	406.1	399.3	397.6
57.5°	347.0	342.5	341.7	335.0	334.3
60°	305.3	302.7	302.7	296.7	296.7
62.5°	269.7	267.8	269.2	265.2	264.6
65°	223.2	221.5	224.0	222.3	222.3
67.5°	186.4	186.4	187.9	187.3	187.3
70°	165.9	165.9	166.7	166.7	166.7
72.5°	147.4	146.7	148.9	148.9	148.3
75°	120.6	120.6	120.6	121.4	121.4
77.5°	93.9	94.1	94.7	94.6	93.9
80°	76.1	76.9	77.0	76.1	76.1
82.5°	58.3	59.1	59.2	59.0	58.3
85°	30.8	32.5	34.2	34.2	34.2
87.5°	9.1	12.2	14.9	15.2	14.5
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	50.1	86.8	33.3	27.4
95°	28.0	102.8	333.0	142.4	90.9
97.5°	45.7	114.0	508.2	391.6	276.3
100°	58.6	120.9	563.3	568.5	463.9
102.5°	70.9	129.2	577.5	705.3	609.3
105°	92.6	142.4	570.9	869.5	811.3
107.5°	113.3	158.9	538.5	949.9	967.2
110°	128.3	169.8	514.0	969.9	1029.7



TEST NUMBER: P564082

CATALOG NUMBER: SQ4-PR1-075U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.9	182.1	489.5	957.0	1048.0
115°	164.0	199.7	457.9	911.8	1034.8
117.5°	185.0	217.9	437.9	848.5	987.5
120°	198.0	229.5	429.0	801.0	944.7
122.5°	209.5	241.1	422.9	759.4	895.8
125°	226.0	257.6	415.4	702.8	823.2
127.5°	241.6	271.7	410.5	655.6	761.2
130°	249.8	280.5	407.8	627.5	723.8
132.5°	259.3	290.0	405.8	602.8	689.9
135°	272.7	302.6	403.5	568.4	643.1
137.5°	285.3	313.0	401.7	540.5	602.2
140°	294.8	320.6	401.0	522.1	577.7
142.5°	303.0	326.7	399.6	505.6	553.2
145°	315.2	336.8	397.6	484.3	521.6
147.5°	328.3	346.9	396.6	465.4	495.3
150°	336.4	353.0	395.9	455.1	478.3
152.5°	343.9	359.2	395.2	446.1	465.4
155°	356.8	368.5	395.1	435.3	447.7
157.5°	366.2	375.6	395.1	426.3	435.0
160°	373.0	380.4	395.1	421.5	428.2
162.5°	378.4	384.5	395.7	417.4	422.7
165°	385.7	390.7	396.8	412.9	415.4
167.5°	390.8	394.6	397.6	409.2	409.8
170°	394.2	396.7	397.6	407.8	407.8
172.5°	396.9	398.1	397.6	405.7	405.1
175°	399.3	400.1	397.6	402.7	401.8
177.5°	400.0	400.0	397.3	401.3	400.0
180°	399.3	399.3	399.3	399.3	399.3

(END OF REPORT)