

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562644

Luminaire Tested: **SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562644
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8504.1 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 78.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562644
CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562644

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8487	8487
25°	8382	8443	8417
30°	8280	8381	8344
35°	8157	8282	8224
40°	8022	8136	8053
45°	7876	7932	7810
50°	7670	7670	7548
55°	7427	7331	7221
60°	7068	6926	6816
65°	6533	6403	6346
70°	5720	5766	5743
75°	4602	5090	5121
80°	3270	4317	4362
85°	1990	3620	3620



TEST NUMBER: P562644

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.8	2.1
10°-20°	501.6	5.9
20°-30°	759.6	8.9
30°-40°	910.7	10.7
40°-50°	928.6	10.9
50°-60°	810.6	9.5
60°-70°	580.3	6.8
70°-80°	298.9	3.5
80°-90°	77.6	0.9
90°-100°	254.5	3.0
100°-110°	691.4	8.1
110°-120°	710.8	8.4
120°-130°	568.3	6.7
130°-140°	446.6	5.3
140°-150°	342.4	4.0
150°-160°	246.2	2.9
160°-170°	150.6	1.8
170°-180°	50.7	0.6
0°-30°	1436.0	16.9
0°-40°	2346.6	27.6
0°-60°	4085.8	48.0
0°-90°	5042.6	59.3
90°-120°	1656.7	19.5
90°-150°	3014.0	35.4
90°-180°	3462.0	40.7
0°-180°	8504.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1847	1847	1847	1847	1847	
5°	1854	1835	1842	1837	1835	176
15°	1784	1769	1784	1784	1782	503
25°	1647	1635	1659	1654	1654	758
35°	1448	1445	1471	1460	1460	906
45°	1207	1204	1216	1200	1197	929
55°	923	912	912	898	898	823
65°	598	585	587	581	581	592
75°	258	270	286	287	287	279
85°	38	58	68	70	68	51
90°	2	7	12	15	15	4
95°	38	139	443	193	130	40
105°	123	191	760	1158	1089	130
115°	218	265	609	1211	1379	215
125°	300	342	551	928	1094	267
135°	361	401	535	756	852	279
145°	418	448	528	642	690	262
155°	472	489	525	577	593	218
165°	511	518	527	549	551	144
175°	530	532	528	535	534	50
180°	530	530	530	530	530	



TEST NUMBER: P562644

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1846.9	1846.9	1846.9	1846.9	1846.9
2.5°	1857.8	1841.8	1846.9	1842.6	1836.0
5°	1853.7	1835.3	1841.8	1836.6	1834.9
7.5°	1840.4	1822.0	1830.5	1827.0	1825.3
10°	1828.1	1809.7	1819.5	1816.1	1814.4
12.5°	1811.7	1794.6	1805.9	1802.4	1802.1
15°	1783.6	1768.6	1783.6	1783.6	1781.9
17.5°	1748.4	1734.7	1750.8	1751.8	1750.8
20°	1723.8	1708.7	1728.9	1727.2	1728.9
22.5°	1693.7	1681.3	1702.9	1698.5	1700.2
25°	1646.8	1635.1	1658.8	1653.7	1653.7
27.5°	1591.4	1583.0	1608.9	1603.4	1603.4
30°	1554.5	1546.1	1573.3	1566.4	1566.4
32.5°	1513.4	1507.7	1533.6	1525.4	1525.4
35°	1448.4	1445.1	1470.7	1460.4	1460.4
37.5°	1381.4	1378.4	1401.6	1389.2	1385.2
40°	1332.2	1330.5	1351.0	1337.3	1337.3
42.5°	1282.9	1281.2	1299.0	1282.6	1282.6
45°	1207.3	1204.0	1215.9	1200.4	1197.1
47.5°	1124.9	1121.6	1129.0	1112.2	1110.5
50°	1068.8	1065.5	1068.8	1053.4	1051.7
52.5°	1011.3	1005.3	1005.9	990.5	990.1
55°	923.4	911.7	911.5	897.8	897.8
57.5°	830.4	815.0	816.4	804.7	803.1
60°	766.1	749.4	750.7	740.4	738.8
62.5°	703.2	683.8	687.8	676.2	675.8
65°	598.5	585.2	586.6	581.4	581.4
67.5°	498.0	485.6	494.6	490.4	490.1
70°	424.1	415.7	427.5	427.5	425.8
72.5°	355.7	355.4	370.1	370.1	371.1
75°	258.2	269.9	285.6	287.3	287.3
77.5°	172.4	193.1	210.3	211.0	210.7
80°	123.1	146.5	162.5	165.8	164.2
82.5°	83.5	108.2	121.4	124.8	123.1
85°	37.6	57.7	68.4	70.1	68.4
87.5°	11.3	24.3	29.7	30.4	27.7
90°	1.7	6.7	11.9	15.3	15.3
92.5°	15.3	69.7	121.0	52.0	44.0
95°	37.5	139.2	443.2	192.9	129.6
97.5°	62.1	153.7	679.5	528.6	371.3
100°	78.4	163.4	751.8	762.1	615.4
102.5°	94.8	173.1	770.9	942.5	813.1
105°	122.7	191.1	760.3	1157.6	1089.3
107.5°	151.7	212.1	716.3	1268.7	1287.7
110°	172.2	227.2	683.6	1290.6	1372.3



TEST NUMBER: P562644

CATALOG NUMBER: SQ4-PC3-050U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.9	242.2	650.8	1272.4	1395.4
115°	218.2	264.9	608.6	1210.7	1379.1
117.5°	244.8	289.5	581.6	1123.3	1312.9
120°	262.5	305.9	569.4	1064.6	1252.9
122.5°	277.5	320.9	561.2	1005.8	1187.5
125°	300.0	341.7	550.6	927.7	1094.4
127.5°	320.1	361.5	544.8	868.5	1011.6
130°	332.4	372.4	542.1	831.4	959.7
132.5°	344.7	384.7	539.4	799.7	913.4
135°	361.4	401.4	535.3	755.7	852.3
137.5°	379.5	415.8	533.2	716.8	798.1
140°	390.4	425.4	531.9	692.1	765.4
142.5°	401.3	433.6	530.5	672.7	734.0
145°	417.6	447.6	528.4	642.1	690.4
147.5°	436.1	461.7	526.7	618.0	656.0
150°	448.3	470.0	526.7	604.1	634.1
152.5°	457.9	476.9	525.4	591.7	616.4
155°	472.2	488.9	525.0	576.6	593.2
157.5°	486.2	499.2	525.0	566.2	578.9
160°	494.4	506.0	525.0	559.4	569.4
162.5°	502.5	511.5	526.4	553.8	561.2
165°	511.4	518.1	526.7	548.9	550.6
167.5°	520.6	523.9	528.4	543.1	544.5
170°	523.3	526.7	528.4	540.4	540.4
172.5°	526.1	528.1	528.4	537.7	537.7
175°	530.2	531.8	528.4	535.2	533.6
177.5°	531.5	531.5	527.4	532.8	530.2
180°	530.2	530.2	530.2	530.2	530.2

(END OF REPORT)