

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562860

Luminaire Tested: **SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562860  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6697.4 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562860  
CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562860

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11321	11321	11321
5°	11406	11332	11290
10°	11378	11325	11293
15°	11318	11318	11307
20°	11244	11277	11277
25°	11137	11218	11184
30°	11002	11135	11087
35°	10838	11005	10928
40°	10659	10809	10700
45°	10466	10539	10376
50°	10192	10192	10029
55°	9868	9741	9594
60°	9391	9203	9056
65°	8681	8508	8432
70°	7600	7661	7631
75°	6115	6764	6803
80°	4346	5736	5794
85°	2646	4811	4811



TEST NUMBER: P562860

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	232.2	3.5
10°-20°	666.5	10.0
20°-30°	1009.3	15.1
30°-40°	1210.0	18.1
40°-50°	1233.8	18.4
50°-60°	1077.0	16.1
60°-70°	771.0	11.5
70°-80°	397.1	5.9
80°-90°	100.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1908.0	28.5
0°-40°	3118.0	46.6
0°-60°	5428.7	81.1
0°-90°	6697.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6697.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2454	2454	2454	2454	2454	
5°	2463	2439	2447	2440	2438	234
15°	2370	2350	2370	2370	2368	668
25°	2188	2173	2204	2197	2197	1007
35°	1925	1920	1954	1940	1940	1204
45°	1604	1600	1616	1595	1590	1235
55°	1227	1211	1211	1193	1193	1094
65°	795	778	779	772	772	787
75°	343	359	380	382	382	371
85°	50	77	91	93	91	70
90°	0	0	0	0	0	



TEST NUMBER: P562860

CATALOG NUMBER: SQ4-PC3-0U-100D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2454.0	2454.0	2454.0	2454.0	2454.0
2.5°	2468.5	2447.2	2454.0	2448.3	2439.4
5°	2463.1	2438.6	2447.2	2440.3	2438.1
7.5°	2445.3	2420.9	2432.2	2427.6	2425.3
10°	2429.0	2404.5	2417.6	2413.0	2410.8
12.5°	2407.2	2384.5	2399.4	2394.9	2394.4
15°	2369.9	2349.9	2369.9	2369.9	2367.6
17.5°	2323.1	2304.9	2326.3	2327.6	2326.3
20°	2290.4	2270.4	2297.2	2295.0	2297.2
22.5°	2250.4	2233.9	2262.7	2256.8	2259.0
25°	2188.1	2172.6	2204.0	2197.2	2197.2
27.5°	2114.5	2103.4	2137.7	2130.4	2130.4
30°	2065.4	2054.3	2090.4	2081.3	2081.3
32.5°	2010.9	2003.3	2037.7	2026.8	2026.8
35°	1924.6	1920.1	1954.1	1940.5	1940.5
37.5°	1835.5	1831.5	1862.3	1845.8	1840.5
40°	1770.0	1767.8	1795.0	1776.9	1776.9
42.5°	1704.6	1702.4	1726.0	1704.1	1704.1
45°	1604.2	1599.7	1615.5	1595.0	1590.5
47.5°	1494.7	1490.2	1500.1	1477.8	1475.6
50°	1420.1	1415.7	1420.1	1399.6	1397.4
52.5°	1343.8	1335.8	1336.5	1316.0	1315.6
55°	1227.0	1211.4	1211.1	1192.9	1192.9
57.5°	1103.4	1082.9	1084.7	1069.2	1067.0
60°	1017.9	995.7	997.5	983.8	981.6
62.5°	934.3	908.6	913.9	898.4	898.0
65°	795.3	777.5	779.4	772.5	772.5
67.5°	661.7	645.2	657.1	651.7	651.2
70°	563.5	552.4	568.0	568.0	565.8
72.5°	472.6	472.2	491.7	491.7	493.1
75°	343.1	358.7	379.5	381.7	381.7
77.5°	229.0	256.6	279.5	280.4	279.9
80°	163.6	194.7	215.9	220.4	218.1
82.5°	110.9	143.8	161.3	165.8	163.6
85°	50.0	76.6	90.9	93.1	90.9
87.5°	14.5	30.5	36.4	36.3	32.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)