

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564346

Luminaire Tested: **SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564346  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6029.2 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 47.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564346  
CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564346

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17
4	71	61	53	47	63	54	48	43	43	39	35	32	29	27	23	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	35	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6214	6214	6214
5°	6270	6222	6189
10°	6250	6207	6174
15°	6223	6184	6150
20°	6191	6151	6106
25°	6148	6107	6036
30°	6081	6038	5952
35°	5992	5939	5855
40°	5855	5792	5687
45°	5617	5518	5404
50°	5196	5071	4971
55°	4534	4433	4340
60°	3821	3790	3714
65°	3305	3318	3292
70°	3035	3051	3051
75°	2916	2916	2937
80°	2742	2773	2742
85°	2212	2456	2456



TEST NUMBER: P564346

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.7	1.1
10°-20°	182.2	3.0
20°-30°	274.9	4.6
30°-40°	327.5	5.4
40°-50°	322.9	5.4
50°-60°	246.8	4.1
60°-70°	152.7	2.5
70°-80°	86.7	1.4
80°-90°	28.0	0.5
90°-100°	314.8	5.2
100°-110°	847.9	14.1
110°-120°	889.9	14.8
120°-130°	722.1	12.0
130°-140°	566.3	9.4
140°-150°	434.8	7.2
150°-160°	312.6	5.2
160°-170°	191.0	3.2
170°-180°	64.4	1.1
0°-30°	520.8	8.6
0°-40°	848.3	14.1
0°-60°	1417.9	23.5
0°-90°	1685.3	28.0
90°-120°	2052.6	34.0
90°-150°	3775.9	62.6
90°-180°	4344.0	72.0
0°-180°	6029.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	674	674	674	674	674	
5°	677	670	672	669	668	64
15°	652	645	647	645	644	184
25°	604	596	600	594	593	278
35°	532	526	527	520	520	332
45°	430	425	423	415	414	330
55°	282	277	276	271	270	253
65°	151	150	152	151	151	153
75°	82	82	82	82	82	86
85°	21	22	23	23	23	24
90°	2	5	10	11	11	4
95°	48	171	516	264	183	50
105°	157	244	938	1403	1317	165
115°	277	339	781	1509	1707	272
125°	378	434	701	1185	1395	338
135°	455	508	682	956	1083	351
145°	526	567	673	817	878	330
155°	598	619	667	733	757	275
165°	648	656	670	696	700	183
175°	674	673	670	680	678	64
180°	673	673	673	673	673	

TEST NUMBER: P564346

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	673.5	673.5	673.5	673.5	673.5
2.5°	677.7	671.8	673.5	672.1	668.9
5°	677.0	669.6	671.8	669.4	668.3
7.5°	671.8	664.5	666.7	664.3	663.7
10°	667.1	660.3	662.5	660.2	659.0
12.5°	662.0	654.8	657.4	654.6	653.5
15°	651.5	644.7	647.4	645.1	643.9
17.5°	639.9	632.6	635.4	632.7	631.2
20°	630.6	623.8	626.5	622.5	621.9
22.5°	620.4	613.6	616.3	610.9	610.8
25°	603.9	596.5	599.9	593.5	592.9
27.5°	584.3	577.5	580.2	573.7	573.1
30°	570.8	564.0	566.8	559.8	558.7
32.5°	555.5	549.2	551.5	544.5	543.8
35°	532.0	525.7	527.3	520.4	519.8
37.5°	505.2	499.5	500.4	492.7	492.2
40°	486.1	480.5	480.9	472.8	472.2
42.5°	465.3	459.6	459.1	451.0	450.4
45°	430.5	424.8	422.9	415.3	414.2
47.5°	390.8	385.1	381.6	375.4	374.6
50°	362.0	356.3	353.3	348.0	346.3
52.5°	330.9	325.2	322.7	317.9	316.2
55°	281.9	277.4	275.6	270.9	269.8
57.5°	235.4	232.4	231.8	227.3	226.8
60°	207.1	205.4	205.4	201.3	201.3
62.5°	183.0	181.7	182.6	179.9	179.5
65°	151.4	150.3	152.0	150.8	150.8
67.5°	126.5	126.5	127.5	127.0	127.0
70°	112.5	112.5	113.1	113.1	113.1
72.5°	100.0	99.6	101.1	101.0	100.6
75°	81.8	81.8	81.8	82.4	82.4
77.5°	63.7	63.8	64.3	64.2	63.7
80°	51.6	52.2	52.2	51.6	51.6
82.5°	39.6	40.1	40.1	40.0	39.6
85°	20.9	22.0	23.2	23.2	23.2
87.5°	6.4	8.9	11.3	11.5	11.0
90°	1.7	5.1	10.3	11.1	11.1
92.5°	20.9	73.9	146.1	70.3	48.9
95°	48.0	171.2	516.0	263.9	182.6
97.5°	76.6	196.0	809.3	676.1	509.9
100°	98.6	205.9	902.6	944.4	783.5
102.5°	119.8	219.7	933.5	1145.3	1013.2
105°	156.9	244.0	937.8	1403.0	1316.6
107.5°	191.8	269.6	897.8	1535.4	1557.7
110°	215.2	288.9	861.5	1576.5	1657.8



TEST NUMBER: P564346

CATALOG NUMBER: SQ4-PR1-125U-050D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	239.8	308.2	826.5	1567.4	1701.0
115°	276.9	338.9	780.9	1508.8	1706.6
117.5°	310.6	368.8	745.6	1415.4	1635.7
120°	332.6	388.7	727.7	1348.3	1574.6
122.5°	351.8	407.3	714.7	1279.8	1505.4
125°	378.0	434.2	701.2	1185.1	1394.6
127.5°	403.2	458.5	692.6	1101.6	1288.7
130°	418.3	473.6	689.2	1053.8	1218.1
132.5°	433.4	488.0	685.7	1011.6	1162.5
135°	455.2	508.0	681.5	956.1	1082.6
137.5°	475.9	526.5	679.2	908.9	1012.8
140°	490.3	538.9	677.2	879.9	973.8
142.5°	505.4	550.7	675.8	852.8	931.9
145°	526.3	567.4	672.9	817.4	877.8
147.5°	548.9	584.6	670.0	787.6	835.1
150°	564.0	595.0	668.6	768.9	808.3
152.5°	577.7	604.7	667.9	753.7	785.7
155°	597.5	619.2	666.9	733.4	756.9
157.5°	614.8	631.7	667.1	719.2	734.9
160°	625.7	640.0	667.7	710.9	722.6
162.5°	635.3	646.9	668.4	703.9	712.3
165°	648.0	655.6	669.5	696.1	699.5
167.5°	658.3	662.7	670.3	690.1	691.4
170°	665.2	666.8	670.3	686.6	686.6
172.5°	669.3	669.6	671.0	683.2	683.2
175°	673.7	672.9	670.3	679.7	678.0
177.5°	675.6	674.3	670.8	676.3	674.9
180°	672.9	672.9	672.9	672.9	672.9

(END OF REPORT)