

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562908

Luminaire Tested: **SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562908
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10401.6 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562908
CATALOG NUMBER: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562908

CATALOG NUMBER: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5781	5781	5781
5°	5824	5787	5765
10°	5810	5783	5766
15°	5780	5780	5774
20°	5741	5758	5758
25°	5687	5729	5711
30°	5618	5686	5661
35°	5534	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5205	5205	5121
55°	5039	4974	4899
60°	4796	4700	4624
65°	4433	4344	4306
70°	3880	3913	3897
75°	3123	3454	3474
80°	2218	2928	2959
85°	1350	2456	2456



TEST NUMBER: P562908

CATALOG NUMBER: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.6	1.1
10°-20°	340.3	3.3
20°-30°	515.4	5.0
30°-40°	617.9	5.9
40°-50°	630.0	6.1
50°-60°	550.0	5.3
60°-70°	393.7	3.8
70°-80°	202.8	1.9
80°-90°	53.5	0.5
90°-100°	503.0	4.8
100°-110°	1388.8	13.4
110°-120°	1432.3	13.8
120°-130°	1150.9	11.1
130°-140°	904.5	8.7
140°-150°	693.7	6.7
150°-160°	498.6	4.8
160°-170°	304.9	2.9
170°-180°	102.8	1.0
0°-30°	974.3	9.4
0°-40°	1592.1	15.3
0°-60°	2772.1	26.7
0°-90°	3422.1	32.9
90°-120°	3324.1	32.0
90°-150°	6073.2	58.4
90°-180°	6979.0	67.1
0°-180°	10401.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1253	1253	1253	1253	1253	
5°	1258	1245	1250	1246	1245	119
15°	1210	1200	1210	1210	1209	341
25°	1117	1109	1126	1122	1122	514
35°	983	980	998	991	991	615
45°	819	817	825	814	812	631
55°	626	619	618	609	609	559
65°	406	397	398	394	394	402
75°	175	183	194	195	195	189
85°	26	39	46	48	46	35
90°	3	7	14	16	17	6
95°	74	272	913	375	244	79
105°	248	382	1528	2333	2196	263
115°	443	536	1231	2436	2770	436
125°	608	692	1115	1888	2215	541
135°	732	811	1084	1529	1724	566
145°	849	908	1071	1302	1401	532
155°	957	989	1062	1168	1205	441
165°	1036	1050	1067	1109	1117	292
175°	1074	1076	1069	1084	1081	102
180°	1074	1074	1074	1074	1074	

TEST NUMBER: P562908

CATALOG NUMBER: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1253.1	1253.1	1253.1	1253.1	1253.1
2.5°	1260.5	1249.6	1253.1	1250.2	1245.7
5°	1257.7	1245.2	1249.6	1246.1	1245.0
7.5°	1248.7	1236.2	1241.9	1239.6	1238.5
10°	1240.3	1227.8	1234.5	1232.2	1231.0
12.5°	1229.2	1217.6	1225.2	1222.9	1222.7
15°	1210.2	1199.9	1210.2	1210.1	1209.0
17.5°	1186.2	1176.9	1187.9	1188.6	1187.9
20°	1169.5	1159.3	1173.0	1171.9	1173.0
22.5°	1149.1	1140.7	1155.4	1152.4	1153.5
25°	1117.3	1109.4	1125.5	1122.0	1122.0
27.5°	1079.7	1074.1	1091.6	1087.9	1087.9
30°	1054.7	1049.0	1067.4	1062.8	1062.8
32.5°	1026.8	1023.0	1040.5	1035.0	1035.0
35°	982.7	980.5	997.8	990.9	990.9
37.5°	937.3	935.2	950.9	942.5	939.8
40°	903.8	902.7	916.6	907.3	907.3
42.5°	870.4	869.3	881.3	870.2	870.2
45°	819.1	816.9	824.9	814.5	812.2
47.5°	763.2	761.0	766.0	754.6	753.5
50°	725.2	722.9	725.2	714.7	713.6
52.5°	686.2	682.1	682.5	672.0	671.8
55°	626.5	618.6	618.4	609.1	609.1
57.5°	563.4	553.0	553.9	546.0	544.9
60°	519.8	508.5	509.4	502.4	501.2
62.5°	477.1	463.9	466.7	458.8	458.5
65°	406.1	397.0	398.0	394.5	394.5
67.5°	337.9	329.5	335.5	332.8	332.5
70°	287.7	282.1	290.1	290.0	288.9
72.5°	241.3	241.1	251.1	251.1	251.8
75°	175.2	183.1	193.8	194.9	194.9
77.5°	117.0	131.0	142.7	143.2	142.9
80°	83.5	99.4	110.2	112.5	111.4
82.5°	56.6	73.4	82.4	84.7	83.5
85°	25.5	39.1	46.4	47.5	46.4
87.5°	8.1	17.0	21.3	21.6	20.1
90°	3.4	6.8	13.7	15.5	17.2
92.5°	30.9	128.4	229.6	83.8	65.3
95°	73.9	272.2	912.6	375.1	244.1
97.5°	122.4	304.9	1351.9	1040.9	753.8
100°	158.1	324.5	1514.2	1524.9	1239.2
102.5°	192.5	346.8	1545.8	1884.1	1613.2
105°	247.5	381.9	1527.9	2332.6	2196.5
107.5°	305.9	425.6	1442.7	2548.9	2598.7
110°	347.2	454.7	1376.7	2595.5	2756.8



TEST NUMBER: P562908

CATALOG NUMBER: SQ4-PC3-100U-050D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.3	487.8	1314.8	2558.7	2796.7
115°	443.4	535.9	1230.6	2436.1	2770.5
117.5°	495.0	587.1	1175.2	2263.6	2644.0
120°	529.4	620.1	1153.2	2146.8	2529.9
122.5°	562.4	649.1	1135.4	2037.7	2400.7
125°	608.4	692.4	1115.4	1887.7	2215.4
127.5°	647.6	731.6	1103.7	1760.9	2043.5
130°	673.7	757.8	1098.2	1683.3	1940.4
132.5°	698.5	778.5	1092.7	1618.1	1851.0
135°	732.2	811.1	1084.5	1528.9	1723.9
137.5°	770.0	841.9	1080.4	1454.0	1620.4
140°	790.6	861.2	1077.6	1404.1	1550.3
142.5°	814.0	879.2	1074.9	1359.7	1488.4
145°	849.0	907.9	1070.7	1301.6	1400.7
147.5°	882.7	934.1	1067.0	1252.6	1329.6
150°	907.5	949.5	1065.6	1223.4	1285.6
152.5°	926.7	966.0	1064.2	1198.4	1249.8
155°	957.3	989.2	1062.2	1167.8	1204.8
157.5°	985.5	1010.0	1062.5	1145.6	1170.8
160°	1002.0	1023.8	1063.9	1133.0	1151.5
162.5°	1015.8	1034.9	1065.2	1122.0	1136.4
165°	1036.4	1049.8	1067.3	1108.8	1117.2
167.5°	1052.2	1060.3	1069.0	1100.7	1103.4
170°	1060.4	1067.2	1069.0	1096.5	1096.5
172.5°	1067.3	1071.3	1069.0	1091.0	1089.7
175°	1074.2	1075.9	1069.0	1084.4	1081.1
177.5°	1076.9	1075.6	1068.7	1078.2	1075.6
180°	1074.2	1074.2	1074.2	1074.2	1074.2

(END OF REPORT)