

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564418

Luminaire Tested: **SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564418  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8553.4 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 75.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564418  
CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564418

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49		
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42		
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36		
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	31		
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30	26		
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23		
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20		
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18		
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16		
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15		
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15530	15530	15530
5°	15669	15549	15468
10°	15620	15511	15430
15°	15551	15455	15371
20°	15473	15374	15260
25°	15365	15261	15084
30°	15198	15091	14874
35°	14974	14844	14631
40°	14632	14476	14213
45°	14037	13790	13507
50°	12986	12673	12423
55°	11334	11078	10845
60°	9551	9470	9283
65°	8261	8294	8230
70°	7588	7626	7626
75°	7286	7286	7340
80°	6854	6934	6854
85°	5526	6140	6140



TEST NUMBER: P564418

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.2	1.9
10°-20°	455.4	5.3
20°-30°	686.9	8.0
30°-40°	818.5	9.6
40°-50°	806.9	9.4
50°-60°	616.7	7.2
60°-70°	381.6	4.5
70°-80°	216.8	2.5
80°-90°	67.5	0.8
90°-100°	314.8	3.7
100°-110°	847.9	9.9
110°-120°	889.9	10.4
120°-130°	722.1	8.4
130°-140°	566.3	6.6
140°-150°	434.8	5.1
150°-160°	312.6	3.7
160°-170°	191.0	2.2
170°-180°	64.4	0.8
0°-30°	1301.5	15.2
0°-40°	2119.9	24.8
0°-60°	3543.6	41.4
0°-90°	4209.5	49.2
90°-120°	2052.6	24.0
90°-150°	3775.9	44.1
90°-180°	4344.0	50.8
0°-180°	8553.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1692	1674	1679	1673	1670	161
15°	1628	1611	1618	1612	1609	459
25°	1509	1491	1499	1483	1482	695
35°	1330	1314	1318	1300	1299	830
45°	1076	1062	1057	1038	1035	824
55°	705	693	689	677	674	631
65°	378	376	380	377	377	383
75°	204	204	204	206	206	216
85°	52	55	58	58	58	61
90°	2	5	10	11	11	5
95°	48	171	516	264	183	50
105°	157	244	938	1403	1317	165
115°	277	339	781	1509	1707	272
125°	378	434	701	1185	1395	338
135°	455	508	682	956	1083	351
145°	526	567	673	817	878	330
155°	598	619	667	733	757	275
165°	648	656	670	696	700	183
175°	674	673	670	680	678	64
180°	673	673	673	673	673	

TEST NUMBER: P564418

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1683.2	1683.2	1683.2	1683.2	1683.2
2.5°	1693.7	1678.9	1683.2	1679.6	1671.6
5°	1691.9	1673.5	1678.9	1673.0	1670.2
7.5°	1678.9	1660.7	1666.1	1660.3	1658.6
10°	1667.3	1650.3	1655.7	1649.8	1647.0
12.5°	1654.5	1636.4	1642.9	1635.9	1633.1
15°	1628.1	1611.1	1618.0	1612.1	1609.3
17.5°	1599.1	1581.0	1587.8	1581.1	1577.4
20°	1575.9	1558.9	1565.8	1555.6	1554.2
22.5°	1550.4	1533.4	1540.3	1526.6	1526.4
25°	1509.3	1490.8	1499.1	1483.1	1481.7
27.5°	1460.3	1443.2	1450.1	1433.8	1432.1
30°	1426.6	1409.6	1416.5	1399.0	1396.2
32.5°	1388.3	1372.5	1378.2	1360.8	1359.1
35°	1329.5	1313.9	1317.9	1300.4	1299.0
37.5°	1262.5	1248.3	1250.6	1231.4	1230.0
40°	1214.9	1200.8	1201.9	1181.6	1180.1
42.5°	1162.7	1148.6	1147.4	1127.1	1125.6
45°	1075.8	1061.6	1056.9	1038.0	1035.2
47.5°	976.6	962.4	953.7	938.3	936.3
50°	904.7	890.5	882.9	869.8	865.5
52.5°	827.0	812.8	806.4	794.4	790.1
55°	704.6	693.3	688.7	677.0	674.2
57.5°	588.3	580.7	579.3	568.0	566.9
60°	517.6	513.3	513.2	503.1	503.1
62.5°	457.3	454.2	456.4	449.7	448.6
65°	378.4	375.6	379.9	377.0	377.0
67.5°	316.1	316.1	318.7	317.5	317.5
70°	281.3	281.3	282.7	282.7	282.7
72.5°	249.9	248.8	252.6	252.5	251.4
75°	204.4	204.4	204.4	205.9	205.9
77.5°	159.2	159.5	160.6	160.3	159.2
80°	129.0	130.5	130.5	129.0	129.0
82.5°	98.9	100.3	100.3	100.0	98.9
85°	52.2	55.0	58.0	58.0	58.0
87.5°	15.4	20.6	25.3	25.4	24.3
90°	1.7	5.1	10.3	11.1	11.1
92.5°	20.9	73.9	146.1	70.3	48.9
95°	48.0	171.2	516.0	263.9	182.6
97.5°	76.6	196.0	809.3	676.1	509.9
100°	98.6	205.9	902.6	944.4	783.5
102.5°	119.8	219.7	933.5	1145.3	1013.2
105°	156.9	244.0	937.8	1403.0	1316.6
107.5°	191.8	269.6	897.8	1535.4	1557.7
110°	215.2	288.9	861.5	1576.5	1657.8



TEST NUMBER: P564418

CATALOG NUMBER: SQ4-PR1-125U-125D-935-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	239.8	308.2	826.5	1567.4	1701.0
115°	276.9	338.9	780.9	1508.8	1706.6
117.5°	310.6	368.8	745.6	1415.4	1635.7
120°	332.6	388.7	727.7	1348.3	1574.6
122.5°	351.8	407.3	714.7	1279.8	1505.4
125°	378.0	434.2	701.2	1185.1	1394.6
127.5°	403.2	458.5	692.6	1101.6	1288.7
130°	418.3	473.6	689.2	1053.8	1218.1
132.5°	433.4	488.0	685.7	1011.6	1162.5
135°	455.2	508.0	681.5	956.1	1082.6
137.5°	475.9	526.5	679.2	908.9	1012.8
140°	490.3	538.9	677.2	879.9	973.8
142.5°	505.4	550.7	675.8	852.8	931.9
145°	526.3	567.4	672.9	817.4	877.8
147.5°	548.9	584.6	670.0	787.6	835.1
150°	564.0	595.0	668.6	768.9	808.3
152.5°	577.7	604.7	667.9	753.7	785.7
155°	597.5	619.2	666.9	733.4	756.9
157.5°	614.8	631.7	667.1	719.2	734.9
160°	625.7	640.0	667.7	710.9	722.6
162.5°	635.3	646.9	668.4	703.9	712.3
165°	648.0	655.6	669.5	696.1	699.5
167.5°	658.3	662.7	670.3	690.1	691.4
170°	665.2	666.8	670.3	686.6	686.6
172.5°	669.3	669.6	671.0	683.2	683.2
175°	673.7	672.9	670.3	679.7	678.0
177.5°	675.6	674.3	670.8	676.3	674.9
180°	672.9	672.9	672.9	672.9	672.9

(END OF REPORT)