

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562932

Luminaire Tested: **SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562932  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12022.2 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 103.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562932  
CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562932

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8520	8520	8520
5°	8584	8529	8497
10°	8563	8523	8499
15°	8518	8518	8510
20°	8462	8487	8487
25°	8382	8443	8417
30°	8280	8381	8344
35°	8157	8282	8224
40°	8022	8136	8053
45°	7876	7932	7810
50°	7670	7670	7548
55°	7427	7331	7221
60°	7068	6926	6816
65°	6533	6403	6346
70°	5720	5766	5743
75°	4602	5090	5121
80°	3270	4317	4362
85°	1990	3620	3620



TEST NUMBER: P562932

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.8	1.5
10°-20°	501.6	4.2
20°-30°	759.6	6.3
30°-40°	910.7	7.6
40°-50°	928.6	7.7
50°-60°	810.6	6.7
60°-70°	580.3	4.8
70°-80°	298.9	2.5
80°-90°	77.8	0.6
90°-100°	503.0	4.2
100°-110°	1388.8	11.6
110°-120°	1432.3	11.9
120°-130°	1150.9	9.6
130°-140°	904.5	7.5
140°-150°	693.7	5.8
150°-160°	498.6	4.1
160°-170°	304.9	2.5
170°-180°	102.8	0.9
0°-30°	1436.0	11.9
0°-40°	2346.6	19.5
0°-60°	4085.8	34.0
0°-90°	5042.8	41.9
90°-120°	3324.1	27.6
90°-150°	6073.2	50.5
90°-180°	6979.0	58.1
0°-180°	12022.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1847	1847	1847	1847	1847	
5°	1854	1835	1842	1837	1835	176
15°	1784	1769	1784	1784	1782	503
25°	1647	1635	1659	1654	1654	758
35°	1448	1445	1471	1460	1460	906
45°	1207	1204	1216	1200	1197	929
55°	923	912	912	898	898	823
65°	598	585	587	581	581	592
75°	258	270	286	287	287	279
85°	38	58	68	70	68	51
90°	3	7	14	16	17	7
95°	74	272	913	375	244	79
105°	248	382	1528	2333	2196	263
115°	443	536	1231	2436	2770	436
125°	608	692	1115	1888	2215	541
135°	732	811	1084	1529	1724	566
145°	849	908	1071	1302	1401	532
155°	957	989	1062	1168	1205	441
165°	1036	1050	1067	1109	1117	292
175°	1074	1076	1069	1084	1081	102
180°	1074	1074	1074	1074	1074	

TEST NUMBER: P562932

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1846.9	1846.9	1846.9	1846.9	1846.9
2.5°	1857.8	1841.8	1846.9	1842.6	1836.0
5°	1853.7	1835.3	1841.8	1836.6	1834.9
7.5°	1840.4	1822.0	1830.5	1827.0	1825.3
10°	1828.1	1809.7	1819.5	1816.1	1814.4
12.5°	1811.7	1794.6	1805.9	1802.4	1802.1
15°	1783.6	1768.6	1783.6	1783.6	1781.9
17.5°	1748.4	1734.7	1750.8	1751.8	1750.8
20°	1723.8	1708.7	1728.9	1727.2	1728.9
22.5°	1693.7	1681.3	1702.9	1698.5	1700.2
25°	1646.8	1635.1	1658.8	1653.7	1653.7
27.5°	1591.4	1583.0	1608.9	1603.4	1603.4
30°	1554.5	1546.1	1573.3	1566.4	1566.4
32.5°	1513.4	1507.7	1533.6	1525.4	1525.4
35°	1448.4	1445.1	1470.7	1460.4	1460.4
37.5°	1381.4	1378.4	1401.6	1389.2	1385.2
40°	1332.2	1330.5	1351.0	1337.3	1337.3
42.5°	1282.9	1281.2	1299.0	1282.6	1282.6
45°	1207.3	1204.0	1215.9	1200.4	1197.1
47.5°	1124.9	1121.6	1129.0	1112.2	1110.5
50°	1068.8	1065.5	1068.8	1053.4	1051.7
52.5°	1011.3	1005.3	1005.9	990.5	990.1
55°	923.4	911.7	911.5	897.8	897.8
57.5°	830.4	815.0	816.4	804.7	803.1
60°	766.1	749.4	750.7	740.4	738.8
62.5°	703.2	683.8	687.8	676.2	675.8
65°	598.5	585.2	586.6	581.4	581.4
67.5°	498.0	485.6	494.6	490.4	490.1
70°	424.1	415.7	427.5	427.5	425.8
72.5°	355.7	355.4	370.1	370.1	371.1
75°	258.2	269.9	285.6	287.3	287.3
77.5°	172.4	193.1	210.3	211.0	210.7
80°	123.1	146.5	162.5	165.8	164.2
82.5°	83.5	108.2	121.4	124.8	123.1
85°	37.6	57.7	68.4	70.1	68.4
87.5°	11.6	24.3	30.1	30.4	28.1
90°	3.4	6.8	13.7	15.5	17.2
92.5°	30.9	128.4	229.6	83.8	65.3
95°	73.9	272.2	912.6	375.1	244.1
97.5°	122.4	304.9	1351.9	1040.9	753.8
100°	158.1	324.5	1514.2	1524.9	1239.2
102.5°	192.5	346.8	1545.8	1884.1	1613.2
105°	247.5	381.9	1527.9	2332.6	2196.5
107.5°	305.9	425.6	1442.7	2548.9	2598.7
110°	347.2	454.7	1376.7	2595.5	2756.8



TEST NUMBER: P562932

CATALOG NUMBER: SQ4-PC3-100U-075D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	384.3	487.8	1314.8	2558.7	2796.7
115°	443.4	535.9	1230.6	2436.1	2770.5
117.5°	495.0	587.1	1175.2	2263.6	2644.0
120°	529.4	620.1	1153.2	2146.8	2529.9
122.5°	562.4	649.1	1135.4	2037.7	2400.7
125°	608.4	692.4	1115.4	1887.7	2215.4
127.5°	647.6	731.6	1103.7	1760.9	2043.5
130°	673.7	757.8	1098.2	1683.3	1940.4
132.5°	698.5	778.5	1092.7	1618.1	1851.0
135°	732.2	811.1	1084.5	1528.9	1723.9
137.5°	770.0	841.9	1080.4	1454.0	1620.4
140°	790.6	861.2	1077.6	1404.1	1550.3
142.5°	814.0	879.2	1074.9	1359.7	1488.4
145°	849.0	907.9	1070.7	1301.6	1400.7
147.5°	882.7	934.1	1067.0	1252.6	1329.6
150°	907.5	949.5	1065.6	1223.4	1285.6
152.5°	926.7	966.0	1064.2	1198.4	1249.8
155°	957.3	989.2	1062.2	1167.8	1204.8
157.5°	985.5	1010.0	1062.5	1145.6	1170.8
160°	1002.0	1023.8	1063.9	1133.0	1151.5
162.5°	1015.8	1034.9	1065.2	1122.0	1136.4
165°	1036.4	1049.8	1067.3	1108.8	1117.2
167.5°	1052.2	1060.3	1069.0	1100.7	1103.4
170°	1060.4	1067.2	1069.0	1096.5	1096.5
172.5°	1067.3	1071.3	1069.0	1091.0	1089.7
175°	1074.2	1075.9	1069.0	1084.4	1081.1
177.5°	1076.9	1075.6	1068.7	1078.2	1075.6
180°	1074.2	1074.2	1074.2	1074.2	1074.2

(END OF REPORT)