

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564874

Luminaire Tested: **SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564874
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3280.8 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564874
CATALOG NUMBER: SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564874

CATALOG NUMBER: SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11897	11897	11897
5°	11974	11880	11827
10°	11878	11783	11718
15°	11752	11622	11579
20°	11612	11433	11411
25°	11449	11242	11207
30°	11207	11038	10966
35°	10889	10736	10672
40°	10549	10385	10345
45°	10139	10006	9962
50°	9719	9637	9572
55°	9265	9265	9119
60°	8700	8868	8553
65°	7962	8359	7763
70°	7019	7693	6836
75°	5992	6883	5832
80°	4649	5797	4707
85°	3006	4446	3970



TEST NUMBER: P564874

CATALOG NUMBER: SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.4	3.7
10°-20°	342.8	10.4
20°-30°	508.5	15.5
30°-40°	595.0	18.1
40°-50°	592.3	18.1
50°-60°	511.5	15.6
60°-70°	368.2	11.2
70°-80°	193.1	5.9
80°-90°	47.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	972.7	29.6
0°-40°	1567.7	47.8
0°-60°	2671.6	81.4
0°-90°	3280.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3280.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1293	1278	1283	1279	1277	122
15°	1230	1215	1217	1214	1212	347
25°	1125	1106	1104	1098	1101	517
35°	967	954	953	944	948	604
45°	777	770	767	765	764	600
55°	576	575	576	568	567	514
65°	365	376	383	368	356	361
75°	168	184	193	180	164	180
85°	28	37	42	40	38	38
90°	0	0	0	0	0	



TEST NUMBER: P564874

CATALOG NUMBER: SQ4-PW1-0U-100D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1289.5	1289.5	1289.5	1289.5	1289.5
2.5°	1296.7	1286.1	1289.5	1286.6	1280.4
5°	1292.9	1278.4	1282.7	1279.2	1277.0
7.5°	1279.7	1266.4	1269.5	1265.8	1264.5
10°	1267.9	1254.6	1257.7	1253.1	1250.8
12.5°	1254.3	1240.0	1243.1	1238.5	1237.2
15°	1230.4	1214.8	1216.8	1214.4	1212.2
17.5°	1202.7	1186.9	1187.2	1183.6	1183.1
20°	1182.7	1166.0	1164.5	1160.0	1162.2
22.5°	1160.9	1143.3	1141.8	1135.5	1138.6
25°	1124.7	1105.9	1104.3	1097.5	1100.9
27.5°	1082.9	1064.3	1064.3	1054.8	1058.4
30°	1052.0	1034.3	1036.1	1024.9	1029.3
32.5°	1019.3	1003.3	1004.3	993.1	997.5
35°	966.8	953.5	953.2	944.2	947.5
37.5°	913.2	901.4	899.6	894.4	895.2
40°	875.9	865.9	862.3	858.9	858.9
42.5°	836.9	827.7	824.1	821.6	820.7
45°	777.1	770.4	766.9	764.6	763.5
47.5°	718.0	711.8	708.7	707.1	706.0
50°	677.1	672.7	671.4	668.0	666.9
52.5°	636.2	633.6	632.4	628.0	626.9
55°	576.0	574.9	576.0	568.0	566.9
57.5°	513.3	515.1	518.7	508.0	505.3
60°	471.5	475.9	480.6	468.0	463.5
62.5°	428.8	435.9	442.4	427.9	421.7
65°	364.7	375.8	382.9	367.8	355.6
67.5°	302.9	316.7	325.2	308.9	295.2
70°	260.2	275.7	285.2	268.9	253.4
72.5°	222.9	240.2	247.9	232.5	217.0
75°	168.1	183.7	193.1	180.3	163.6
77.5°	119.3	134.0	141.8	130.6	116.8
80°	87.5	103.0	109.1	99.7	88.6
82.5°	62.0	74.9	79.1	73.4	65.9
85°	28.4	37.3	42.0	39.7	37.5
87.5°	7.3	13.5	17.3	17.3	18.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)