

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562980

Luminaire Tested: **SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562980
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15528.5 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 140.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562980
CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562980

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55		
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	47		
2	90	83	76	71	83	77	72	67	66	62	59	56	54	51	47	45	43	39		
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33		
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28		
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24		
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21		
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19		
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17		
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15		
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14446	14446	14446
5°	14555	14461	14408
10°	14520	14452	14411
15°	14444	14444	14430
20°	14348	14391	14391
25°	14213	14316	14272
30°	14040	14210	14148
35°	13831	14043	13945
40°	13602	13795	13655
45°	13355	13450	13242
50°	13006	13006	12798
55°	12593	12430	12243
60°	11985	11744	11557
65°	11078	10857	10762
70°	9699	9777	9738
75°	7803	8630	8682
80°	5547	7319	7396
85°	3377	6140	6140



TEST NUMBER: P562980

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.4	1.9
10°-20°	850.5	5.5
20°-30°	1288.0	8.3
30°-40°	1544.1	9.9
40°-50°	1574.5	10.1
50°-60°	1374.4	8.9
60°-70°	984.0	6.3
70°-80°	506.8	3.3
80°-90°	130.4	0.8
90°-100°	503.0	3.2
100°-110°	1388.8	8.9
110°-120°	1432.3	9.2
120°-130°	1150.9	7.4
130°-140°	904.5	5.8
140°-150°	693.7	4.5
150°-160°	498.6	3.2
160°-170°	304.9	2.0
170°-180°	102.8	0.7
0°-30°	2434.8	15.7
0°-40°	3979.0	25.6
0°-60°	6927.8	44.6
0°-90°	8549.0	55.1
90°-120°	3324.1	21.4
90°-150°	6073.2	39.1
90°-180°	6979.0	44.9
0°-180°	15528.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3132	3132	3132	3132	3132	
5°	3143	3112	3123	3114	3111	298
15°	3024	2999	3024	3024	3021	853
25°	2792	2772	2813	2804	2804	1285
35°	2456	2450	2494	2476	2476	1536
45°	2047	2042	2062	2035	2030	1576
55°	1566	1546	1546	1522	1522	1396
65°	1015	992	995	986	986	1004
75°	438	458	484	487	487	473
85°	64	98	116	119	116	87
90°	3	7	14	16	17	8
95°	74	272	913	375	244	79
105°	248	382	1528	2333	2196	263
115°	443	536	1231	2436	2770	436
125°	608	692	1115	1888	2215	541
135°	732	811	1084	1529	1724	566
145°	849	908	1071	1302	1401	532
155°	957	989	1062	1168	1205	441
165°	1036	1050	1067	1109	1117	292
175°	1074	1076	1069	1084	1081	102
180°	1074	1074	1074	1074	1074	

TEST NUMBER: P562980

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3131.6	3131.6	3131.6	3131.6	3131.6
2.5°	3150.2	3122.9	3131.6	3124.4	3113.0
5°	3143.2	3112.0	3122.9	3114.1	3111.3
7.5°	3120.6	3089.4	3103.8	3097.9	3095.1
10°	3099.7	3068.5	3085.2	3079.3	3076.5
12.5°	3071.9	3043.0	3062.0	3056.2	3055.6
15°	3024.3	2998.8	3024.3	3024.3	3021.4
17.5°	2964.6	2941.3	2968.6	2970.3	2968.6
20°	2922.8	2897.3	2931.5	2928.7	2931.5
22.5°	2871.8	2850.8	2887.5	2880.0	2882.8
25°	2792.3	2772.5	2812.6	2803.9	2803.9
27.5°	2698.4	2684.2	2728.0	2718.7	2718.7
30°	2635.8	2621.6	2667.7	2656.1	2656.1
32.5°	2566.2	2556.5	2600.4	2586.5	2586.5
35°	2456.0	2450.3	2493.7	2476.3	2476.3
37.5°	2342.3	2337.2	2376.5	2355.5	2348.7
40°	2258.8	2256.0	2290.7	2267.5	2267.5
42.5°	2175.3	2172.5	2202.6	2174.7	2174.7
45°	2047.1	2041.5	2061.6	2035.4	2029.7
47.5°	1907.4	1901.7	1914.3	1885.9	1883.0
50°	1812.3	1806.6	1812.3	1786.1	1783.3
52.5°	1714.8	1704.6	1705.6	1679.5	1678.9
55°	1565.8	1546.0	1545.5	1522.3	1522.3
57.5°	1408.1	1382.0	1384.3	1364.5	1361.7
60°	1299.0	1270.7	1272.9	1255.5	1252.6
62.5°	1192.3	1159.4	1166.2	1146.5	1145.9
65°	1014.9	992.2	994.6	985.9	985.9
67.5°	844.4	823.4	838.6	831.6	831.0
70°	719.1	704.9	724.9	724.8	722.0
72.5°	603.1	602.6	627.5	627.5	629.2
75°	437.8	457.7	484.2	487.1	487.1
77.5°	292.3	327.4	356.7	357.8	357.2
80°	208.8	248.5	275.5	281.2	278.4
82.5°	141.5	183.5	205.9	211.6	208.8
85°	63.8	97.8	116.0	118.8	116.0
87.5°	19.2	40.3	49.1	49.4	45.2
90°	3.4	6.8	13.7	15.5	17.2
92.5°	30.9	128.4	229.6	83.8	65.3
95°	73.9	272.2	912.6	375.1	244.1
97.5°	122.4	304.9	1351.9	1040.9	753.8
100°	158.1	324.5	1514.2	1524.9	1239.2
102.5°	192.5	346.8	1545.8	1884.1	1613.2
105°	247.5	381.9	1527.9	2332.6	2196.5
107.5°	305.9	425.6	1442.7	2548.9	2598.7
110°	347.2	454.7	1376.7	2595.5	2756.8

TEST NUMBER: P562980

CATALOG NUMBER: SQ4-PC3-100U-125D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.3	487.8	1314.8	2558.7	2796.7
115°	443.4	535.9	1230.6	2436.1	2770.5
117.5°	495.0	587.1	1175.2	2263.6	2644.0
120°	529.4	620.1	1153.2	2146.8	2529.9
122.5°	562.4	649.1	1135.4	2037.7	2400.7
125°	608.4	692.4	1115.4	1887.7	2215.4
127.5°	647.6	731.6	1103.7	1760.9	2043.5
130°	673.7	757.8	1098.2	1683.3	1940.4
132.5°	698.5	778.5	1092.7	1618.1	1851.0
135°	732.2	811.1	1084.5	1528.9	1723.9
137.5°	770.0	841.9	1080.4	1454.0	1620.4
140°	790.6	861.2	1077.6	1404.1	1550.3
142.5°	814.0	879.2	1074.9	1359.7	1488.4
145°	849.0	907.9	1070.7	1301.6	1400.7
147.5°	882.7	934.1	1067.0	1252.6	1329.6
150°	907.5	949.5	1065.6	1223.4	1285.6
152.5°	926.7	966.0	1064.2	1198.4	1249.8
155°	957.3	989.2	1062.2	1167.8	1204.8
157.5°	985.5	1010.0	1062.5	1145.6	1170.8
160°	1002.0	1023.8	1063.9	1133.0	1151.5
162.5°	1015.8	1034.9	1065.2	1122.0	1136.4
165°	1036.4	1049.8	1067.3	1108.8	1117.2
167.5°	1052.2	1060.3	1069.0	1100.7	1103.4
170°	1060.4	1067.2	1069.0	1096.5	1096.5
172.5°	1067.3	1071.3	1069.0	1091.0	1089.7
175°	1074.2	1075.9	1069.0	1084.4	1081.1
177.5°	1076.9	1075.6	1068.7	1078.2	1075.6
180°	1074.2	1074.2	1074.2	1074.2	1074.2

(END OF REPORT)