

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563004

Luminaire Tested: **SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563004  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12110.8 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 96.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563004  
CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563004

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	76	74	62	60	58	47	45	44	32	31	31	24
2	85	77	72	67	75	70	65	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	48	43	43	38	34	32	29	26	22	20	19	14
5	65	53	46	40	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	17	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5781	5781	5781
5°	5824	5787	5765
10°	5810	5783	5766
15°	5780	5780	5774
20°	5741	5758	5758
25°	5687	5729	5711
30°	5618	5686	5661
35°	5534	5619	5580
40°	5443	5520	5464
45°	5344	5382	5299
50°	5205	5205	5121
55°	5039	4974	4899
60°	4796	4700	4624
65°	4433	4344	4306
70°	3880	3913	3897
75°	3123	3454	3474
80°	2218	2928	2959
85°	1350	2456	2456



TEST NUMBER: P563004

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.6	1.0
10°-20°	340.3	2.8
20°-30°	515.4	4.3
30°-40°	617.9	5.1
40°-50°	630.0	5.2
50°-60°	550.0	4.5
60°-70°	393.7	3.3
70°-80°	202.8	1.7
80°-90°	54.4	0.4
90°-100°	629.6	5.2
100°-110°	1695.9	14.0
110°-120°	1779.8	14.7
120°-130°	1444.2	11.9
130°-140°	1132.7	9.4
140°-150°	869.6	7.2
150°-160°	625.2	5.2
160°-170°	382.0	3.2
170°-180°	128.8	1.1
0°-30°	974.3	8.0
0°-40°	1592.1	13.1
0°-60°	2772.1	22.9
0°-90°	3423.1	28.3
90°-120°	4105.2	33.9
90°-150°	7551.7	62.4
90°-180°	8688.0	71.7
0°-180°	12110.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1253	1253	1253	1253	1253	
5°	1258	1245	1250	1246	1245	119
15°	1210	1200	1210	1210	1209	341
25°	1117	1109	1126	1122	1122	514
35°	983	980	998	991	991	615
45°	819	817	825	814	812	631
55°	626	619	618	609	609	559
65°	406	397	398	394	394	402
75°	175	183	194	195	195	189
85°	26	39	46	48	46	35
90°	3	10	21	22	22	8
95°	96	342	1032	528	365	100
105°	314	488	1876	2806	2633	330
115°	554	678	1562	3018	3413	545
125°	756	868	1402	2370	2789	675
135°	910	1016	1363	1912	2165	703
145°	1053	1135	1346	1635	1756	660
155°	1195	1238	1334	1467	1514	550
165°	1296	1311	1339	1392	1399	365
175°	1348	1346	1341	1359	1356	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P563004

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1253.1	1253.1	1253.1	1253.1	1253.1
2.5°	1260.5	1249.6	1253.1	1250.2	1245.7
5°	1257.7	1245.2	1249.6	1246.1	1245.0
7.5°	1248.7	1236.2	1241.9	1239.6	1238.5
10°	1240.3	1227.8	1234.5	1232.2	1231.0
12.5°	1229.2	1217.6	1225.2	1222.9	1222.7
15°	1210.2	1199.9	1210.2	1210.1	1209.0
17.5°	1186.2	1176.9	1187.9	1188.6	1187.9
20°	1169.5	1159.3	1173.0	1171.9	1173.0
22.5°	1149.1	1140.7	1155.4	1152.4	1153.5
25°	1117.3	1109.4	1125.5	1122.0	1122.0
27.5°	1079.7	1074.1	1091.6	1087.9	1087.9
30°	1054.7	1049.0	1067.4	1062.8	1062.8
32.5°	1026.8	1023.0	1040.5	1035.0	1035.0
35°	982.7	980.5	997.8	990.9	990.9
37.5°	937.3	935.2	950.9	942.5	939.8
40°	903.8	902.7	916.6	907.3	907.3
42.5°	870.4	869.3	881.3	870.2	870.2
45°	819.1	816.9	824.9	814.5	812.2
47.5°	763.2	761.0	766.0	754.6	753.5
50°	725.2	722.9	725.2	714.7	713.6
52.5°	686.2	682.1	682.5	672.0	671.8
55°	626.5	618.6	618.4	609.1	609.1
57.5°	563.4	553.0	553.9	546.0	544.9
60°	519.8	508.5	509.4	502.4	501.2
62.5°	477.1	463.9	466.7	458.8	458.5
65°	406.1	397.0	398.0	394.5	394.5
67.5°	337.9	329.5	335.5	332.8	332.5
70°	287.7	282.1	290.1	290.0	288.9
72.5°	241.3	241.1	251.1	251.1	251.8
75°	175.2	183.1	193.8	194.9	194.9
77.5°	117.0	131.0	142.7	143.2	142.9
80°	83.5	99.4	110.2	112.5	111.4
82.5°	56.6	73.4	82.4	84.7	83.5
85°	25.5	39.1	46.4	47.5	46.4
87.5°	8.1	17.6	22.7	23.0	21.2
90°	3.4	10.1	20.6	22.3	22.3
92.5°	41.8	147.8	292.1	140.6	97.7
95°	96.0	342.4	1032.0	527.8	365.2
97.5°	153.3	392.0	1618.7	1352.3	1019.7
100°	197.2	411.7	1805.2	1888.8	1566.9
102.5°	239.7	439.5	1866.9	2290.6	2026.4
105°	313.7	488.1	1875.5	2805.9	2633.3
107.5°	383.7	539.2	1795.6	3070.7	3115.3
110°	430.3	577.8	1722.9	3153.0	3315.6



TEST NUMBER: P563004

CATALOG NUMBER: SQ4-PC3-125U-050D-935-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	479.7	616.5	1653.0	3134.8	3402.0
115°	553.7	677.8	1561.8	3017.7	3413.3
117.5°	621.3	737.6	1491.2	2830.8	3271.3
120°	665.2	777.5	1455.5	2696.7	3149.3
122.5°	703.6	814.5	1429.4	2559.5	3010.8
125°	756.0	868.3	1402.3	2370.2	2789.3
127.5°	806.4	917.1	1385.2	2203.2	2577.4
130°	836.6	947.2	1378.3	2107.6	2436.1
132.5°	866.8	976.1	1371.5	2023.3	2325.0
135°	910.3	1015.9	1362.9	1912.1	2165.2
137.5°	951.8	1053.1	1358.5	1817.8	2025.7
140°	980.6	1077.8	1354.3	1759.8	1947.5
142.5°	1010.8	1101.3	1351.6	1705.6	1863.9
145°	1052.6	1134.8	1345.8	1634.8	1755.5
147.5°	1097.9	1169.3	1339.9	1575.3	1670.1
150°	1128.0	1190.1	1337.2	1537.9	1616.6
152.5°	1155.5	1209.5	1335.8	1507.3	1571.4
155°	1194.9	1238.5	1333.8	1466.8	1513.8
157.5°	1229.5	1263.4	1334.1	1438.4	1469.9
160°	1251.5	1280.0	1335.5	1421.7	1445.2
162.5°	1270.7	1293.8	1336.9	1407.9	1424.6
165°	1296.1	1311.1	1338.9	1392.2	1398.9
167.5°	1316.6	1325.3	1340.6	1380.1	1382.8
170°	1330.3	1333.7	1340.6	1373.2	1373.2
172.5°	1338.6	1339.2	1342.0	1366.3	1366.3
175°	1347.5	1345.8	1340.6	1359.4	1356.1
177.5°	1351.3	1348.6	1341.7	1352.6	1349.9
180°	1345.8	1345.8	1345.8	1345.8	1345.8

(END OF REPORT)