

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563220

Luminaire Tested: **SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563220
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6672.8 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563220
CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563220

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75		
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64		
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54		
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46		
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39		
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34		
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30		
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27		
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24		
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22		
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8999	8999	8999
5°	9065	9010	8978
10°	9050	8986	8946
15°	8990	8941	8892
20°	8930	8880	8813
25°	8824	8763	8676
30°	8661	8615	8506
35°	8434	8376	8271
40°	8165	8113	8020
45°	7942	7885	7808
50°	7656	7607	7533
55°	7260	7164	7109
60°	6610	6420	6388
65°	5822	5580	5561
70°	5027	4819	4819
75°	4328	4267	4205
80°	3815	3860	3770
85°	2985	3255	3255



TEST NUMBER: P563220

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.5	2.8
10°-20°	526.7	7.9
20°-30°	788.9	11.8
30°-40°	925.4	13.9
40°-50°	928.3	13.9
50°-60°	791.9	11.9
60°-70°	516.4	7.7
70°-80°	259.1	3.9
80°-90°	73.1	1.1
90°-100°	126.2	1.9
100°-110°	331.8	5.0
110°-120°	344.1	5.2
120°-130°	276.0	4.1
130°-140°	216.6	3.2
140°-150°	166.2	2.5
150°-160°	119.7	1.8
160°-170°	73.2	1.1
170°-180°	24.7	0.4
0°-30°	1500.1	22.5
0°-40°	2425.5	36.3
0°-60°	4145.6	62.1
0°-90°	4994.2	74.8
90°-120°	802.1	12.0
90°-150°	1460.9	21.9
90°-180°	1679.0	25.2
0°-180°	6672.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1951	1951	1951	1951	1951	
5°	1958	1939	1946	1939	1939	186
15°	1882	1864	1872	1865	1862	531
25°	1734	1714	1722	1706	1705	797
35°	1498	1483	1487	1470	1469	936
45°	1217	1209	1209	1197	1197	937
55°	903	899	891	886	884	802
65°	533	523	511	508	510	532
75°	243	243	239	238	236	263
85°	56	61	62	62	62	66
90°	2	5	13	7	7	4
95°	17	65	218	112	76	19
105°	60	91	367	557	520	63
115°	106	129	294	586	669	105
125°	148	166	267	452	533	131
135°	176	194	259	365	413	136
145°	204	217	256	311	335	128
155°	231	237	256	281	289	106
165°	249	252	256	266	269	70
175°	259	259	257	261	261	25
180°	259	259	259	259	259	

TEST NUMBER: P563220

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1950.7	1950.7	1950.7	1950.7	1950.7
2.5°	1963.1	1947.0	1950.7	1947.8	1939.8
5°	1957.6	1939.2	1945.6	1938.8	1938.8
7.5°	1944.3	1924.2	1930.6	1923.7	1923.4
10°	1931.9	1911.9	1918.3	1911.4	1909.7
12.5°	1914.2	1894.1	1901.9	1893.6	1893.3
15°	1882.4	1864.0	1872.1	1865.2	1861.8
17.5°	1846.5	1826.4	1836.2	1826.6	1825.3
20°	1819.1	1799.0	1808.8	1795.2	1795.2
22.5°	1786.3	1766.2	1777.4	1759.6	1759.6
25°	1733.6	1713.6	1721.7	1706.2	1704.6
27.5°	1671.0	1651.3	1659.8	1642.3	1642.0
30°	1625.9	1607.5	1617.4	1598.5	1596.8
32.5°	1576.7	1559.6	1566.8	1547.9	1546.2
35°	1497.7	1482.6	1487.4	1470.3	1468.6
37.5°	1414.6	1399.2	1404.7	1390.0	1389.3
40°	1355.8	1345.7	1347.2	1335.2	1331.8
42.5°	1301.1	1289.7	1291.2	1279.2	1278.5
45°	1217.3	1208.9	1208.7	1196.8	1196.8
47.5°	1128.4	1122.0	1120.2	1110.3	1109.9
50°	1066.8	1061.8	1060.0	1051.4	1049.7
52.5°	1002.6	1000.2	994.4	987.2	986.8
55°	902.7	899.4	890.7	885.6	883.9
57.5°	794.3	787.6	777.9	770.4	771.8
60°	716.4	709.7	695.8	692.4	692.4
62.5°	641.1	633.1	619.2	614.5	617.2
65°	533.4	523.4	511.2	507.8	509.5
67.5°	435.6	426.6	413.4	413.4	412.0
70°	372.7	367.7	357.3	357.3	357.3
72.5°	316.6	314.3	306.7	306.7	305.3
75°	242.8	242.8	239.4	237.6	235.9
77.5°	181.9	182.6	180.9	179.1	176.1
80°	143.6	147.0	145.3	143.6	141.9
82.5°	108.1	111.4	111.1	108.0	107.7
85°	56.4	61.4	61.5	61.5	61.5
87.5°	15.4	21.4	24.5	23.2	24.6
90°	1.7	4.9	13.3	6.6	6.6
92.5°	7.0	33.6	74.4	32.9	21.2
95°	16.6	65.3	217.5	112.1	76.4
97.5°	28.9	71.7	325.4	258.8	190.6
100°	38.2	77.1	358.6	363.4	282.2
102.5°	46.2	82.5	367.9	452.6	383.1
105°	59.8	90.6	366.9	556.9	519.6
107.5°	73.7	102.3	346.0	611.1	620.2
110°	83.0	109.0	328.7	625.1	664.0



TEST NUMBER: P563220

CATALOG NUMBER: SQ4-PP3-025U-075D-935-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	92.3	117.0	312.8	616.3	676.0
115°	106.2	129.0	293.8	586.2	669.0
117.5°	119.9	140.6	280.9	544.6	636.5
120°	127.8	147.3	275.6	516.7	605.9
122.5°	135.8	155.3	271.6	488.7	576.7
125°	147.7	165.6	267.3	451.7	532.9
127.5°	157.4	175.6	263.6	421.9	490.4
130°	162.7	182.2	262.3	403.2	466.5
132.5°	168.0	187.5	261.0	387.1	443.9
135°	176.0	193.8	259.0	364.7	413.4
137.5°	184.3	201.8	258.6	347.9	387.8
140°	190.9	207.1	257.3	334.5	371.9
142.5°	196.2	211.2	257.3	325.1	357.3
145°	204.2	217.2	255.7	311.0	335.3
147.5°	212.2	224.8	255.7	299.3	319.4
150°	217.5	228.8	255.7	292.5	308.8
152.5°	222.8	231.5	255.7	287.1	299.5
155°	230.8	237.2	255.7	280.7	288.9
157.5°	236.7	242.9	255.7	275.0	280.9
160°	240.7	245.6	255.7	272.3	275.6
162.5°	244.7	248.3	255.7	269.7	272.9
165°	249.0	252.3	255.7	265.7	268.9
167.5°	253.0	254.6	257.3	264.0	265.3
170°	255.7	257.3	257.3	264.0	264.0
172.5°	257.0	257.3	257.3	262.6	261.3
175°	259.0	259.0	257.3	260.6	260.6
177.5°	259.0	259.0	257.6	260.3	259.0
180°	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)