

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565042

Luminaire Tested: **SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565042
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6814.6 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565042
CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565042

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	32	31	26
3	79	70	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	19	18	14
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8954	8954	8954
5°	9011	8940	8901
10°	8939	8867	8820
15°	8845	8747	8714
20°	8739	8605	8588
25°	8617	8461	8434
30°	8435	8308	8253
35°	8195	8080	8032
40°	7939	7817	7785
45°	7632	7531	7497
50°	7315	7253	7204
55°	6973	6973	6864
60°	6547	6674	6438
65°	5993	6292	5842
70°	5282	5789	5144
75°	4509	5183	4388
80°	3496	4362	3544
85°	2265	3345	2985



TEST NUMBER: P565042

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.3
10°-20°	258.0	3.8
20°-30°	382.7	5.6
30°-40°	447.8	6.6
40°-50°	445.8	6.5
50°-60°	385.0	5.6
60°-70°	277.1	4.1
70°-80°	145.3	2.1
80°-90°	37.6	0.6
90°-100°	314.8	4.6
100°-110°	847.9	12.4
110°-120°	889.9	13.1
120°-130°	722.1	10.6
130°-140°	566.3	8.3
140°-150°	434.8	6.4
150°-160°	312.6	4.6
160°-170°	191.0	2.8
170°-180°	64.4	0.9
0°-30°	732.1	10.7
0°-40°	1179.9	17.3
0°-60°	2010.7	29.5
0°-90°	2470.7	36.3
90°-120°	2052.6	30.1
90°-150°	3775.9	55.4
90°-180°	4344.0	63.7
0°-180°	6814.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	973	962	965	963	961	92
15°	926	914	916	914	912	261
25°	846	832	831	826	828	389
35°	728	718	717	711	713	455
45°	585	580	577	575	575	451
55°	434	433	434	428	427	387
65°	274	283	288	277	268	272
75°	126	138	145	136	123	136
85°	21	28	32	30	28	28
90°	2	5	10	11	11	4
95°	48	171	516	264	183	50
105°	157	244	938	1403	1317	165
115°	277	339	781	1509	1707	272
125°	378	434	701	1185	1395	338
135°	455	508	682	956	1083	351
145°	526	567	673	817	878	330
155°	598	619	667	733	757	275
165°	648	656	670	696	700	183
175°	674	673	670	680	678	64
180°	673	673	673	673	673	

TEST NUMBER: P565042

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.5	970.5	970.5	970.5	970.5
2.5°	975.9	967.9	970.5	968.3	963.6
5°	973.0	962.2	965.3	962.7	961.1
7.5°	963.1	953.1	955.4	952.7	951.7
10°	954.2	944.2	946.5	943.1	941.4
12.5°	944.0	933.3	935.6	932.1	931.1
15°	926.0	914.3	915.8	914.0	912.3
17.5°	905.2	893.3	893.5	890.8	890.4
20°	890.1	877.6	876.4	873.0	874.7
22.5°	873.7	860.5	859.3	854.6	856.9
25°	846.5	832.3	831.1	826.0	828.5
27.5°	815.0	801.0	801.0	793.9	796.6
30°	791.8	778.4	779.8	771.3	774.7
32.5°	767.1	755.1	755.9	747.4	750.7
35°	727.6	717.6	717.4	710.6	713.1
37.5°	687.3	678.4	677.0	673.1	673.8
40°	659.2	651.7	649.0	646.4	646.4
42.5°	629.8	623.0	620.2	618.4	617.7
45°	584.9	579.8	577.2	575.4	574.6
47.5°	540.4	535.7	533.4	532.2	531.3
50°	509.6	506.3	505.3	502.7	501.9
52.5°	478.8	476.8	475.9	472.6	471.8
55°	433.5	432.7	433.5	427.5	426.7
57.5°	386.3	387.6	390.4	382.3	380.3
60°	354.8	358.2	361.7	352.2	348.9
62.5°	322.7	328.0	333.0	322.1	317.4
65°	274.5	282.8	288.2	276.8	267.6
67.5°	228.0	238.3	244.7	232.5	222.1
70°	195.8	207.5	214.6	202.4	190.7
72.5°	167.8	180.8	186.6	175.0	163.3
75°	126.5	138.3	145.4	135.7	123.1
77.5°	89.8	100.8	106.7	98.3	87.9
80°	65.8	77.5	82.1	75.1	66.7
82.5°	46.7	56.4	59.5	55.3	49.6
85°	21.4	28.1	31.6	29.9	28.2
87.5°	5.8	11.2	15.1	15.2	15.9
90°	1.7	5.1	10.3	11.1	11.1
92.5°	20.9	73.9	146.1	70.3	48.9
95°	48.0	171.2	516.0	263.9	182.6
97.5°	76.6	196.0	809.3	676.1	509.9
100°	98.6	205.9	902.6	944.4	783.5
102.5°	119.8	219.7	933.5	1145.3	1013.2
105°	156.9	244.0	937.8	1403.0	1316.6
107.5°	191.8	269.6	897.8	1535.4	1557.7
110°	215.2	288.9	861.5	1576.5	1657.8

TEST NUMBER: P565042

CATALOG NUMBER: SQ4-PW1-125U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.8	308.2	826.5	1567.4	1701.0
115°	276.9	338.9	780.9	1508.8	1706.6
117.5°	310.6	368.8	745.6	1415.4	1635.7
120°	332.6	388.7	727.7	1348.3	1574.6
122.5°	351.8	407.3	714.7	1279.8	1505.4
125°	378.0	434.2	701.2	1185.1	1394.6
127.5°	403.2	458.5	692.6	1101.6	1288.7
130°	418.3	473.6	689.2	1053.8	1218.1
132.5°	433.4	488.0	685.7	1011.6	1162.5
135°	455.2	508.0	681.5	956.1	1082.6
137.5°	475.9	526.5	679.2	908.9	1012.8
140°	490.3	538.9	677.2	879.9	973.8
142.5°	505.4	550.7	675.8	852.8	931.9
145°	526.3	567.4	672.9	817.4	877.8
147.5°	548.9	584.6	670.0	787.6	835.1
150°	564.0	595.0	668.6	768.9	808.3
152.5°	577.7	604.7	667.9	753.7	785.7
155°	597.5	619.2	666.9	733.4	756.9
157.5°	614.8	631.7	667.1	719.2	734.9
160°	625.7	640.0	667.7	710.9	722.6
162.5°	635.3	646.9	668.4	703.9	712.3
165°	648.0	655.6	669.5	696.1	699.5
167.5°	658.3	662.7	670.3	690.1	691.4
170°	665.2	666.8	670.3	686.6	686.6
172.5°	669.3	669.6	671.0	683.2	683.2
175°	673.7	672.9	670.3	679.7	678.0
177.5°	675.6	674.3	670.8	676.3	674.9
180°	672.9	672.9	672.9	672.9	672.9

(END OF REPORT)