

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565138

Luminaire Tested: **SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565138
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7705.0 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565138
CATALOG NUMBER: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565138

CATALOG NUMBER: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	22	21	17
5	65	54	46	40	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8954	8954	8954
5°	9011	8940	8901
10°	8939	8867	8820
15°	8845	8747	8714
20°	8739	8605	8588
25°	8617	8461	8434
30°	8435	8308	8253
35°	8195	8080	8032
40°	7939	7817	7785
45°	7632	7531	7497
50°	7315	7253	7204
55°	6973	6973	6864
60°	6547	6674	6438
65°	5993	6292	5842
70°	5282	5789	5144
75°	4509	5183	4388
80°	3496	4362	3544
85°	2265	3345	2985



TEST NUMBER: P565138

CATALOG NUMBER: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.4	1.2
10°-20°	258.0	3.3
20°-30°	382.7	5.0
30°-40°	447.8	5.8
40°-50°	445.8	5.8
50°-60°	385.0	5.0
60°-70°	277.1	3.6
70°-80°	145.3	1.9
80°-90°	37.7	0.5
90°-100°	377.3	4.9
100°-110°	1020.1	13.2
110°-120°	1072.5	13.9
120°-130°	871.2	11.3
130°-140°	683.3	8.9
140°-150°	524.5	6.8
150°-160°	377.2	4.9
160°-170°	230.4	3.0
170°-180°	77.7	1.0
0°-30°	732.1	9.5
0°-40°	1179.9	15.3
0°-60°	2010.7	26.1
0°-90°	2470.9	32.1
90°-120°	2469.9	32.1
90°-150°	4548.9	59.0
90°-180°	5234.0	67.9
0°-180°	7705.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	973	962	965	963	961	92
15°	926	914	916	914	912	261
25°	846	832	831	826	828	389
35°	728	718	717	711	713	455
45°	585	580	577	575	575	451
55°	434	433	434	428	427	387
65°	274	283	288	277	268	272
75°	126	138	145	136	123	136
85°	21	28	32	30	28	28
90°	2	5	11	12	11	5
95°	58	206	627	325	193	61
105°	190	293	1132	1669	1601	200
115°	334	408	938	1817	2051	330
125°	457	524	846	1428	1677	407
135°	548	613	823	1153	1305	423
145°	637	685	812	987	1062	399
155°	719	747	805	885	914	332
165°	783	791	808	840	844	221
175°	813	812	809	820	818	77
180°	812	812	812	812	812	

TEST NUMBER: P565138

CATALOG NUMBER: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.5	970.5	970.5	970.5	970.5
2.5°	975.9	967.9	970.5	968.3	963.6
5°	973.0	962.2	965.3	962.7	961.1
7.5°	963.1	953.1	955.4	952.7	951.7
10°	954.2	944.2	946.5	943.1	941.4
12.5°	944.0	933.3	935.6	932.1	931.1
15°	926.0	914.3	915.8	914.0	912.3
17.5°	905.2	893.3	893.5	890.8	890.4
20°	890.1	877.6	876.4	873.0	874.7
22.5°	873.7	860.5	859.3	854.6	856.9
25°	846.5	832.3	831.1	826.0	828.5
27.5°	815.0	801.0	801.0	793.9	796.6
30°	791.8	778.4	779.8	771.3	774.7
32.5°	767.1	755.1	755.9	747.4	750.7
35°	727.6	717.6	717.4	710.6	713.1
37.5°	687.3	678.4	677.0	673.1	673.8
40°	659.2	651.7	649.0	646.4	646.4
42.5°	629.8	623.0	620.2	618.4	617.7
45°	584.9	579.8	577.2	575.4	574.6
47.5°	540.4	535.7	533.4	532.2	531.3
50°	509.6	506.3	505.3	502.7	501.9
52.5°	478.8	476.8	475.9	472.6	471.8
55°	433.5	432.7	433.5	427.5	426.7
57.5°	386.3	387.6	390.4	382.3	380.3
60°	354.8	358.2	361.7	352.2	348.9
62.5°	322.7	328.0	333.0	322.1	317.4
65°	274.5	282.8	288.2	276.8	267.6
67.5°	228.0	238.3	244.7	232.5	222.1
70°	195.8	207.5	214.6	202.4	190.7
72.5°	167.8	180.8	186.6	175.0	163.3
75°	126.5	138.3	145.4	135.7	123.1
77.5°	89.8	100.8	106.7	98.3	87.9
80°	65.8	77.5	82.1	75.1	66.7
82.5°	46.7	56.4	59.5	55.3	49.6
85°	21.4	28.1	31.6	29.9	28.2
87.5°	5.8	11.2	15.3	15.5	16.0
90°	1.7	5.2	11.4	12.2	11.4
92.5°	24.8	90.4	178.4	77.5	56.1
95°	58.5	205.5	627.4	324.7	193.1
97.5°	94.0	235.7	978.0	809.4	594.4
100°	120.6	247.9	1087.1	1133.7	916.7
102.5°	145.1	264.9	1125.6	1379.7	1217.3
105°	189.6	293.0	1131.7	1669.3	1600.9
107.5°	230.9	325.2	1082.2	1850.0	1872.7
110°	263.0	348.5	1038.2	1898.5	1995.1

TEST NUMBER: P565138

CATALOG NUMBER: SQ4-PW1-150U-075D-935-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.7	371.7	997.6	1888.8	2051.0
115°	333.8	408.2	938.5	1816.9	2051.0
117.5°	375.1	444.8	899.6	1706.9	1972.3
120°	400.2	468.6	876.5	1628.1	1898.9
122.5°	424.0	491.0	862.5	1543.5	1816.4
125°	457.0	523.7	845.9	1427.5	1677.0
127.5°	487.4	552.9	836.1	1332.8	1552.2
130°	504.2	571.7	831.9	1274.2	1472.5
132.5°	521.7	588.5	827.7	1221.5	1404.0
135°	547.9	612.9	823.2	1152.6	1304.7
137.5°	574.3	635.7	819.3	1096.7	1220.6
140°	592.5	649.7	817.9	1060.8	1171.0
142.5°	610.0	663.8	815.2	1028.3	1124.9
145°	637.1	684.9	811.8	986.6	1061.8
147.5°	661.7	704.1	808.0	948.8	1006.5
150°	679.9	717.5	806.6	928.2	974.4
152.5°	696.7	729.5	805.9	909.2	947.1
155°	719.2	747.4	804.8	885.0	914.1
157.5°	742.6	762.3	805.0	868.2	887.3
160°	755.9	772.1	805.7	857.6	871.3
162.5°	766.4	779.9	806.4	849.1	859.4
165°	783.0	790.7	808.3	839.9	844.2
167.5°	794.4	799.7	808.5	832.0	834.0
170°	801.3	803.9	809.2	828.4	828.4
172.5°	806.9	807.4	809.2	824.2	823.5
175°	812.7	811.8	809.2	819.7	817.9
177.5°	814.6	812.6	809.0	816.0	813.9
180°	811.8	811.8	811.8	811.8	811.8

(END OF REPORT)